



Natural Solutions for a Natural World

## Why All-Natural?

If we all understood the connection of environmental damage to our own lives, we would be much more motivated to preserve and protect our habitat.

A global survey of groundwater pollution shows that a toxic brew of pesticides, nitrogen fertilizers, industrial chemicals, and heavy metals is fouling groundwater everywhere. "Groundwater contamination is an irreversible act that will deprive future generations of one of life's basic resources," according to Payal Sampat in a Worldwatch paper.

OSM is committed to bringing all-natural and environmentally friendly products to the global marketplace.

Our objective is the ultimate safety of our children, our pets, our wildlife, and Mother Nature.

We offer the finest biodegradable, nontoxic, effective "green" cleaners and odor-control products available.

Biodegradable, **All-Natural**, environmentally preferable cleaners.  
Powerful, yet nontoxic for even the toughest jobs!



Can be emptied safely down your drain.

Renewable-plant-based formulations, phosphate free, no glycol ether, phthalate free, and ozone safe.

Available in convenient ready to use 32 ounce spray bottles,  
and in 1 gallon and 5 gallon jugs.



**Fisher Scientific**



## OSM All-Natural Odor Control

- Destroys severe odors naturally
- Instantly freshens enclosed areas
- Eliminates odor on contact
- Nontoxic
- Biodegradable
- Safe to use around people and animals
- Effective against animal odors, smoke, and all types of waste odors
- No harsh chemical fumes or vapor
- Nonallergenic
- Renewable-plant-derived formulation, phosphate free, no glycol ether, ozone safe, phthalate free

<b>ODOR CONTROL</b>	<b>32 OZ</b>	<b>1/EA &amp; 12/CS</b>	<b># 15-336-504</b>
<b>ODOR CONTROL</b>	<b>1 GAL</b>	<b>1/EA &amp; 4/CS</b>	<b># 15-336-513</b>
<b>ODOR CONTROL</b>	<b>5 GAL</b>	<b>1/EA</b>	<b># 15-336-522</b>

OSM All-Natural Odor Control destroys severe odors naturally. This nontoxic, biodegradable formulation freshens instantaneously in enclosed areas and replaces the offensive odor with a light, refreshing citrus aroma. It quickly eliminates odors on contact. This formulation may be used as an air freshener or mixed with cleaning solutions to eliminate unwanted odors. Very effective, OSM Odor Control removes animal odors, smoke, and all types of waste odors. Ideal for use in kitchens, bathrooms, offices, and industrial settings. Perfect for use in healthcare, vivariums, and animal environments.



## OSM All-Natural Instrument Detergent

- Perfect cleaner for surgical instruments
- Ideal for histology, cytology, necropsy, and pathology work
- Mild foaming detergent provides quick and thorough cleaning in manual, ultrasonic, and automated cleaning applications
- pH neutral, will not damage or rust instruments and equipment
- Multi-enzyme formula effectively works within minutes to disintegrate and carry away organic wastes
- Nontoxic, nonflammable, noncaustic, noncorrosive, biodegradable
- Does not sanitize
- No harsh chemical fumes or vapor
- Phosphate free, no glycol ether, ozone safe, phthalate free

<b>INSTRUMENT CLEANER</b>	<b>32 OZ</b>	<b>1/EA &amp; 12/CS</b>	<b># 15-336-507</b>
<b>INSTRUMENT CLEANER</b>	<b>1 GAL</b>	<b>1/EA &amp; 4/CS</b>	<b># 15-336-516</b>
<b>INSTRUMENT CLEANER</b>	<b>5 GAL</b>	<b>1/EA</b>	<b># 15-336-525</b>

OSM All-Natural Instrument Detergent is a low foaming multi-enzyme detergent and presoak cleaner for medical instruments and apparatuses. This formula is a blend of enzymes that are effective in the removal of proteins, blood, and fatty tissue, and effectively works within minutes to disintegrate and carry away these organic soils. It is ideal for cleaning endoscopes, respiratory equipment, glassware, and tissue culture tubes, and removes stains in surgical scrubs, linens, and medical clothing. This powerful natural detergent provides quick and thorough cleaning in manual, ultrasonic, and automatic cleaning applications. It can be used as a presoak prior to autoclaving. It is pH neutral, nontoxic, noncaustic, and biodegradable.



## OSM Eco-Friendly Instrument Lubricant

- Ideal for histology, cytology, necropsy, and pathology work
- Perfect lubricant for surgical instruments
- Powerful anticorrosive agent
- Keeps moving parts working freely, frees box locks and hinges
- Protects against rust and pitting
- Safe to use around people and animals
- No harsh chemical fumes or vapor
- pH neutral, safe for all types of instruments
- Water-soluble, gentle formula,
- Leaves a protective coating, which prolongs instrument life
- Phosphate free, no glycol ether, ozone safe, phthalate free

<b>INSTRUMENT LUBRICANT</b>	<b>32 OZ</b>	<b>1/EA &amp; 12/CS</b>	<b># 15-336-508</b>
<b>INSTRUMENT LUBRICANT</b>	<b>1 GAL</b>	<b>1/EA &amp; 4/CS</b>	<b># 15-336-517</b>
<b>INSTRUMENT LUBRICANT</b>	<b>5 GAL</b>	<b>1/EA</b>	<b># 15-336-526</b>

OSM Instrument Lubricant contains an eco-friendly corrosion inhibitor and lubricant especially formulated to lubricate and protect surgical instruments, hinges, box locks, and general equipment during the autoclaving process. Ideal for histology, cytology, necropsy, and pathology work. Its powerful anticorrosive agent keeps moving parts working freely and protects against pitting and rusting. It is pH neutral and safe for all types of instruments. OSM Instrument Detergent and OSM Lubricant are perfectly compatible for the autoclaving process. For the autoclaving process, use OSM Instrument Detergent as a presoak prior to spraying with OSM Instrument Lubricant and then autoclaving.



## OSM All-Natural Stain Remover

- Works on hard surfaces, carpet, or fabric
- Noncaustic, nontoxic, non-allergenic, and environmentally preferable
- No harsh chemical fumes or vapor
- Removes lab animal stains, blood, food stains, mold, mildew, and more
- Ideal for cleaning hard-to-reach spots like tile, grout, and corners
- Safe to use around people and animals
- Renewable-plant-derived formulation, phosphate free, no glycol ether, ozone safe, phthalate free

<b>STAIN REMOVER</b>	<b>32 OZ</b>	<b>1/EA &amp; 12/CS</b>	<b># 15-336-505</b>
<b>STAIN REMOVER</b>	<b>1 GAL</b>	<b>1/EA &amp; 4/CS</b>	<b># 15-336-514</b>
<b>STAIN REMOVER</b>	<b>5 GAL</b>	<b>1/EA</b>	<b># 15-336-523</b>

OSM All-Natural Stain Remover is a proprietary blend of natural cleaning agents, plant-based surfactants, biocatalysts and enzymes. Nontoxic and biodegradable, our special blend of enzyme-based stain remover is strong enough to remove all protein matter, mold and mildew from hard laboratory surfaces as well as carpeting and fabrics. Removes lab animal stains, blood, vomit, fecal matter, urine, food stains, mold, mildew, and more. Non-allergenic and safe to use around children and animals. Environmentally preferable, it is perfect for use in healthcare, vivariums, and animal environments.



## OSM All-Natural Glass & Surface Cleaner

- All-natural water-based formula
- Use on a variety of surfaces in bathroom, kitchen, and work areas
- Streak-free shine with no smearing
- Safe to use around people and animals
- No harsh chemical fumes or vapor
- Non-allergenic, nontoxic, noncaustic, and biodegradable
- Use on glass, plastics, rubber, vinyl, labware, and most metals
- No ammonia
- Renewable-plant-derived formulation, phosphate free, no glycol ether, ozone safe, phthalate free

<b>GLASS CLEANER</b>	<b>32 OZ</b>	<b>1/EA &amp; 12/CS</b>	<b># 15-336-503</b>
<b>GLASS CLEANER</b>	<b>1 GAL</b>	<b>1/EA &amp; 4/CS</b>	<b># 15-336-512</b>
<b>GLASS CLEANER</b>	<b>5 GAL</b>	<b>1/EA</b>	<b># 15-336-521</b>

OSM All-Natural Glass & Surface Cleaner is an environmentally friendly, nontoxic alternative glass and surface cleaner that cleans streak free with no smearing. Use on a variety of surfaces in the bathroom, kitchen, lab, and work areas. Safe for use on plastics, glass, glassware, labware, rubber, vinyl, and most metals. Perfect for glass test tubes, glass petri dishes, and weigh plates. Contains no ammonia or phosphates. Ideal for nontoxic cleaning in office, school, lab, work, and animal environments.



## OSM All-Natural Degreaser

- Removes grease and oil naturally, and leaves no residue
- No chlorinated solvents or alkaline detergents
- Cuts through grease and grime in seconds
- Nontoxic, biodegradable, non-allergenic
- Safe to use around people and animals
- Ideal for use on all lab and office surfaces
- No harsh chemical fumes or vapor
- Renewable-plant-derived formulation, phosphate free, no glycol ether, ozone safe, phthalate free
- Cleans dry erase boards free of "ghosts"

<b>DEGREASER</b>	<b>32 OZ</b>	<b>1/EA &amp; 12/CS</b>	<b># 15-336-502</b>
<b>DEGREASER</b>	<b>1 GAL</b>	<b>1/EA &amp; 4/CS</b>	<b># 15-336-511</b>
<b>DEGREASER</b>	<b>5 GAL</b>	<b>1/EA</b>	<b># 15-336-520</b>

OSM All-Natural Degreaser cuts through grease and grime in seconds. Removing grease and oil naturally, Degreaser is a unique blend of natural plant-based surfactants, and biopolymers that readily emulsify oil, grease, and hydrocarbon-based liquids. This water-based formulation contains no chlorinated solvents, alkaline detergents, or harsh chemicals. Biodegradable, it produces no harmful vapors and leaves no residue. It is ideal for steam cleaning engines and machines, or for general cleanups in and around facilities. May also be used on wood, chrome, plastic, laminates, tile, and more. Use anywhere oil and grease is a problem. Ideal for use on all lab and office surfaces. Cleans dry erase boards.



## OSM All-Natural No-Rinse Floor Cleaner

- Use on wood, vinyl, laminate, linoleum, and tile
- Penetrates and lifts grease, dirt, and grime
- Gently cleans, leaving a beautiful luster
- No harmful residue
- Biodegradable, noncaustic, and environmentally preferable
- Natural formula safe to use around people and animals
- Perfect for cabinets, molding, doors, and painted surfaces
- No harsh chemical fumes or vapor
- Nonallergenic, highly effective
- Renewable-plant-based formulation, phosphate free, no glycol ether, ozone safe, phthalate free

**FLOOR CLEANER 32 OZ 1/EA & 12/CS # 15-336-501**

**FLOOR CLEANER 1 GAL 1/EA & 4/CS # 15-336-510**

**FLOOR CLEANER 5 GAL 1/EA # 15-336-519**

OSM Floor Cleaner is a multi-enzyme blend designed to break oils, grease and other organic material from hard surfaces. This cleaner is specially formulated to clean and degrease floors, walls, kitchens, restrooms, concrete, terrazzo, ceramic tile, machines, and equipment in industrial, commercial, and institutional applications. It penetrates and emulsifies grease, dirt, grime on wood, vinyl, laminate, linoleum, and tile surfaces. The solution is biodegradable, noncaustic, nontoxic, and enzyme-based. It contains no harsh chemicals such as butyls, caustics, or phosphates. Leaves no harmful residue.



## OSM All-Natural Concrete Cleaner

- Nontoxic, biodegradable, environmentally preferable
- Noncaustic, noncorrosive, and nonallergenic
- Removes oil, grease, grime, and mildew from concrete, asphalt, and stone
- Ideal for use on driveways, patios, floors, and sidewalks
- Ideal for use in kennels and barn stalls
- No harsh chemical fumes or vapor
- Ideal for statuary, markers, and gravestones
- Can be used in power washers
- Natural, enzymatic, microbial-based formulation
- Renewable-plant-based formulation, phosphate free, no glycol ether, ozone safe, phthalate free

**CONCRETE CLEANER 32 OZ 1/EA & 12/CS # 15-336-506**

**CONCRETE CLEANER 1 GAL 1/EA & 4/CS # 15-336-515**

**CONCRETE CLEANER 5 GAL 1/EA # 15-336-524**

OSM All-Natural Concrete Cleaner is a blend of natural plant-based cleaning agents, surfactants, and biocatalysts. It uses powerful natural cleaning agents, and digesting microbes. This noncaustic, noncorrosive, biodegradable formulation removes oil, mildew, mold, and waste stains from listed surfaces by emulsifying and biodegrading the stain. It is ideal for petroleum-based stains on garage floors, sidewalks, parking lots, kennels, and barns. It allows you to effectively clean surfaces without harming people, pets, wildlife, lawns, and gardens. May be used on any stone, asphalt, and concrete surfaces.



## OSM All-Natural All-Purpose Cleaner

- Powerful cleaning action
- Penetrates and lifts dirt, grease, and grime
- Ideal for use on countertops, floors, cabinets, appliances, and all lab surfaces
- No harsh chemical fumes or vapor
- Nontoxic, biodegradable, noncaustic
- Environmentally preferable
- Safe to use around people and pets
- Non-allergenic
- Renewable-plant-derived formulation, phosphate free, no glycol ether, ozone safe, phthalate free

**ALL-PURPOSE CLEANER 32 OZ 1/EA & 12/CS # 15-336-500**

**ALL-PURPOSE CLEANER 1 GAL 1/EA & 4/CS # 15-336-509**

**ALL-PURPOSE CLEANER 5 GAL 1/EA # 15-336-518**

OSM All-Purpose Cleaner is an enzyme-based formula designed to attack and remove organic debris from all types of surfaces. This environmentally preferable formula is plant-derived from natural sources and does not contain any harsh chemicals or solvents. Nontoxic and biodegradable, the cleaning action is powerful enough to lift and remove grease and grime from all hard laboratory surfaces, yet will not harm people, wildlife, or lawn and grounds. Perfect for use in healthcare, vivariums, and animal environments.



**Fisher Scientific**

For customer service, call 1-800-766-7000.  
To fax an order, use 1-800-926-1166.  
To order online: [www.fishersci.com](http://www.fishersci.com)

BN112072