

72 Hour QuickShip



Buchi announces new 72 hour QuickShip Program.

Now you can receive the quality you need; as quickly as you need it. Just place an order for one of the products listed on the reverse side of this flyer and within 72 hours it will be shipped out to you. Products include our most popular models in the following categories:

- R11 Rotavapor
- R-210 Rotavapor
- R-215 Rotavapor
- R-220 Rotavapor
- V-700 Vacuum Pump
- V-710 Vacuum Pump



Buchi R11 Rotavapor®

Equipped with a new sealing system and a mechanical lifting jack. The rotation speed can be adjusted between 20 - 280 Rpm. The insulated heating bath has a temperature range of 20 - 95°C with water as a medium. Complete and ready to use with one 1000ml evaporating flask and one 1000ml receiving flask.

Fisher Cat No	Buchi Cat No	Description	US Sugg List Price
05-402-287	2422V1	100-120V, 24/40, V-Condenser, Plastic + Glass	4,285.45
05-402-285	2422C1	100-120V, 24/40, C-Condenser, Plastic + Glass	4,564.52

Buchi R-210 Rotavapor®

Equipped with a new sealing system, an electronic quick-action jack. Rotation speed is electronically adjusted from 20 - 280 Rpm. Insulated heating bath has a temperature range of 20 - 180°C and can be used with oil or water; the bath is equipped with an illuminated display for set and actual temperature. Unit is complete and ready to use with one 1000ml evaporating flask and one 1000ml receiving flask.

Fisher Cat No	Buchi Cat No	Description	US Sugg List Price
05-402-201	23022C100	100-120V, C-Condenser, Plastic + Glass, 24/40	5,455.14
05-402-209	23022V100	100-120V, V-Condenser, Plastic + Glass, 24/40	5,151.00
05-402-205	23022C112	100-120V, C-Condenser, Plastic + Glass, 24/40, V-850 & Valve Unit	8,147.12
05-402-213	23022V112	100-120V, V-Condenser, Plastic + Glass, 24/40, V-850 & Valve Unit	8,871.87

Buchi R-215 Rotavapor®

Equipped with a display module for rotation and vapor temperature, a new sealing system, an electronic quick-action jack. The rotation speed can be adjusted between 20 - 280 Rpm. Insulated heating bath has a temperature range of 20 - 180°C and can be used with oil or water as a medium; the bath also has a digital temperature display. The unit is complete with one 1000ml evaporating flask and one 1000ml receiving flask.

Fisher Cat No	Buchi Cat No	Description	US Sugg List Price
05-402-249	23122C100	100-120V, C-Condenser, Plastic + Glass, 24/40	6,024.58
05-402-257	23122V100	100-120V, V-Condenser, Plastic + Glass, 24/40	5,843.40
05-402-253	23122C112	100-120V, C-Condenser, Plastic + Glass, 24/40, V-850 & Valve Unit	9,544.86
05-402-264	23122V122	100-120V, V-Condenser, Plastic + Glass, 24/40, V-855 & Valve Unit	9,564.28

Buchi R-220 Rotavapor®

Insulated heating bath with an electronic bath lift, suitable for use with water or oil, with a temperature range of 20 - 180°C. Easy assembly and dismantling with the patented Snap Flange Coupling and the EasyClamp. Easy to use control panel with 3 LED-displays for speed, vapor temperature and bath temperature.

Fisher Cat No	Buchi Cat No	Description	US Sugg List Price
05-402-030	8111C262	230V, with Bath Replenishment, 20L Evap Flask, Descending Cond with Secondary Cond, two 10L Rec Flask	38,170.50

Buchi V-700 Vacuum Pump

Completely enclosed, chemically resistant PTFE diaphragm pump with transparent window heads that works with all types of gases or vapours. The unit has a flow rate of 1.8 m³/h and an max. vacuum of <10 mbar. All systems include a silencer and 2m of tubing. Buchi highly recommends using a Woulff Bottle to protect your pump from contaminants or particulate matter.

Fisher Cat No	Buchi Cat No	Description	US Sugg List Price
05-402-100	071000	100-230V basic unit	1,868.86
05-402-103	071010	100-230V with Woulff Bottle	2,016.40

Buchi V-710 Vacuum Pump

Completely enclosed, chemically resistant PTFE diaphragm pump with transparent window heads that works with all types of gases or vapours. The unit has a flow rate of 3.1 m³/h and an max. vacuum of 2 mbar. All systems include a silencer and 2m of tubing and integrated ON-OFF function.

Fisher Cat No	Buchi Cat No	Description	US Sugg List Price
05-402-136	072000	100-230V basic unit	5,209.23



Fisher Scientific

For customer service, call 1-800-766-7000.

To fax an order, use 1-800-926-1166.

To order online: www.fishersci.com

1-877-MYBUCHI or visit www.mybuchicom

Quality in your hands