



---

# Water and Waste Water Treatment

---

Tel: 1-800-955-7000 Fax: 1-800-926-1166 Web: [www.fishersci.com](http://www.fishersci.com)



***Making the world a healthier, safer, cleaner place***



Choice and convenience ... look to Fisher Scientific for all your water and wastewater treatment products. We can supply you with the brand – name products you know and prefer at very competitive prices.

We have created this catalog specifically for your environmental and testing needs. Products are grouped by testing application.

For more choices and information visit our Web site or call our customer service today!

## **FREE Water Quality Powder Pack Reagent Samples**

Use the Business Reply  
Card found inside to get  
your FREE Water Quality  
Powder Pack™ Reagent  
Samples from  
**Orbeco-Hellige.**

**orbeco**  
H E L L I G E

**Fisher Scientific. One Source. Infinite Solutions.**



For customer service, call 1-800-766-7000.  
To fax an order, use 1-800-926-1166.  
To order online: [www.fishersci.com](http://www.fishersci.com)

# Table of Contents

---

<b>Alkalinity.....</b>	<b>1</b>	<b>Solids.....</b>	<b>50</b>
<b>Aluminum.....</b>	<b>1</b>	<b>Sulfide.....</b>	<b>55</b>
<b>Chloride and Chlorine Dioxide.....</b>	<b>1</b>	<b>Temperature.....</b>	<b>55</b>
<b>Chromate.....</b>	<b>3</b>	<b>Turbidity.....</b>	<b>56</b>
<b>Copper, and Cyanide.....</b>	<b>3</b>	<b>Zinc.....</b>	<b>57</b>
<b>Electrochemistry.....</b>	<b>4</b>		
Conductivity.....	4		
Oxygen.....	7		
pH/pX (including ISE and ORP).....	12		
<b>Filtration.....</b>	<b>28</b>		
<b>Fluoride and Glycol.....</b>	<b>36</b>		
<b>General Labware.....</b>	<b>36</b>		
<b>Hardness and Hydrazine.....</b>	<b>39</b>		
<b>Hydrogen Peroxide.....</b>	<b>39</b>		
<b>Iron and Lead.....</b>	<b>40</b>		
<b>Lab Equipment and Instruments.....</b>	<b>40</b>		
<b>Manganese.....</b>	<b>44</b>		
<b>Microbiological.....</b>	<b>44</b>		
<b>Nitrogen (including Amonia, Nitrate and Nitrite).....</b>	<b>48</b>		
<b>Ozone and Phenol.....</b>	<b>49</b>		
<b>Phosphates, Phosphorus and Silica.....</b>	<b>49</b>		



# Alkalinity

## LaMotte Series 1200 Colorimeter Single-Test Kits - For Alkalinity Testing



**22-307-839** - Each for \$48.00  
Colorimeter; Series 1200; LaMotte; Single-parameter; Water-resistant, handheld single-parameter meters; Analyte: P and T Alkalinity; Range (ppm): 0-200 as CaCO<sub>3</sub>; Method: Direct Reading Titrator

**22-307-838** - Each for \$31.95  
Analyte: Acidity; Range (ppm): 1 drop = 0.1 or 1.0%; Method: Dropper Bottle

## Orbeco Model 942 Mini Analysts Ordering Information - With Reagent Tablets - For Alkalinity Testing

**15-405-107** - Each for \$302.66  
Spectrophotometer; Model 942; Orbeco; With reagent tablets; 50 tests; Test: Alkalinity, total; Range: 0-500mg/L

## Orbeco Model 942: Test Kits for 975MP Analyst and 942 Mini Analysts - With Reagent Tablets - For Alkalinity Testing

**15-410-M** - Each for \$23.41  
Reagent, Test Kit; For use with 975MP and 942 Mini Analysts; 50 tests; Test: Alkalinity, total; Range: 0-500mg/L

**15-410-C** - Each for \$24.46  
Test: Alkalinity, P; Range: 0-500mg/L

# Aluminum

## EM Science Quant Test Strips - For Aluminum Testing



**M100151** - Pack of 100 for \$85.22  
Quants Aluminum 100/Pk., Range: 0-10-30-100-500-1000ppm

## Orbeco-Hellige Powder Packs for Metals - For Aluminum Testing



**09-053-257** - Each for \$86.00  
Reagent set, Colorimeter; Powder Pack; Aluminum; 10mL; 100 tests

## Orbeco-Hellige SC400 Series Colorimeters - For Aluminum Testing



**09-053-274** - Each for \$320.00  
Colorimeter; Orbeco-Hellige SC400; Aluminum; Range, 0.01-0.80mg/L

# Chloride and Chlorine Dioxide

## Fisherbrand DPD Free Chlorine Test Reagent



**15-393-57** - Pack of 200 for \$49.88  
Reagent; Fisherbrand; Chlorine Test; DPD Free; 5mL

## CHEMetrics Chemets Self-Filling Ampules - For Chlorine Testing



**13-299-248** - Pack of 1 for \$41.79  
Kit, Test; Chemets; CHEMetrics; Provide results in two minutes or less; Analyte: Chlorine (DPD); Testing Range: 0.1-2.0ppm; Analytical Method: DPD; Complete Test Kit

**13-299-508B** - Pack of 30 for \$24.13  
Chlorine (DPD); Testing Range: 0.1-2.0ppm; Analytical Method: DPD; Refil Ampule

**13-299-215B** - Each for \$57.84  
Chlorine (DDPD); Testing Range: 0-1.0 and 1.0-5.0ppm; Analytical Method: DDPD Chemistry; Complete Test Kit

**13-299-215C** - Pack of 30 for \$24.60  
Chlorine (DDPD); Testing Range: 0-1.0 and 1.0-5.0ppm; Analytical Method: DDPD Chemistry; Refil Ampule

## EM Science Quant Test Strips - For Chlorine Testing



**M100791** - Pack of 100 for \$54.20  
Testing Supplies; Water quality; Strips; Test; EM Quant; Test: Chloride; Range: 500 to 3000ppm; Ready-to-use; Detection chemicals, buffers, masking agents, stabilizers are incorporated; Supplied in sturdy aluminum cylinders

**M100431** - Pack of 100 for \$105.38  
Test: Chlorine; Range: 4-12-40-120ppm

## HF Scientific Chlorine Dioxide Pocket Photometer

**15-393-91** - Each for \$333.44  
Photometer, Pocket; HF Scientific; Chlorine Dioxide, w/Four Cuvets with Caps, Powder Pop Dispenser with 100 Doses of Reagent, 30mL Glycine Reagent, 4-AAA Alkaline Batteries, and Instructions

## HF Scientific Chlorine Micro Check Test Strips



**14-376-163** - Pack of 50 for \$14.70  
Paper; pH Indicator; Format: Strips; Micro Check; Total Chlorine; Range: 0.05 to 10ppm; Accurate results in under a minute

**14-376-164** - Pack of 50 for \$14.70  
Free Chlorine

## HF Scientific Chlorine Pocket Photometer



**15-393-92** - Each for \$425.24  
Photometer, Pocket, Free Chlorine, w/Carrying Case, Four Cuvets with Caps, 4-AAA Alkaline Batteries, and Instructions

**15-393-90** - Each for \$425.24  
Pocket Photometer (Total Chlorine)

**HF Scientific Chlorine Testing DPD Powder Pop Dispenser**



- 15-393-65** - Each for \$56.74  
Water Testing Strips; Total Chlorine; PPD-2 DPD; Powder Pop; For Manufacturers: HF Scientific (including Model CP-15), Hach; Sample Size: 5mL
- 15-393-71** - Each for \$66.74  
Total Chlorine; Sample Size: 10mL; For Manufacturers: Hanna, Lamotte, Palintest, Tintometer, YSI, Orbeco/Hellige
- 15-393-70** - Each for \$66.74  
Total Chlorine; Sample Size: 10mL; For Manufacturers: Hach
- 15-393-68** - Each for \$66.74  
Free Chlorine; Sample Size: 10mL; For Manufacturers: Hach
- 15-393-69** - Each for \$66.74  
Free Chlorine; Sample Size: 10mL; For Manufacturers: Hanna, Lamotte, Palintest, Tintometer, YSI, Orbeco/Hellige
- 15-393-64** - Each for \$62.29  
Free Chlorine; Sample Size: 5mL

**HF Scientific MicroTPW Portable Turbidimeter**



- 15-393-55** - Each for \$777.41  
Turbidimeter; Portable, MicroTPW; White Light; Waterproof; 0-1100 NTU; Includes: Carrying Case, Manual, Calibration Standards; Indexing Rings, 4 x (AAA) Batteries, and Measuring Cuvettes with Light Shield Caps

**Lamotte Chlorine TRACER PockeTester**



- 22-278-617** - Each for \$169.95  
TRACER PockeTester Total Chlorine Kit, Read Total Chlorine from 0.00 to 9.99ppm to 0.01ppm resolution, Extra bold display includes an analog bar graph feature, uses four LR-44 batteries, Readings are not affected by sample color

**Lamotte DPD Chlorine Secondary Standards Kit for Series 1200 Colorimeters**



- 22-307-837** - Each for \$70.00  
Standards, DPD Chlorine Secondary; Lamotte; For use with 1200 series chlorine colorimeters; One blank, 3 standards for low-, mid-range, high calibrations

**LaMotte Insta-Test Sanitizer Test Strips**



- 22-307-871** - Each for \$8.36  
Chlorine Dioxide Sanitizer Test Strips; LaMotte Insta-Test; Range, 0-10ppm (0-0.25-0.5-1-3-10); 10-second development time; For food/beverage water testing; 50 tests per vial; Desiccant liner and tight snap cap
- 22-307-872** - Each for \$8.31  
Chlorine Dioxide; Range, 0-500ppm

**LaMotte Series 1200 Colorimeter Single-Test Kits - For Chlorine Testing**



- 22-278-567** - Each for \$350.44  
Colorimeter; Series 1200; LaMotte; Single-parameter; Water-resistant, handheld single-parameter meters; Analyte: Chlorine, free and total; Range (ppm): 0-4.0; Method: DPD Tablets
- 22-278-553** - Pack of 50 for \$55.50  
Analyte: Chlorine free and total; Range (ppm): 0.2-3.0; Method: DPD Tablet Octa-Slide
- 22-278-568** - Each for \$350.44  
Analyte: Chlorine, free and total; Range (ppm): 0-4.0; Method: DPD Liquid
- 22-307-854** - Each for \$89.34  
Analyte: Chlorine free and total; Range (ppm): Low: 0.1-1.0/High: 1.0-6.0; Method: DPD Tablet 2 Octa-Slide
- 22-307-845** - Each for \$44.00  
Analyte: Chlorine Bleach Iodometric Titration; Range (ppm): 0-10%; Method: Direct Reading Titrator

**LaMotte Test Strips**




- 22-479-808** - Pack of 200 for \$5.35  
Paper, Test Strip; LaMotte; For Chlorine test; 10, 50, 100, 200ppm Test Range; 200 Strips; With Color Chart; Plastic Waterproof Vial

**Micro Essential Lab Hydrion Micro Chlorine Test Paper**

- 15-420-2T** - Case of 50 for \$83.09  
Test strips; Chlorine; Refill; For Hydrion Micro Chlorine tester; 15 ft. (4.6m) roll; 10 to 200ppm free available chlorine; 50/Cs.

**Micro Essential Lab Hydrion Micro Chlorine Tester for 10 to 200ppm**



- 15-420-2Q** - Case of 10 for \$47.28  
Test strips; Chlorine; Hydrion; Micro; Chlorine tester; Range: 10, 50, 100, and 200ppm; Includes dispenser with color chart and two 15 ft. (4.6m) rolls of test paper; For chlorine sanitizing solutions from 10 to 200ppm;

**Orbeco Model 942 Mini Analysts Ordering Information - With Reagent Tablets - For Chlorine Testing**

- 15-405-114** - Each for \$291.68  
Spectrophotometer; Model 942; Orbeco; With reagent tablets; 50 tests; Test: Chlorine, free and total; Range: 0-3.5/7.0mg/L
- 15-405-113** - Each for \$302.66  
Test: Chloride; Range: 0-50mg/L
- 15-405-115** - Each for \$302.10  
Test: Chlorine, high range; Range: 0-250mg/L

**Orbeco Model 942: Test Kits for 975MP Analyst and 942 Mini Analysts - With Reagent Tablets - For Chlorine Testing**

- 15-398-412** - Each for \$18.00  
Reagent, Test Kit; For use with 975MP and 942 Mini Analysts; 50 tests; Test: Chlorine, free and total; Range: 0-3.5/7.0mg/L

**15-398-450** - Each for \$44.00  
Test: Chloride; Range: 0-50mg/L

### Orbeco-Hellige Pocket Comparators DPD Tablets

**15-398-102A** - Pack of 50 for \$6.75  
Tablets, DPD; Orbeco-Hellige; For pocket comparators and DPD color discs;  
Tablet No. 1; For Determining: Free Available Chlorine  
**15-398-102B** - Pack of 50 for \$7.07  
Dpd Tablets No 2 50/pk  
**15-398-102C** - Pack of 50 for \$7.07  
Dpd Tablets No 3 50/pk  
**15-398-102D** - Pack of 50 for \$6.75  
Dpd Tablets No 4 50/pk

### Orbeco-Hellige Pocket Comparators Low-Range Chlorine Color Discs for DPD Procedure

**15-398-101B** - Each for \$89.11  
Standards; For use with Orbeco-Hellige Pocket Comparators; Chlorine color discs; Standards for: 0.1, 0.2, 0.25, 0.3, 0.4, 0.5, 0.6, 0.7, 0.8, 1.0ppm Cl  
**15-398-101C** - Each for \$91.34  
Chlorine DPD Disc 0.1 - 2.0ppm  
**15-398-101A** - Each for \$91.34  
Chlorine DPD Disc 0.2 - 4.0ppm

### Orbeco-Hellige Pocket Comparators Low-Range Color Discs, Assorted

**15-398-101D** - Each for \$186.67  
Standards; For use with Orbeco-Hellige Pocket Comparators; Low Range DPD Color Discs; Assorted pack

### Orbeco-Hellige Powder Packs for Free and Total Chlorine



**09-053-216** - Each for \$13.75  
Reagent, Colorimeter; Powder Pack; Free Chlorine; DPD; 5mL; Pack of 100  
**09-053-217** - Each for \$117.50  
Free Chlorine; 5mL; Pack of 1000  
**09-053-218** - Each for \$16.50  
Free Chlorine; 10mL; Pack of 100  
**09-053-219** - Each for \$142.00  
Free Chlorine; 10mL; Pack of 3000  
**09-053-220** - Each for \$17.50  
Free Chlorine; 25mL; Pack of 100  
**09-053-221** - Each for \$149.25  
Free Chlorine; 25mL; Pack of 1000  
**09-053-214** - Each for \$13.75  
Total Chlorine; 5mL; Pack of 100  
**09-053-215** - Each for \$117.50  
Total Chlorine; 5mL; Pack of 1000  
**09-053-222** - Each for \$16.50  
Total Chlorine; 10mL; Pack of 100  
**09-053-223** - Each for \$142.00  
Total Chlorine; 10mL; Pack of 1000  
**09-053-224** - Each for \$17.50  
Total Chlorine; 25mL; Pack of 100  
**09-053-225** - Each for \$149.25  
Total Chlorine; 25mL; Pack of 1000

### Orbeco-Hellige SC400 Series Colorimeters - For Chlorine Testing



**09-053-277** - Each for \$320.00  
Colorimeter; Orbeco-Hellige SC400; Chlorine (Free & Total); Range, 0.02-2.00, 0.1-8.0mg/L  
**09-053-276** - Each for \$320.00  
Chlorine Dioxide

### Orbeco-Hellige Simplex Chlorine and pH Comparator Test Kits - For Chlorine Testing



**15-398-396** - Each for \$81.64  
Water Testing Supplies; Uses eight built-in, nonfading, color standards mounted in a durable, corrosion-resistant housing; Chlorine/pH Kit; Method: DPD/Phenol Red; 0.2-3.0ppm Cl<sub>2</sub>; Range: 6.8-8.2 pH  
**15-398-399** - Each for \$45.18  
Orthotolidine Test Kits For Chlorine; Method: Acid Orthotolidine; Range: 0.2-3.0ppm  
**15-398-398** - Each for \$40.31  
Total and Free Chlorine Test Kit; Method: DPD; Range: 0.1-1.0ppm  
**15-398-397** - Each for \$40.31  
Total and Free Chlorine Test Kit; Method: DPD; Range: 0.2-3.0ppm

### Thermo Scientific Orion AQUAfast II Colorimeters Single Parameter Kits - For Chlorine Testing



**13-642-688** - Each for \$351.44  
Colorimeter; AQUAfast II; Thermo Scientific Orion; Single parameter; Ideal for fast, accurate water quality testing in the laboratory and the field; Analyte: Chlorine, free and total; Range: 0.05 to 6.0mg/L

## Chromate

### EM Science Quant Test Strips - For Chromate Testing



**M100121** - Pack of 100 for \$65.14  
Test: Chromate Kit; Pack of: 100; Range: 3-10-30-100ppm

## Copper, and Cyanide

### CHEMetrics Chemets Self-Filling Ampoules - For Copper Testing



**13-299-216A** - Each for \$57.84  
Kit, Test; Chemets; CHEMetrics; Provide results in two minutes or less; Analyte: Copper; Testing Range: 0-1.0 and 1-10ppm; Analytical Method: Bathocuproine; Complete Test Kit  
**13-299-216B** - Each for \$24.13  
Copper; Testing Range: 0-1.0 and 1-10ppm; Analytical Method: Bathocuproine; Refill Ampule

### EM Science Quant Test Strips - For Copper Testing



**M100441** - Pack of 100 for \$95.15  
Test: Cyanide Kit; Pack of: 100; Range: 1-3-10-30ppm  
**M106481** - Pack of 100 for \$54.20  
Test: Carbonate hardness; Range: 0 to 425ppm  
**M100031** - Pack of 100 for \$54.20  
Test: Copper; Range: 10 to 300ppm

### Orbeco-Hellige Powder Packs for Metals - For Copper Testing



**09-053-226** - Each for \$28.75  
Reagent, Colorimeter; Powder Pack; Copper; 10mL; Pack of 100

Orbeco-Hellige SC400 Series Colorimeters - For Copper Testing




**09-053-279** - Each for \$320.00  
Colorimeter; Orbeco-Hellige SC400; Copper; Range, 0.04-5.00mg/L

Pyrex Regular Cyanide Distillation Apparatus



**05-723-16** - Case of 1 for \$511.95  
Apparatus, Cyanide Distillation; Pyrex; For testing soluble and insoluble cyanides in water; Complete assembly

Wheaton Complete Cyanide Distillation Apparatus



**09-108** - Case of 1 for \$326.09  
Apparatus, Cyanide Distillation; Wheaton; Convert any cyanide to hydrocyanic acid (HCN), HCN is distilled and absorbed in NaOH solution, and sample is analyzed for CN; Complete Distillation Assembly  
**09-108-1** - Each for \$23.75  
Component: Absorber Jacket  
**09-108-2** - Case of 1 for \$90.12  
Component: Absorber Top  
**09-108-3** - Case of 1 for \$62.62  
Component: Cold Finger Condenser  
**09-108-4** - Case of 1 for \$78.40  
Component: Cold Finger Jacket  
**09-108-5** - Case of 1 for \$71.14  
Component: Distilling Flask, 1000mL  
**09-108-6** - Case of 1 for \$28.02  
Component: Inlet Tube

# Electrochemistry

## Conductivity

Fisher pH/Conductivity Universal Flow-thru Adapter



**06-662-59** - Each for \$86.44  
Adapter, Flow; Fisherbrand; pH/Conductivity; Universal; Constant use up to 500 deg. F

Fisher Scientific accumet AP75 Portable Waterproof Conductivity Meter



**13-636-AP75A** - Each for \$773.00  
Meter, Conductivity, Fisher Scientific accumet AP75 Conductivity/TDS/ deg. C/F Meter/Probe; 0.00uS/cm - 199.9mS/cm, 0.00 - 200ppt; 0.0 - 100.0 deg. C; Time/date stamp, 5-pt. calibration, 50-reading memory  
**13-636-AP75** - Each for \$873.57  
Meter Kit

Fisher Scientific accumet Basic AB30 Conductivity Meter



**13-636-AB30** - Each for \$970.16  
Meter Kit, Fisher Scientific accumet Benchtop Model AB30 Basic; Temp. mode: -5 to 105 deg. C; Resolution: 0.1 deg. C; Conductivity Mode: 0 To 3 x 10<sup>4</sup>S/cm; Accuracy; +/-0.5%; Power Supply, Manual, Electrode Supply  
**13-636-AB30A** - Each for \$907.28  
AB30 Basic Meter only

Fisher Scientific accumet Dedicated Conductivity Probe for Fisher Scientific accumet and Oakton Meters



**13-620-AP54** - Each for \$253.74  
Probe; Conductivity/TDS/Temperature; For Fisher Scientific accumet AP75; AP85 Portable Meters; Plastic body, K=1.0cmsup-1. With 3ft. cable, notched 6-p

Fisher Scientific accumet Excel XL30 Conductivity Meter



**13-636-XL30** - Each for \$1939.69  
Meter, Electrochemistry; Fisher Scientific accumet Excel XL30; Measures conductivity/resistivity/salinity/temperature; Uses 2 or 4-cell probes; Includes meter, 2-cell cond. cell w/ATC probe, electrode support arm/bracket, and power supplies  
**13636XL30A** - Each for \$1701.39  
XL30 Meter Only

Fisher Scientific accumet Temperature-Compensated Two-Cell Conductivity Probes



**13-620-101** - Each for \$335.33  
Electrode, Two-Cell Conductivity Probe/Temperature Sensor Fisher Scientific accumet; for Excel Meters XL60, XL50, XL30, XL15; Cell Constant: 0.1cm<sup>-1</sup>; Epoxy body, 8-pin connector  
**13-620-100** - Each for \$335.33  
Two-Cell Conductivity Probe/Temperature Sensor; Cell Constant: 1.0cm<sup>-1</sup>; 8-pin connector for XL Meters  
**13-620-102** - Each for \$335.33  
Two-Cell Conductivity Probe/Temperature Sensor; Cell Constant: 10.0cm<sup>-1</sup>; 8-pin connector for XL Meters



### Fisher Scientific accumet Two-Cell and Four-Cell Conductivity Probes



- 13-620-156** - Each for \$254.80  
Electrode, Two-Cell Conductivity Probe, Fisher Scientific accumet; for Fisher Scientific accumet Meters AR60, AR50, AR20; AB30; AP65; 0.5-200microS range; 0.1cm<sup>-1</sup> cell constant; Glass body, 8-pin connector
- 13-620-160** - Each for \$254.81  
Two-Cell Conductivity Probe; Cell Constant: 1.0 cm<sup>-1</sup>, 8-pin connector for AR and AB meters
- 13-620-162** - Each for \$254.81  
Two-Cell Conductivity Probe; Cell Constant: 10cm<sup>-1</sup>, 8-pin connector for AR and AB meters
- 13-620-161** - Each for \$254.82  
Two-Cell; Cell Constant: 0.1 cm<sup>-1</sup>
- 13-620-155** - Each for \$254.82  
Two-Cell; Cell Constant: 1.0cm<sup>-1</sup>
- 13-620-157** - Each for \$254.80  
Two-Cell; Cell Constant: 10.0cm<sup>-1</sup>
- 13-620-163** - Each for \$422.31  
Four-Cell Conductivity Probe, Cell Constant: 1.0cm<sup>-1</sup>, 8-pin connector for AR and AB meters
- 13-620-165** - Each for \$403.92  
Four-Cell, Cell Constant: 1.0cm<sup>-1</sup>
- 13-620-166** - Each for \$402.72  
Four-Cell, Cell Constant: 10.0cm<sup>-1</sup>, Epoxy Body
- 13-620-164** - Each for \$422.31  
Four-Cell, Cell Constant: 10.0cm<sup>-1</sup>, Glass Body

### Fisherbrand Redi-Stor Conductivity Probe Storage Solution



- 09-330-1** - Each for \$31.73  
Conductivity Probe Storage Solution, Conductivity Cell Accessories, Fisherbrand Redi-Stor; Preserves cleanliness. Eliminates growths found when stored in water; 16 oz.,

### Fisherbrand Traceable Conductivity Calibration Standards



- 09-328-5** - Each for \$28.43  
Standard, Conductivity Calibration; Fisherbrand; Dissolved Solids: 66,666 ppm; Calibration Resistance: 0.00001 megohms; Conductivity: 100,000 micromhos
- 06-664-24** - Each for \$28.43  
Dissolved Solids: 6666 ppm; Calibration Resistance: 0.0001 megohms; Conductivity: 10,000 micromhos
- 06-664-24** - Each for \$57.26  
TDS: 3.3ppm; Resistivity: 0.5megohms; Conductivity: 5micromhos; 16 oz.
- 09-328-1** - Each for \$28.43  
TDS: 6.6ppm; Resistivity: 0.1megohms; Conductivity: 10micromhos; 16 oz.
- 09-328-3** - Each for \$28.43  
TDS: 666ppm; Resistivity: 0.001megohms; Conductivity: 100micromhos; 16 oz.
- 09-328-2** - Each for \$28.43  
TDS: 66ppm; Resistivity: 0.01megohms; Conductivity: 100micromhos; 16 oz.
- 09-328-11** - Each for \$26.74  
TDS: 933ppm; Resistivity: 0.00071megohms; Conductivity: 1413micromhos; 16 oz.

### Fisherbrand Traceable One-Shot Conductivity Calibration Standards



- 06-664-25** - Pack of 6 for \$76.34  
Calibration Standards, Conductivity; Fisherbrand; Traceable One-Shot; 5um; Dissolved Solids: 3.3ppm; Calibration Resistance: 0.2megohms; Conductivity: 5micromhos; Ideal for lab or field applications
- 09-328-6** - Pack of 6 for \$32.06  
Calibration Standards, Conductivity: 10umhos
- 09-328-7** - Pack of 6 for \$32.06  
Calibration Standards, Conductivity: 100umhos
- 09-328-8** - Pack of 6 for \$32.06  
Calibration Standards, Conductivity: 1,000umhos
- 09-328-12** - Pack of 6 for \$32.06  
Calibration Standards, Conductivity: 1,413umhos
- 09-328-9** - Pack of 6 for \$32.06  
Calibration Standards, Conductivity: 10,000 umhos
- 09-328-10** - Pack of 6 for \$32.06  
Calibration Standards, Conductivity: 100,000 umhos

### Fisherbrand Traceable One-Shot Conductivity Calibration Standards Assortment

- 09-328-20** - Pack of 6 for \$44.47  
Calibration Standards, Conductivity; Fisherbrand; Traceable One-Shot; Assortment; 6/pk

### Mettler Toledo S30 Basic Conductivity Meter



- 01-913-801** - Each for \$1155.00  
Meter, Conductivity; Mettler Toledo; S30 Basic Conductivity Meter; Includes meter, 9V power supply, electrode support arm, operating instructions, conductivity probe, two 12.88mS/cm and two 1413uS/cm 20mL buffer sachets
- 01-913-800** - Each for \$925.00  
Conductivity Meter Only

### Mettler Toledo S70 Advanced Conductivity Meter



- 01-913-803** - Each for \$1920.00  
Meter, Conductivity; Mettler Toledo; S70K Advanced Conductivity Meter Kit. Includes InLab 730 conductivity probe, standards, electrode support arm, power supply, and operating instructions. Meets USP guidelines. 120V
- 01-913-802** - Each for \$1695.00  
Advanced Conductivity Meter Only

### Mettler Toledo Probes for S30 and S70 Meters

- 01-928-133** - Each for \$274.00  
Electrode, conductivity, Mettler Toledo, 0 to 500 uS/cm, mini-DIN connector, ATC probe; 2-cell probe; For InLab 720; Probe Material: Glass/Platinum
- 01-920-143** - Each for \$465.00  
2-cell probe; For InLab 740; Probe Material: PVC, V4A Steel/Steel
- 01-928-132** - Each for \$274.00  
4-cell probe; For InLab 710; Probe Material: Glass/Platinum
- 01-911-258** - Each for \$317.00  
4-cell probe; For InLab 730; Probe Material: Epoxy/Graphite

### Mettler Toledo SevenGo and SevenGo pro Conductivity Meters



- 01-910-522** - Each for \$765.00  
Meter, Conductivity; SevenGo; Mettler Toledo; Automatic and manual endpoint recognition; Automatic temperature compensation; Data memory for 30 GLP data points; Meter with Electrode and 1.8m Cable
- 01-910-525** - Each for \$1155.00  
Meter with Electrode, 1.8m Cable, Case and ErGo Field Assistant
- 01-910-527** - Each for \$1180.00  
Pro Meter with Electrode, 1.8m Cable and Case

**01-910-529** - Each for \$1480.00  
Pro Meter with Electrode, 1.8m Cable, Case and ErGo Field Assistant

**Oakton Acorn CON 6 and TDS 6 Portable Meters**



**15-500-050** - Each for \$414.22  
Meter Kit, Handheld; Acorn CON 6; Oakton; Measures conductivity from 0.0uS/cm to 200.00mS/cm; Autoranging; Meter Kit  
**15-500-052** - Each for \$309.21  
CON 6; Meter with Probe  
**15-500-051** - Each for \$414.22  
TDS 6; Meter Kit  
**15-500-053** - Each for \$309.21  
TDS 6; Meter with Probe

**Oakton CON 11 Standard Conductivity Meter**



**13-620-236** - Each for \$547.53  
Meter Kit, Conductivity; Oakton Con 11; Includes meter, conductivity/TDS/temperature cell, 20 calibration pouches; 0-19.99mS range; 0-9.99ppt range; +/-1% FS accuracy; 0.0-100.0 deg. C; Autoranging; 4 point calibration  
**13-620-237** - Each for \$458.70  
Meter Only

**Oakton CON 110 Advanced Conductivity Meter**



**13-620-240** - Each for \$613.54  
Meter, Conductivity Kit, Oakton Con 110; Inc: meter, conductivity/temperature cell, 20 calibration pouches, carrying case; Measures conductivity/temp.; 0-199.9mS range; Autoranging; +/-1% FS accuracy; 16 memory points; 5 point calibration  
**13-620-241** - Each for \$523.43  
Meter Only

**Oakton CON 510 Benchtop Meter**



**13-620-328** - Each for \$630.40  
Meter, Benchtop; Oakton Con 510; Conductivity Mode Range: 0-19.99uS, 0-199.9uS, 0-1999uS, 0-19.99mS, 0-199.9mS; TDS Mode: 0-9.99ppm, 10-99.9ppm, 100-999ppm, 1.00 to 9.99ppt, 10-99.9ppt, 100-200ppt; Temp. Range: 0-100 deg. C (32-212 deg. F)

**Oakton Replacement Electrode Sensors for TDSTestrs and ECTestrs Portable Conductivity Meters**



**13-200-233** - Each for \$52.73  
Sensor, Replacement; Oakton; Electrode sensor replacement part for TDSTestrs and ECTestrs models  
**13-200-240** - Each for \$62.19  
Replacement sensor for TDSTestrs Plus and ECTestrs Plus models

**Thermo Scientific Orion 2-Electrode Conductivity Cell for Orion Star Series Meters**

**13-642-224** - Each for \$331.84  
Electrode, Conductivity, Thermo Scientific Orion; 2-Electrode Cell; for Orion Star Series meters; Field and lab use; Epoxy/Graphite body; 10uS/cm to 200mS/cm range; Cell constant, 1.0cm<sup>-1</sup>

**Thermo Scientific Orion 3-Star Benchtop Conductivity Meter**



**13-645-105** - Each for \$1039.38  
Meter, Electrochemistry, Benchtop pH/Conductivity, Orion 3-Star; Meter Kit for Ultrapure Water; 0.000 to 3000mS/cm, -5 to +105 deg. C; Includes meter, conductivity probe with 1.5m cable, 100mS standard, electrode stand, manual  
**13-645-106** - Each for \$1386.18  
3-Star Benchtop pH Meter Kit for USP 645  
**13-642-054** - Each for \$782.34  
3-Star Benchtop pH Meter Only  
**13-645-104** - Each for \$1138.32  
3-Star Benchtop pH Meter/Probe

**Thermo Scientific Orion 3-Star Portable Conductivity Meter**



**13-645-121** - Each for \$890.46  
Meter, Conductivity; Orion; 3-Star Portable Conductivity Meter; Measures conductivity, resistivity, salinity, TDS; Meter/Probe Kit package; 4-cell conductivity probe  
**13-642-061** - Each for \$714.00  
Meter Only; without electrode or accessories.

**Thermo Scientific Orion Conductivity Cells**



**13-642-226** - Each for \$464.00  
Cells, Conductivity; Orion; OLD; DuraProbe 4-electrode; Epoxy/graphite cell; K = 0.475cmsup-1; Mini-DIN; 3m cable  
**13-642-225** - Each for \$430.00  
Epoxy/Graphite Cell, K = 0.475cmsup-1, 1.5m Cable  
**13-642-223** - Each for \$371.34  
Epoxy/Graphite, K = 0.10.1cmsup-1, 1.5m Cable  
**13-642-228** - Each for \$439.65  
Epoxy/graphite; K=0.55cmsup-1, Mini-DIN, 3m cable  
**13-642-227** - Each for \$574.00  
Stainless Steel Cell, K = 0.10.1cmsup-1, 1m Cable

**Thermo Scientific Orion Two- and Four-Electrode Conductivity Cells**



**13-302** - Each for \$271.00  
Conductivity Cell; Orion; 2-electrode Cell, Epoxy/graphite body; Cell Constant: 0.1cm<sup>-1</sup>; For field and laboratory applications; 17.8mm dia., 134mL; 3m cable, 8-pin DIN connector  
**13-302-15** - Each for \$422.00  
4-electrode cell; Epoxy/graphite body; Cell Constant: 0.475cm<sup>-1</sup>  
**13-302-1** - Each for \$419.00  
4-electrode cell; Epoxy/graphite; Cell Constant: 0.55cm<sup>-1</sup>; for Models 130A, 135A  
**13-302-18** - Each for \$569.00  
Conductivity Cells, K = 0.10.1cmsup-1; 8-Pin DIN; 1m cable  
**13-302-12** - Each for \$613.88  
Epoxy/graphite; Cell Constant: 0.475cm<sup>-1</sup>, 8-Pin waterproof DIN, 20m cable  
**13-302-9** - Each for \$422.00  
Epoxy/graphite; Cell Constant: 0.475cm<sup>-1</sup>, 8-pin waterproof DIN, 5 ft. cable  
**13-302-7** - Each for \$611.00  
Stainless steel; Cell Constant: 0.1cm<sup>-1</sup>, 8-Pin Waterproof DIN, 1m cable

### Yellow Springs Instrument Benchtop Conductivity Meters



**09-324-46** - Each for \$898.00  
 Meter, Benchtop Conductivity/Temperature, YSI; Model 3100 120; 0 to 499,999microS/cm (in 5 ranges); -5 to +95 deg. C; order probes separately; 120V 60Hz  
**09-324-47** - Each for \$898.00  
 Model 3100; 230V 50/60Hz  
**09-324-48** - Each for \$1625.00  
 Model 3200; 120V 60Hz  
**09-324-49** - Each for \$1650.00  
 Model 3200; 230V 50/60Hz

### Yellow Springs Instrument Dip-Type Glass Conductivity Cells



**09-324-32** - Each for \$427.66  
 Electrode, Conductivity; Yellow Springs Instrument; Length: 6-1/4 in.; With thermistor; K = 0.1cm-1, +/- 1%  
**09-324-55** - Each for \$427.66  
 Without thermistor; K = 0.1cm-1, +/- 1%  
**09-324-31** - Each for \$399.00  
 Without thermistor; K = 1.0cm-1, +/- 1%  
**09-324-33** - Each for \$427.66  
 Without thermistor; K = 10.0cm-1, +/- 1%

### Yellow Springs Instrument Dip-Type Glass Micro Conductivity Cells



**09-324-52** - Each for \$397.46  
 Electrode, Conductivity; Yellow Springs Instrument; Dip-Type; Glass; With thermistor; K = 1.0cm-1, +/- 1%  
**09-324-22** - Each for \$377.34  
 Without thermistor; K = 1.0cm-1, +/- 1%

### Yellow Springs Instrument Dip-Type Plastic Conductivity Cells



**09-324-51** - Each for \$230.00  
 Electrode, Conductivity; Yellow Springs Instrument; Dip-Type; Plastic; With thermistor; K = 1.0cm-1, +/-1%  
**09-324-30** - Each for \$225.00  
 Without thermistor; K = 0.1cm-1, +/-1%  
**09-324-28** - Each for \$225.00  
 Without thermistor; K = 1.0cm-1, +/-1%

### Yellow Springs Instrument Fill Conductivity Cell

**09-324-53** - Each for \$427.66  
 Electrode, Conductivity; Yellow Springs Instrument; Glass; Fill Type; K = 1.0cm-1, +/-1%

### Yellow Springs Instrument Flow-Through Conductivity Cell



**09-324-54** - Each for \$437.72  
 Electrode, Conductivity; Yellow Springs Instrument; Glass; Flow-Through Type; K = 0.1cm-1, +/-1%

### Yellow Springs Instrument Pro Series Conductivity/Temperature Probes with Cables

**15-177-474** - Each for \$295.00  
 Cable; Conductivity/Temperature; probe and cable; 4m cable  
**15-177-476** - Each for \$395.00  
 20m cable

### Yellow Springs Instrument Adapter for Dip-Type Plastic Conductivity Cells

**09-324-50** - Each for \$158.61  
 Adapter, Electrode; Yellow Springs Instrument; For Dip-Type Plastic Cells; Required to use cells without thermistor with Models 3200 and 3100 Conductivity Meters

## Oxygen

### Fisher Dissolved Oxygen Membrane Kit for accumet Benchtop Dissolved Oxygen Meters

**13-637-DOM** - Each for \$153.99  
 Membrane Kit; Includes: Six membrane caps; Polishing Disk; Electrolyte filling solution; For accumet Benchtop Dissolved Oxygen Meters

Fisher Scientific accumet Basic AB40 Benchtop Dissolved Oxygen Meter Kit



**13-636-AB40** - Each for \$2084.19  
 Meter Kit; Benchtop; Dissolved Oxygen; Fisher Scientific accumet Basic-AB40; 4-1/2L x 3 in. W display; On-screen prompt guide; Range: 0-60mg/L (ppm), 0-600% saturation; Accuracy: 0.1% +1 Isd (mg/L); Temp Range: 0-45 deg. C

Fisher Scientific accumet BOD Probe for Fisher Scientific accumet Benchtop Dissolved Oxygen Meters

**13-620-SSP** - Each for \$991.63  
 Probe; Self-Stirring BOD; For all current Fisher Scientific accumet benchtop meters with dissolved oxygen mode, including XL60, XL40, AR40, AB40.

Fisher Scientific accumet Excel XL60 pH/mV/Temperature/DO/ISE/Conductivity Meter - For Oxygen Testing



**13-636-XL60D** - Each for \$3770.50  
 Meter, pH/ISE/Conductivity/DO; Fisher Scientific accumet XL60D Benchtop Meter Kit/DO; reads 1x10sup-6 to 9.99x10sup10 ISE, -2.000. to +20.000pH, -2000 to +2000mV, 0 to 5x10E5microS/cm conductivity, 0 to 60mg/L and 0 to 600% saturation DO

Fisher Scientific Isotemp Large-Capacity Refrigerated Incubator Chart Recorder Paper



**15-074-79** - Pack of 60 for \$46.25  
 Paper, Chart; Fisher Scientific Isotemp; Pen Line Resolution to: 0.75degree F/C; Ruled to: 2degree F/C; Range: - 50degree to + 50degree F/C  
**15-074-80** - Pack of 60 for \$46.25  
 Range: -50 to 0 or 0 to 50 deg. F/C; Ruled: 1 deg. F/C

Fisher Scientific Isotemp Large-Capacity Refrigerated Incubator Red Recorder Pens



**13-940-997** - Pack of 6 for \$71.84  
 Recorder Pen, replacement pen for Fisher Scientific Isotemp Large Capacity Refrigerated Incubator, Red

Fisher Scientific Isotemp Large-Capacity Refrigerated Incubator Shelves

**11-679-10L** - Each for \$102.77  
 Shelf, Incubator, Fisher; Large shelf for Isotemp 304 and 304R Large-Capacity BOD Incubators; Fits lower half of the unit  
**11-679-10SN** - Each for \$102.77  
 Small shelf fits upper half of unit

Fisher Scientific Isotemp Large-Capacity Refrigerated Incubators



**11-679-304RN** - Each for \$9580.00  
 Incubator; Low-temperature; Fisher; isotemp Model 304RN; Holds 600 BOD bottles; Chamber capacity: 30.4 cu.ft.; 4 shelves; Temp range: -15 to 50 deg.C; With chart recorder; 115V 60Hz; 15A  
**11-679-304** - Each for \$8418.00  
 Without chart recorder

Fisher Scientific Isotemp Standard-Capacity Refrigerated Incubator



**11-679-25CN** - Each for \$5146.61  
 Incubator, Refrigerated, Standard-Capacity, Fisher; Isotemp Incubator; Microprocessor-based controller, LED readout; ?10 to +60 deg. C range; +/-0.5 deg.C uniformity; +/-0.25 deg.C stability; Safety relay, alarm LED, zero switching; CFC-fr

Fisher Scientific Isotemp Undercounter Refrigerated Incubators



**97-990E** - Each for \$3497.41  
 Incubator, Undercounter Refrigerated; Fisher Scientific Isotemp; 6.1 cubic ft. capacity; 115V 60Hz, 6A; Temp range -10 to 60 deg. C; Door-mounted microprocessor controller; White; 24-1/2 L x 24 W x 34-1/2 in. H; CSA approved  
**97-995EN** - Each for \$4163.00  
 230V 50Hz, 5.8A

BioScience accu-Test COD Reactors



**01-215-23** - Each for \$807.50  
 Vial for COD Reactor Type, 15-tube, BioScience, L x W x H: 7 x 8 x 4 in.; Contains mercury  
**01-215-24** - Each for \$1024.92  
 30-tube; 9-1/2 x 8 x 4 in.; Contains Mercury

CHEMetrics Chemets Self-Filling Ampoules - For Oxygen Testing



**13-299-201** - Each for \$50.63  
 Kit, Test; Chemets; CHEMetrics; Provide results in two minutes or less; Analyte: Dissolved Oxygen; Testing Range: 0-1ppm; Analytical Method: Rhodazine D; Complete Test Kit  
**13-299-201A** - Pack of 30 for \$24.45  
 Dissolved Oxygen; Testing Range: 0-1ppm; Analytical Method: Rhodazine D; Refil Ampule  
**13-299-202** - Each for \$59.29  
 Dissolved Oxygen; Testing Range: 0-40ppb; Analytical Method: Rhodazine D; Complete Test Kit  
**13-299-202A** - Pack of 30 for \$36.50  
 Dissolved Oxygen; Testing Range: 0-40ppb; Analytical Method: Rhodazine D; Refil Ampule

- 13-299-200** - Each for \$50.63  
Dissolved Oxygen; Testing Range: 1-12ppm; Analytical Method: Indigo Carmine; Complete Test Kit
- 13-299-200B** - Pack of 30 for \$24.81  
Dissolved Oxygen; Testing Range: 1-12ppm; Analytical Method: Indigo Carmine; Refil Ampule
- 13-299-203** - Each for \$57.69  
Dissolved Oxygen; Testing Range: 0-100ppb; Analytical Method: Rhodazine D; Complete Test Kit

### Interlab Polyseed BOD and Polyseed-NX CBOD Capsules



- 13-297-200** - Pack of 50 for \$109.62  
Water Testing Supplies; BOD Analysis; Polyseed Capsules; Yield: up to 200 tests; Each capsule contains 100mg of specialized bacterial cultures for use in a broad range of areas involving degradation of industrial and municipal waste
- 13-297-201** - Pack of 50 for \$146.16  
Polyseed NX Capsules

### Kimax Glass Imhoff Sediment Cone



- 10-310-52** - Case of 1 for \$191.78  
Cone, Imhoff Sediment; Kimax; 1L; Graduations: 0 to 2mL (in 0.1mL subdivisions); 2 to 10mL (in 0.5mL); 10 to 40mL (in 1.0mL); and at 1000mL

### Kimax-35 300mL BOD Bottles



- 02-885A** - Case of 24 for \$270.24  
Bottles; BOD; Type I Borosilicate Glass; Kimax; With Stopper; Unnumbered; Dia. x H: 2-3/4 x 6-1/2 in.; neck I.D. approx. 2/3 in; For sampling, incubation of aqueous samples for biochemical oxygen demand (BOD) analysis
- 02-885B** - Case of 24 for \$281.52  
With Stopper; No. Sequence: 01-24
- 02-885C** - Case of 24 for \$283.92  
With Stopper; No. Sequence: 25-48
- 02-940-1A** - Case of 24 for \$230.17  
With Stopper; No. Sequence: Unnumbered

### LaMotte Series 1200 Colorimeter Single-Test Kits - For Oxygen Testing



- 22-307-857** - Each for \$47.50  
Colorimeter; Series 1200; LaMotte; Single-parameter; Water-resistant, handheld single-parameter meters; Analyte: Dissolved Oxygen; Range (ppm): 0-10; Method: Direct Reading Titrator Liquid
- 22-307-856** - Each for \$47.45  
Analyte: Dissolved Oxygen; Range (ppm): 0-10; Method: Direct Reading Titrator Powder

### Orbeco Model 942 COD Mini Analyst



- 15-398-183** - Each for \$353.99  
Analyzer, Mini; Model 942; Orbeco; COD; Low Range; 5 - 150mg/L
- 15-398-184** - Each for \$353.99  
Mid Range; 20 - 900mg/L

### Orbeco-Hellige COD Tube Tests



- 09-053-272** - Each for \$30.00  
Reagent, Colorimeter; Tube Test; COD; 0-150mg/L; 25 Tests
- 09-053-273** - Each for \$30.00  
0-1500mg/L
- 09-054-105** - Each for \$30.00  
0-15,000mg/L

### Thermo Scientific Orion 5-Star pH/ISE/ORP/DO/Conductivity Benchtop Meter - For Oxygen Testing



- 13-642-058** - Each for \$1315.80  
Meter, Electrochemistry, Benchtop Multiparameter, Orion 5-Star; Meter Only; -2 to +19pH, +/-1999mV. 0 to 90mg/L DO, 0 to 19,900 mg/L/M/%/ppb ranges; Includes meter, CFR Part II software, power supply, manual

### Thermo Scientific Orion Dissolved Oxygen/BOD Probe



- 13-299-80** - Each for \$1029.00  
Electrode, Dissolved Oxygen/BOD Probe, Orion; Permits DO/BOD measurement from 0 to 14ppm +/-0.05ppm/2% of reading with any pH meter; Polarographic sensor; U.S. Standard connector

### Thermo Scientific Precision Large-Capacity Incubators



- 11-679-69** - Each for \$8024.00  
Incubator; Precision; Thermo Scientific; 30 cu. ft. (849.5L) chamber volume; Operating range from 5 deg. C above ambient to 70 deg. C, with +/-0.5 deg. C uniformity at 37 deg. C; Door: Glass
- 11-679-68** - Each for \$7563.00  
Model 30M; Solid Door
- 11-679-70** - Each for \$8962.00  
Model 30MR; Glass Door
- 11-679-71** - Each for \$8558.00  
Model 30MR; Solid Door

Thermo Scientific Revco BOD Refrigerated Incubators



- 13-990-117** - Each for \$6175.00  
Incubator, Refrigerated; Revco; Programmable; Temp. range: 0 - 50 deg. C; Chamber capacity: 20.0 cu.ft.; 300mL BOD Bottle Capacity: >400; 4 shelves; CFC free; Manual defrost
- 13-990-203** - Each for \$4890.00  
Nonprogrammable; Capacity: 20 cu.ft.
- 13-990-204** - Each for \$3703.00  
Nonprogrammable; Capacity: 6.1 cu.ft.

Thermo Scientific Revco BOD Refrigerated Incubator Temperature Recorder



- 13-990-116** - Each for \$83.92  
Paper, Chart; For Revco BOD Refrigerated Incubator Temperature Recorder; Packs of 50 charts
- 13-990-115** - Each for \$1762.90  
Temperature Recorder, 115v 60hz

Wheaton BOD Bottles with Stoppers



- 02-926-13** - Case of 36 for \$658.47  
Bottle; BOD; Wheaton; Permanent Marking Area; Shoulder radius sweeps all air from inside bottle while filling; Capacity: 60mL; Closure: Robotic Stopper; No. Sequence: 1-36
- 02-926-14** - Case of 36 for \$658.47  
Capacity: 60mL; Closure: Robotic Stopper; No. Sequence: 37-72
- 02-926-15** - Case of 36 for \$658.47  
Capacity: 60mL; Closure: Robotic Stopper; No. Sequence: 73-108
- 02-926-12** - Case of 36 for \$561.78  
Capacity: 60mL; Closure: Robotic Stopper; No. Sequence: Unnumbered
- 02-926-8** - Case of 24 for \$270.41  
Capacity: 300mL; Closure: Pennyhead Stopper; No. Sequence: 1-24
- 02-926-9** - Case of 24 for \$270.41  
Capacity: 300mL; Closure: Pennyhead Stopper; No. Sequence: 25-48
- 02-926-11** - Case of 24 for \$270.41  
Capacity: 300mL; Closure: Pennyhead Stopper; No. Sequence: 49-72
- 02-926-25** - Case of 24 for \$270.41  
Capacity: 300mL; Closure: Pennyhead Stopper; No. Sequence: 73-96
- 02-926-90** - Case of 24 for \$270.41  
Capacity: 300mL; Closure: Pennyhead Stopper; No. Sequence: 97-120
- 02-926-91** - Case of 24 for \$270.41  
Capacity: 300mL; Closure: Pennyhead Stopper; No. Sequence: 121-144
- 02-926-92** - Case of 24 for \$270.41  
Capacity: 300mL; Closure: Pennyhead Stopper; No. Sequence: 145-168
- 02-926-93** - Case of 24 for \$270.41  
Capacity: 300mL; Closure: Pennyhead Stopper; No. Sequence: 169-192
- 02-926-94** - Case of 24 for \$270.41  
Capacity: 300mL; Closure: Pennyhead Stopper; No. Sequence: 193-216
- 02-926-95** - Case of 24 for \$270.41  
Capacity: 300mL; Closure: Pennyhead Stopper; No. Sequence: 217-240
- 02-926-96** - Case of 24 for \$270.41  
Capacity: 300mL; Closure: Pennyhead Stopper; No. Sequence: 241-264
- 02-926-7A** - Case of 24 for \$259.14  
Capacity: 300mL; Closure: Pennyhead Stopper; No. Sequence: Unnumbered
- 02-926-27** - Case of 24 for \$270.41  
Capacity: 300mL; Closure: Robotic Stopper; No. Sequence: 1-24
- 02-926-28** - Case of 24 for \$270.41  
Capacity: 300mL; Closure: Robotic Stopper; No. Sequence: 25-48

- 02-926-29** - Case of 24 for \$270.41  
Capacity: 300mL; Closure: Robotic Stopper; No. Sequence: 49-72
- 02-926-30** - Case of 24 for \$270.41  
Capacity: 300mL; Closure: Robotic Stopper; No. Sequence: 73-96
- 02-926-31** - Case of 24 for \$270.41  
Capacity: 300mL; Closure: Robotic Stopper; No. Sequence: 97-120
- 02-926-32** - Case of 24 for \$270.41  
Capacity: 300mL; Closure: Robotic Stopper; No. Sequence: 121-144
- 02-926-33** - Case of 24 for \$270.41  
Capacity: 300mL; Closure: Robotic Stopper; No. Sequence: 145-168
- 02-926-34** - Case of 24 for \$270.41  
Capacity: 300mL; Closure: Robotic Stopper; No. Sequence: 169-192
- 02-926-35** - Case of 24 for \$270.41  
Capacity: 300mL; Closure: Robotic Stopper; No. Sequence: 193-216
- 02-926-36** - Case of 24 for \$270.41  
Capacity: 300mL; Closure: Robotic Stopper; No. Sequence: 217-240
- 02-926-37** - Case of 24 for \$270.41  
Capacity: 300mL; Closure: Robotic Stopper; No. Sequence: 241-264
- 02-926-38** - Case of 24 for \$270.41  
Capacity: 300mL; Closure: Robotic Stopper; No. Sequence: 265-288
- 02-926-39** - Case of 24 for \$270.41  
Capacity: 300mL; Closure: Robotic Stopper; No. Sequence: 289-312
- 02-926-40** - Case of 24 for \$270.41  
Capacity: 300mL; Closure: Robotic Stopper; No. Sequence: 313-336
- 02-926-41** - Case of 24 for \$270.41  
Capacity: 300mL; Closure: Robotic Stopper; No. Sequence: 337-360
- 02-926-42** - Case of 24 for \$270.41  
Capacity: 300mL; Closure: Robotic Stopper; No. Sequence: 361-384
- 02-926-43** - Case of 24 for \$270.41  
Capacity: 300mL; Closure: Robotic Stopper; No. Sequence: 385-408
- 02-926-44** - Case of 24 for \$270.41  
Capacity: 300mL; Closure: Robotic Stopper; No. Sequence: 409-432
- 02-926-26** - Case of 24 for \$259.14  
Capacity: 300mL; Closure: Robotic Stopper; No. Sequence: Unnumbered

Yellow Springs Instrument Benchtop Models 5000 and 5100 Dissolved Oxygen Meters



- 13-298-21** - Each for \$1195.00  
Meter, Benchtop Dissolved Oxygen/Temperature, YSI; Model 5000; Microprocessor, menu-driven; graphic LCD; 100 datapoints, RS-232-C; Ranges: 0 to 60mg/L, 0 to 600% saturation; -5.00 to +50.00 deg. C; Includes batteries, 115VAC power supply.
- 13-298-22** - Each for \$1575.00  
Model 5100

Yellow Springs Instrument BOD Analyst Software

- 02-681-448** - Each for \$306.91  
YSI BOD Analyst Software. Windows software for automated 5-day BOD calculations. Works with YSI 52, 5000 and 5100 Dissolved Oxygen Instruments.

Yellow Springs Instrument Detachable Cables for 5739 Field Oxygen/Temp Probe

- 13-299-40** - Each for \$195.00  
Cable; Yellow Springs Instrument; Detachable Cables for 5739 Field Oxygen/Temp Probe; Cable Length: 10 ft.
- 13-299-46** - Each for \$235.00  
Cable Length: 25 ft.
- 13-299-1** - Each for \$298.42  
Cable Length: 50 ft.
- 13-299-48** - Each for \$353.27  
Cable Length: 100 ft.
- 13-299-52** - Each for \$479.05  
Cable Length: 200 ft.

### Yellow Springs Instrument Model 5239 Field Oxygen/Temperature Probe with Cable

**13-398-87** - Each for \$501.13

Electrode, Probe; Field/O<sub>2</sub> Temperature; Model 5239; Weighted plastic body w/heavy-duty guard; Auto temp and pressure compensation; For use with YSI 5000, 5100, 52, 58 meters; Includes one 10 ft. cable

**13-398-88** - Each for \$536.00

Model 5239; with 20 ft. cable

**13-298-89** - Each for \$580.00

Model 5239; with 50 ft. cable

### Yellow Springs Instrument Model 55 Handheld Dissolved Oxygen Meter



**13-298-56** - Each for \$699.00

Meter, Portable Dissolved Oxygen, YSI; Model 55; Ranges: 0 to 20mg/L DO (+/-0.3mg/L); 0 to 200% air saturation (+/-2%); -5 to +45 deg. C; Includes ABS plastic case, probe, 12 ft. Cable; Requires 6 AA batteries; 2-1/2" x 3-1/2" W x 9-1/2" in. H

**13-298-57** - Each for \$735.00

With 25 ft. cable

**13-298-62** - Each for \$800.00

With 50 ft. cable

### Yellow Springs Instrument Model 550A Dissolved Oxygen Meter



**13-298-118** - Each for \$795.00

Dissolved Oxygen/Temperature Meter, Yellow Springs Instrument Model 550A; Temperature Range: -5 to +45C; Replaceable Electrode; Handheld; Waterproof; Meter with Probe; Cable length: 12 ft. (3.7m)

**13-298-120** - Each for \$845.00

Meter with Probe; Cable length: 25 ft. (7.6m)

**13-298-122** - Each for \$895.00

Meter with Probe; Cable length: 50 ft. (15.2m)

**13-298-116** - Each for \$945.00

Meter with Probe; Cable length: 100 ft. (30.5m)

**13-298-119** - Each for \$875.00

Meter with Probe and Carrying Case; Cable length: 12 ft. (3.7m)

**13-298-121** - Each for \$925.00

Meter with Probe and Carrying Case; Cable length: 25 ft. (7.6m)

**13-298-123** - Each for \$975.00

Meter with Probe and Carrying Case; Cable length: 50 ft. (15.2m)

**13-298-117** - Each for \$1025.00

Meter with Probe and Carrying Case; Cable length: 100 ft. (30.5m)

### Yellow Springs Instrument Model 5739 Field Oxygen/Temperature Probe



**13-299-43** - Each for \$305.00

Electrode, Probe; Field/O<sub>2</sub> Temperature; Model 5739; Plastic body w/built-in sinker weight; Auto temp and pressure compensation; For use with YSI 5000/5100 meters; Includes one membrane/KCl kit; Without cable (required)

### Yellow Springs Instrument Model 5750 Nonstirring BOD Probe for Dissolved Oxygen Meters

**13-298-80** - Each for \$352.18

Probe, Nonstirring; BOD bottle probe senses dissolved oxygen and temperature; Includes: Membrane/KCl Kit 5775 found in Probe Service Kits

### Yellow Springs Instrument Model 58 Portable Dissolved Oxygen Meter



**13-298-58** - Each for \$1795.00

Dissolved Oxygen Meter, YSI Model 58; Portable; Range, 0 to 20mg/L (ppm) or 0 to 200% air saturation; Accuracy: +/-0.03mg/L, +/-0.3%; For measuring supersaturated water; Displays oxygen concentrations in two temperature-compensated mode; LCD

### Yellow Springs Instrument Model 5905 Self-Stirring BOD Probe for Dissolved Oxygen



**13-298-76** - Each for \$645.00

Electrode, Probe; BOD; For YSI Model 5905 dissolved O<sub>2</sub> meter; Self-stirring; Rapid temperature changes in less than 30 sec.; Compatible with 300mL BOD bottles; With 6 membranes, KCL solution

### Yellow Springs Instrument Model 85 Handheld Dissolved Oxygen/Conductivity Meter



**13-298-24** - Each for \$1275.00

Meter, Oxygen/Conductivity; Model 85; Yellow Springs Instrument; Includes: Combination probe; Membrane caps; Probe solution; and case; Cable Length: 10 ft.

**13-298-25** - Each for \$1295.00

Cable Length: 25 ft.

**13-298-26** - Each for \$1450.00

Cable Length: 50 ft.

**13-298-27** - Each for \$1435.00

Cable Length: 100 ft.

### Yellow Springs Instrument Probe Adapter Cable for Models 5000 and 5100 Dissolved Oxygen Meters

**13-299-78** - Each for \$78.39

Adapter, Cable; Yellow Springs Instrument; Probe adapter cable for models 5000 and 5100 dissolved oxygen meters

### Yellow Springs Instrument Probe Service Kits for Yellow Springs Instrument Dissolved Oxygen Probes

**13-298-82** - Pack of 10 for \$90.52

Kit, Service; Yellow Springs Instrument; Service kit for replenishing oxygen sensor on YSI Dissolved Oxygen Probes; Standard Membrane Kit

**13-298-83** - Pack of 10 for \$71.76

High-sensitivity Membrane Kit

**13-299-16** - Each for \$26.15

Standard Membrane/KCl Kit

**13-299-32** - Each for \$28.17

High-sensitivity Membrane/KCl Kit

**Yellow Springs Instrument Replacement Electrode for Models 550 and 550A Dissolved Oxygen Meters**

**13-298-63** - Each for \$160.01  
Electrode; Dissolved O<sub>2</sub>; Replacement; For YSI 550A DO meter

**Yellow Springs Instrument Self-stirring BOD Probes for Models 5000 and 5100 Dissolved Oxygen Meters**

**15-176-20** - Each for \$1046.00  
Electrode, Self-Stirring BOD, YSI; Model 5010; Plugs directly into Meters 5000 and 5100, uses meter power supply; Creates consistent flow past membrane; Includes 6-3/4 in. (17cm) shaft for use in wine industry, 6 membrane caps, KCl solution  
**15-176-17** - Each for \$726.00  
Includes adapter with 5 deg. Taper, 4-1/4 in. Paddle  
**15-176-18** - Each for \$625.00  
Includes Standard Taper 24 funnel, 4-1/4 in. Paddle  
**13-298-23** - Each for \$595.00  
Stir paddle size: 3-1/4 in

**pH/pX (including ISE and ORP)**

**Fisher Scientific accuCap Capillary Junction pH Combination Electrodes**



**13-620-131** - Each for \$321.80  
Electrode, pH Combination, Fisher Scientific accuCap; Capillary reference junction; Glass body, Gel-filled; 130mmL, 12mm dia.; 0 to 14pH; 0 to 80 deg. C; BNC connector  
**13-620-132** - Each for \$177.58  
pH Combination Electrode, accuCap; Capillary reference junction; Plastic Body, Gel filled, BNC connector  
**13-620-133** - Each for \$266.42  
pH Combination Electrode, accuCap; Capillary reference junction; Spear Tip, Plastic Body, Gel filled, BNC connector  
**13-620-130** - Each for \$377.14  
pH Combination, accuCap; Capillary reference junction; Glass Body Refillable, BNC connector

**Fisher Scientific accuFet Solid-State pH/ATC Combination Electrodes**



**13-620-755** - Each for \$481.94  
Electrode, pH/ATC Combination; Fisher Scientific accuFet; Solid state; DIN Connector; pH range: 0 to 14; For discontinued BASIC benchtop meters

**Fisher Scientific accuFet XL Solid-State pH Combination Electrodes**



**13-620-700** - Each for \$664.70  
Electrode, ISFET pH Solid State Combination, Fisher Scientific accuFet XL; Polyetherimide (PEI) Body; Gel-Filled; Ag/AgCl reference; Cone Tip; 160mmL, 10mm dia.; 0 to 14pH; -5 to 105 deg. C; DIN Connector for accumet XL Series meters  
**13-620-710** - Each for \$659.26  
Cup Tip  
**13-620-720** - Each for \$719.06  
Flat Tip

**13-620-730** - Each for \$727.21  
Lance Tip

**Fisher Scientific accuFlow Flushable Junction pH Combination Electrodes**



**13-620-109** - Each for \$201.93  
Electrode, pH Combination, Fisher Scientific accuFlow; Flushable Junction, Double-junction Ag/AgCl reference; Polymer body, refillable, 175mmL, 12mm dia.; 0 to 14pH; 0 to 100 deg. C; BNC connector.  
**13-620-116** - Each for \$328.07  
pH Combination, accuFlow Junction, accuHast reference, BNC connector.  
**13-620-117** - Each for \$378.57  
pH/ATC Combination, accuFlow Junction, accu-pHast reference; BNC/mini-phone connectors  
**13-620-110** - Each for \$239.76  
pH/ATC combination, Ag/AgCl double junction, BNC/mini-phone connectors

**Fisher Scientific accumet AP71 and AP72 pH/mV/ Temperature Meters**



**13-636-AP71A** - Each for \$595.50  
Meter, Electrochemistry, Fisher Scientific accumet AP71 pH/mV/ deg. C Meter Only; Dual LCD; -2.00 to +16.00pH, +/-2000mV, 0.0 to 100.0 deg. C; ATC; Recognizes 5 pH buffers; 5 calibration points; 16-reading memory; IP67  
**13-636-AP71** - Each for \$690.78  
Model AP71 Meter and Kit  
**13-636-AP72** - Each for \$756.27  
AP72 Meter Kit

**Fisher Scientific accumet AP84 Portable pH/Dissolved Oxygen Meter**



**13-636-AP84A** - Each for \$1319.77  
Meter, Electrochemistry, Fisher Scientific accumet AP84 pH/DO/ deg. C/F Meter/Probe; Dual LCD; -2.00-- +16.00pH, 0.00-- 20.00mg/L, 0.0% sat.; 0.0-- 50.0 deg. C/32-- 122 deg. F; 5 pH/2 DO cal.pts; time/date stamp; 50-reading memory; IP67  
**13-636-AP84** - Each for \$1445.45  
Meter Kit

**Fisher Scientific accumet AP85 Portable pH/Conductivity Meter**



**13-636-AP85** - Each for \$1042.12  
Meter Kit, pH; Fisher Scientific accumet AP85; Includes conductivity cell/temperature probe; pH/ATC electrode, pH buffers; Reads pH/conductivity/TDS/ deg. C/ deg. F; +/-0.01 pH accuracy; +/-1% FS Cond/Tds Accuracy; Autoranging; Dual display  
**13-636-AP85A** - Each for \$964.70  
Meter and Probe



### Fisher Scientific accumet Basic AB15 Basic and BioBasic Meters



- 13-636-AB15C** - Each for \$1012.09  
Meter, Electrochemistry, AB15 pH/mV/deg. C, Fisher Scientific accumet; Meter Only with NIST-Traceable Certificate; -1.99 to +19.99pH range, 0.1/0.01pH resolution
- 13-636-AB15A** - Each for \$664.46  
AB15 Meter Only
- 13-636-AB15B** - Each for \$875.89  
AB15 Meter BioKit
- 13-636-AB15** - Each for \$839.65  
AB15 Meter/pH Kit

### Fisher Scientific accumet Basic AB15 Plus Basic and BioBasic Meters



- 13-636-AB15PC** - Each for \$1285.17  
Meter, Electrochemistry, AB15 Plus pH/mV/deg. C, Fisher Scientific accumet; Meter Only; NIST-Traceable Certificate; -1.999 to +19.999pH range, 0.1/0.01/0.001pH resolution.
- 13-636-AB15P** - Each for \$1111.48  
pH Meter Kit
- 13-636-AB15PA** - Each for \$936.30  
Meter only
- 13-636-AB15PB** - Each for \$1147.73  
Meter BioKit
- 13-636-15PAC** - Each for \$1117.80  
Meter Only; NIST-Traceable
- 13-636-15PBC** - Each for \$1325.30  
Meter BioKit; NIST-Traceable

### Fisher Scientific accumet Combination Gas-Sensing ISEs



- 13-620-511** - Each for \$614.03  
Electrode, Ion Selective, Carbon Dioxide Gas-Sensing Combination, Fisher Scientific accumet; Epoxy body, 0.440 to 1320ppm range, 0 to 50 deg. C operating range, 4.5pH; 102mmL, 13mm dia.; BNC connector
- 13-620-509** - Each for \$547.40  
Ion Selective, Ammonia Gas-Sensing Combination Electrode; BNC connector
- 13-620-508** - Each for \$547.40  
Ion Selective, Ammonia Gas-Sensing Combination Electrode; U.S. Standard/pin connectors

### Fisher Scientific accumet Combination Polymer Membrane ISEs



- 13-620-532** - Each for \$605.47  
Electrode, Ion Selective, Potassium Polymer Membrane Combination, Fisher Scientific accumet; Epoxy body, 0.04 to 39,000ppm range, 0 to 40 deg. C operating range, 2.5 to 11pH range; 102mmL, 13mm dia.; BNC connector
- 13-620-535** - Each for \$613.40  
Nitrate Polymer Membrane Combination ISE; U.S. Standard/pin connectors
- 13-620-534** - Each for \$613.40  
Nitrate Polymer Membrane Combination ISE; ZBNC connector

### Fisher Scientific accumet Dual Platinum Pin KF Titration Electrode



- 13-620-123** - Each for \$241.73  
Electrode, Titration; Fisher Scientific accumet; For use with Fisher Scientific KF Titrimeter; Sulfur Analyzer, pH meters having -10uA KF polarizing output; Covers -5 to +100 deg. C range

### Fisher Scientific accumet Dual Platinum Plate Combination Titration Electrode



- 13-620-149** - Each for \$265.06  
Electrode, Titration; Fisher Scientific accumet; Dual platinum plate combination; For chlorine titrations; Covers 10-80 deg. C range; 4-1/2 in.L; Requires pin-jack adapter for use w/U.S. standard inputs; Dual pin connectors

### Fisher Scientific accumet Epoxy Body Ag/AgCl ISE Reference Electrodes



- 13-620-47** - Each for \$226.28  
Electrode, ISE/pH Reference; Fisher Scientific accumet; Single-Junction; Inner body w/4M KCl electrolyte, saturated with AgCl; Outer body uses sample-compatible electrolyte; Removable cap
- 13-620-46** - Each for \$182.21  
Single junction

Fisher Scientific accumet Epoxy Body Calomel Reference Electrodes



**13-620-259** - Each for \$135.18  
Electrode, Calomel Reference; Fisher Scientific accumet; Porous polymer junction; Filled for gelled KCl electrolyte; Never needs refilling; 30 in. cable.  
**13-620-258** - Each for \$133.23  
Liquid-filled

Fisher Scientific accumet Excel XL50 pH/mV/Temperature/ISE/Conductivity Meter



**13-636-XL50A** - Each for \$2423.70  
Meter, Electrochemistry; Fisher Scientific accumet Excel XL 50; Modes: pH/mV/ISE/Conductivity/Resistivity/Temperature; 1x10sup-6 to 9.99x10sup10 ISE, -2 to +20pH, 0 to +/-2000mV, 0 to 5x10sup5 microSiemens/cm conductivity ranges  
**13-636-XL50** - Each for \$2698.76  
Meter Kit  
**13-636-XL50AC** - Each for \$2613.11  
Meter Only; NIST-Traceable  
**13-636-XL50C** - Each for \$2896.25  
Meter Kit; NIST-Traceable

Fisher Scientific accumet Excel XL60 pH/mV/Temperature/DO/ISE/Conductivity Meter - For pH Testing



**13-636-XL60** - Each for \$3094.72  
Meter Kit; Conductivity; Fisher Scientific accumet Excel XL60 pH/mV/DO/ISE/Conductivity/Resistivity/Temperature  
**13-636-XL60A** - Each for \$2823.90  
Meter only  
**13-636-XL60C** - Each for \$3303.85  
accumet XL60 Meter Kit/pH-Conductivity with NIST-Traceable Certificate: includes meter, accuCap Combination pH Electrode 13-620-130; ATC probe 13-620-19; electrode support; manual; 110/220V power supply  
**13-636-XL60DC** - Each for \$3999.53  
accumet XL60 Meter Kit/pH-DO with NIST-Traceable Certificate: includes meter, accuCap Combination pH Electrode 13-620-130; DO Probe 13-620-SSP, ATC probe 13-620-19; electrode support; manual; 110/220V power supply  
**13-636-XL60AC** - Each for \$3025.08  
accumet XL60 Meter Only with NIST-Traceable Certificate: includes meter, electrode support, manual, 110/220V power supply

Fisher Scientific accumet Excel XL15 pH/mV/Temperature Meter



**13-636-XL15A** - Each for \$1284.72  
Meter, pH/mV/Temperature; Fisher Scientific accumet Excel XL15; -2 to +20pH; 0 to +/-2000mV range; Includes meter, electrode support arm and bracket, 110/220V power supply and operation manual  
**13-636-XL15** - Each for \$1460.94  
Meter Kit  
**13-636-XL15AC** - Each for \$1440.63  
Meter Only; NIST-Traceable  
**13-636-XL15C** - Each for \$1622.04  
Meter Kit; NIST-Traceable

Fisher Scientific accumet Excel XL20 pH/mV/Temperature/Conductivity/Resistivity Meter



**13-636-XL20A** - Each for \$1815.86  
Meter, Electrochemistry, pH/mV/Conductivity/Resistivity/Salinity/Temperature, Fisher Scientific accumet; XL20 Meter Only; -2 to +20pH, 0 to +/-2000mV, 0 to 5x10E5 microSiemens/cm conductivity ranges  
**13-636-XL20C** - Each for \$2248.77  
accumet XL20 Meter Kit/pH with NiST-Traceable Certificate: includes meter, accuCap Combination pH Electrode 13-620-130; ATC probe 13-620-19; electrode support; manual; 110/220V power supply  
**13-636-XL20AC** - Each for \$1987.38  
accumet XL20 Meter Only with NiST-Traceable Certificate: includes meter, electrode support, manual, 110/220V power supply

Fisher Scientific accumet Gas Sensing ISE Membrane Caps

**13-620-512** - Pack of 3 for \$127.39  
Membrane Cap, Fisher Scientific accumet Electrode Accessory, For Ammonia Gas-Sensing Combination ISEs, 12mm dia.

Fisher Scientific accumet Gel-Filled Paper Pulp pH Combination Electrodes



**13-620-299** - Each for \$145.91  
Electrodes, pH Combination; Fisher Scientific accumet; Paper pulp double junction; Polymer Body Gel-Filled; 39 in. lead; BNC Connector

Fisher Scientific accumet Excel XL25 pH/mV/Temperature/ISE Meter



**13-636-XL25A** - Each for \$1815.86  
Meter, Electrochemistry, pH/mV/ISE/Temperature, Fisher Scientific accumet; XL25A Meter Only; 1 x 10sup-6 to 9.99 x 10E10 ISE, 0 to +20pH, 0 to +/-2000mV ranges  
**13-636-XL25** - Each for \$2069.76  
XL25 Meter Kit; With electrode, probe, electrode support  
**13-636-XL25C** - Each for \$2248.77  
accumet XL25 Meter Kit/pH: includes meter, accuCap combination pH electrode 13-620-130; ATC probe 13-620-19; electrode support; manual; 110/220V power supply:  
**13-636-XL25AC** - Each for \$1987.38  
accumet XL25 Meter Only with NIST-Traceable Certificate: includes meter, electrode support; manual; 110/220V power supply

### Fisher Scientific accumet Gel-Filled Pencil-Thin pH Combination Electrodes



**13-620-290** - Each for \$175.47  
Electrodes, pH Combination; Fisher Scientific accumet; Epoxy body; Gel-filled; Pencil thin; Ag/AgCl reference; Polymer single junction; 30 in lead; BNC connector

### Fisher Scientific accumet Glass Body Ag/AgCl Reference Electrodes



**13-620-273** - Each for \$211.88  
Electrode, Ag/AgCl Reference; Fisher Scientific accumet; High Temperature Reference; Glass Body; Double-Junction; 4M KCl electrolyte saturated with AgCl (inner body).  
**13-620-53** - Each for \$125.48  
Single-Junction High Temperature Ag/AgCl Reference  
**13-620-216** - Each for \$121.78  
Single-Junction High Temperature Ag/AgCl Reference for Silver and Chloride Titrations  
**13-620-45** - Each for \$127.80  
Single-Junction High Temperature Ag/AgCl Reference with Side Arm

### Fisher Scientific accumet Gel-Filled pH/ATC Double-Junction Combination Electrodes



**13-620-111** - Each for \$247.35  
Electrode; pH/ATC; Fisher Scientific accumet; Gel-filled; Ag/AgCl reference; Double-Junction; Pencil thin epoxy body; 106mm L; 10mm dia.; BNC/Mini-phone ATC connector; For basic AB15/15plus, XL and AR Series, disc. 1000, BASIC models  
**13-620-112** - Each for \$260.63  
Double-junction Ag/AgCl reference; BNC/ in. Phone ATC connectors for discontinued accumet 5, 10, 15, 20, 25, 30, 50 benchtop meters.

### Fisher Scientific accumet Glass Body Calomel Reference Electrodes



**13-620-79** - Each for \$117.57  
Electrode, Calomel Reference; Fisher Scientific accumet; Contains Mercury; Miniature Glass Body; 2-1/2 in.L (6.4cm)  
**13-620-61** - Each for \$140.36  
Standard Size Glass Body; High Flowrate; Reverse Sleeve Junction; 30 in. (72.cm) lead.  
**13-620-62** - Each for \$140.37  
Standard Size Glass Body; High Flowrate; Sleeve Junction; 30 in. (72.cm) lead.  
**13-620-57** - Each for \$140.35  
Standard Size Glass Body; Low Flowrate; Dri-Pak, with 50mL of saturated KCl. 30 in. (76.2cm) lead.  
**13-620-52** - Each for \$122.45  
Standard-Size Glass Body; 30 in. (76.2cm) lead.  
**13-620-64** - Each for \$135.18  
Standard-Size Glass Body; 60 in. (152cm) lead for Fisher Titralyzer II.  
**13-620-51** - Each for \$122.45  
Standard-Size Glass Body; Dri-Pak, with 50mL of saturated KCl. 30 in. (76.2cm) lead.

### Fisher Scientific accumet Gel-Filled Polymer Body Single-Junction pH Combination Electrodes



**13-620-108** - Each for \$119.65  
Electrode; pH Combination; Fisher Scientific accumet; Gel filled; Single junction; Ag/AgCl reference; 0 to 14pH range, -5 to +80 deg C; Polypropylene body; 106mm L; 10mm dia.; BNC connector  
**13-620-104** - Each for \$117.36  
pH Combination; U.S. standard pin connector

### Fisher Scientific accumet Glass Body Standard Size Combination Electrodes



**13-620-223** - Each for \$188.91  
Electrode, pH Combination, Fisher Scientific accumet; Double-junction, Ag/AgCl reference; Glass body refillable, , refillable, 106mmL, 10mm dia.; 0 to 14pH; -5 to +100 deg C; BNC Connector  
**13-620-285** - Each for \$190.00  
pH Combination, accumet; Single-Junction Ag/AgCl reference; BNC Connector  
**13-620-286** - Each for \$189.96  
pH Combination, accumet; Single-Junction, Calomel reference; BNC Connector

Fisher Scientific accumet Glass Membrane Sodium Combination ISE



**13-620-503** - Each for \$498.59  
 Electrode, Sodium Combination ISE; Epoxy Body; BNC connector; 0 to 14pH Range; Applications: Determine sodium in meats, fish, dairy products, fruit juices, brewing water, ground /sea water, soils, pulp and paper monitoring

Fisher Scientific accumet Liquid-Filled pH/ATC Epoxy Body Combination Electrodes



**13-620-530** - Each for \$168.89  
 Electrode, pH/ATC Single-Junction Combination; Fisher Scientific accumet; Ag/AgCl Reference; Liquid-Filled; 0 to 14pH, -5 to +100 deg C ranges; Epoxy body; 106mmL; 12mm dia.; BNC/Mini-phone ATC connectors  
**13-620-531** - Each for \$181.99  
 pH/ATC Combination, accumet; Single-Junction, Calomel Reference; BNC/Mini-phone ATC connectors

Fisher Scientific accumet Glass Membrane Sodium Half Cell ISE



**13-620-501** - Each for \$373.65  
 Electrode; Sodium Half Cell; Fisher Scientific accumet; Glass Membrane; Low drift, fast response, high selectivity ratio, good thermal stability and wide operating range; Connector: BNC  
**13-620-500** - Each for \$373.65  
 Connector: U.S. Standard

Fisher Scientific accumet Liquid-Filled Polymer Body pHCombination Electrodes



**13-620-221** - Each for \$168.47  
 Electrode, pH Combination; Fisher Scientific accumet; Double-Junction Ag/AgCl reference; Polypropylene body, refillable, 106mmL, 10mm dia.; 0 to 14pH; -5 to +100 deg C; BNC connector  
**13-620-300** - Each for \$177.25  
 Single junction; Calomel reference; BNC connector  
**13-620-287** - Each for \$147.44  
 Single-Junction Ag/AgCl reference; BNC connector

Fisher Scientific accumet Liquid-Filled pH Epoxy Body Combination Electrodes



**13-620-288** - Each for \$176.67  
 Electrode, pH Combination; Fisher Scientific accumet; Calomel Reference, Single-Junction; Epoxy body; Liquid-Filled; Tris compatible; 0 to 14pH, -5 to +80 deg C ranges; 106mmL, 10mm dia.; BNC connector  
**13-620-289** - Each for \$214.43  
 pH Single-Junction Flat Surface Combination, Ag/AgCl reference; BNC connector

Fisher Scientific accumet Micro and Semimicro Size Glass Combination Electrodes



**13-620-292** - Each for \$224.19  
 Electrode, Combination; Fisher Scientific accumet; Extra-Long Ag/AgCl; Connector: BNC  
**13-620-293** - Each for \$214.14  
 Extra-Long Calomel; Connector: BNC  
**13-620-95** - Each for \$313.87  
 MicroTip Calomel; Length: 10 in.; Connector: BNC  
**13-620-96** - Each for \$284.26  
 MicroTip Calomel; Length: 20 in.; Connector: BNC  
**13-620-94** - Each for \$225.91  
 Miniature Ag/AgCl; Connector: U.S. Standard  
**13-620-291** - Each for \$224.19  
 Standard Ag/AgCl; Connector: BNC

### Fisher Scientific accumet pH Indicating Epoxy Body Glass Membrane Models



**13-620-294** - Each for \$128.69  
Electrode, Indicating; Fisher Scientific accumet;  
Connector: BNC; Lead: 30 in. (76.2cm); Suggested  
Reference Electrodes: 13-620-258, 13-620-259

### Fisher Scientific accumet Platinum Half Cell Electrode for ORP Measurements



**13-620-115** - Each for \$199.40  
Electrode, Platinum Pin Indicating Half-Cell, Fisher  
Scientific accumet; Glass Body, Platinum Element, Large  
Surface Area; For ORP/Redox measurements; 140mmL,  
10mm dia.; -5 to 100 deg. C; Pin connector

### Fisher Scientific accumet pH Indicating Full-Range/High-pH Glass Body Models



**13-620-295** - Each for \$142.33  
Electrode, Indicating; Fisher Scientific accumet;  
Connector: BNC; Lead: 30 in. (76.2cm); Suggested  
Reference Electrodes: 13-620-51, 13-620-52, 13-620-57,  
13-620-61, 13-620-62, 13-620-45, 13-620-53, 13-620-46,  
13-620-47

### Fisher Scientific accumet Platinum ORP Combination Electrode



**13-620-81** - Each for \$316.79  
Electrode, Platinum ORP Combination; Fisher Scientific  
accumet; Ag/AgCl Reference Element; For environmental  
ORP measurements; -5 to +100 deg. C; 140mm long;  
10mm dia.; BNC Connector  
**13-620-82** - Each for \$322.15  
Connector: U.S. Standard

### Fisher Scientific accumet pH Indicating Glass Body Universal Glass Membrane Models



**13-620-284** - Each for \$141.50  
Electrode, pH Indicating; Fisher Scientific accumet; Glass  
body; Universal glass membrane; BNC connector; Lead:  
30 in.; Suggested Reference Electrodes: 13-620-51, -52,  
-57, -61, -62, -45, -53, -46, -47

### Fisher Scientific accumet Silver Billet Indicating Electrode for Silver and Halide Titrations



**13-620-122** - Each for \$191.81  
Electrode, Indicating; Silver Billet; Fisher Scientific  
accumet; Extra-large silver billet half cell; Glass body,  
14cmL; -5 to +100 deg. C temperature range; Body is  
10mm in diameter

Fisher Scientific accumet Solid State Combination ISEs



- 13-620-525** - Each for \$674.78  
Electrode, Ion Selective, Bromide Solid-State Combination, Fisher Scientific accumet; Glass body; 0.4 to 79,000ppm, 0 to 80 deg. C, 2 to 14pH ranges; 108mmL, 13mm dia., BNC connector
- 13-620-527** - Each for \$661.67  
Chloride combination; BNC connector
- 13-620-526** - Each for \$661.67  
Chloride Solid-State Combination ISE; U.S. Standard/Pin connectors
- 13-620-546** - Each for \$741.03  
Cupric Solid-State Combination ISE; BNC connector
- 13-620-547** - Each for \$741.03  
Cupric Solid-State Combination ISE; U.S. Standard/pin connectors
- 13-620-538** - Each for \$518.56  
Cyanide Solid-State Combination ISE; BNC connector
- 13-620-539** - Each for \$518.56  
Cyanide Solid-State Combination ISE; U.S. Standard/pin connectors
- 13-620-528** - Each for \$661.67  
Fluoride Solid-State Combination ISE; U.S. Standard/pin connectors
- 13-620-529** - Each for \$661.67  
Fluoride; BNC connector
- 13-620-549** - Each for \$748.41  
Lead Solid-State Combination ISE; BNC connector
- 13-620-551** - Each for \$688.14  
Silver/Sulfide Solid-State Combination ISE; BNC connector

Fisher Scientific accumet Solid-State Half-Cell ISEs



- 13-620-521** - Each for \$518.55  
Electrode, Ion selective; Fisher Scientific accumet; Bromide half-cell, epoxy body; BNC connector
- 13-620-519** - Each for \$522.80  
Chloride half-cell, epoxy body; BNC connector
- 13-620-523** - Each for \$521.81  
Fluoride half-cell, epoxy body; BNC connector
- 13-620-522** - Each for \$521.81  
Fluoride half-cell, epoxy body; U.S. Standard connector
- 13-620-545** - Each for \$541.86  
Silver/sulfide half cell, epoxy body; BNC connector

Fisher Scientific accupHast R Rugged Variable Temperature pH Combination Electrodes



- 13-620-196** - Each for \$397.40  
Electrode, pH Combination, Fisher Scientific accupHast R Variable Temperature pH; Epoxy Body, refillable, rugged bulb; Fisher Scientific accuFlow flushable junction; 102mmL, 10mm dia; 0 to 14pH; -5 to +100 deg. C; BNC connector
- 13-620-195** - Each for \$351.29  
pH Combination Electrode, accupHast R, Ag/AgCl reference; Glass Body, refillable, BNC connector
- 13-620-197** - Each for \$397.40  
pH Combination, accu-pHast R, Flushable junction, Ag/AgCl reference; Glass Body, refillable, BNC connector

Fisher Scientific accupHast Variable Temperature pH Combination Electrodes



- 13-620-298** - Each for \$324.36  
Electrode, pH Combination, Fisher Scientific accupHast Variable Temperature; Extra-long epoxy Body, refillable; 140mmL, 10mm dia; 0 to 14pH; -5 to +100 deg. C; BNC connector.
- 13-620-296** - Each for \$342.16  
pH Combination Electrode, accupHast, Ag/AgCl reference; Glass Body, refillable; BNC connector
- 13-620-297** - Each for \$432.35  
pH Combination, accupHast, Double junction, Ag/AgCl reference; MicroProbe glass body, refillable, BNC connector
- 13-620-113** - Each for \$422.08  
pH/ATC Combination Electrode, accupHast, Ag/AgCl reference; Extra-long epoxy Body, refillable, BNC and 1/4 in. Phone connectors.
- 13-620-114** - Each for \$397.58  
pH/ATC Combination Electrode, accupHast, Ag/AgCl reference; Extra-long epoxy Body, refillable, BNC and Mini-Phone connectors

Fisher Scientific accuTupH Plus Rugged Bulb Variable Temperature pH Combination Electrode



- 13-620-185** - Each for \$367.92  
Electrode, pH Combination; Fisher Scientific accuTupH Plus Rugged Bulb Variable Temperature; Double junction, Glass body; Gel-filled; 0-14pH range; -5 to +100 deg. C range; 102mmL, 10mm dia., BNC connector

Fisher Scientific accuTupH Rugged Bulb pH Combination Electrodes



- 13-620-181** - Each for \$186.52  
Electrode, pH Combination; Fisher Scientific accuTupH Rugged Bulb Variable Temperature; Single junction, Ag/AgCl reference, Glass body; Liquid filled; 0-14pH range; 0 to 100 deg. C range; 102mmL, 10mm dia., BNC connector.
- 13-620-183** - Each for \$204.35  
pH Combination, accuTupH Rugged Bulb Variable Temperature, Double junction, Ag/AgCl reference; Glass Body, refillable, BNC connector

### Fisher Scientific accuTupH Rugged Bulb pH Indicating Electrode



**13-620-187** - Each for \$160.82  
Electrode, pH Indicating; Fisher Scientific Fisher Scientific accuTupH; Connector: BNC; Suggested Reference Electrodes: 13-620-51, 13-620-52, 13-620-57, 13-620-61, 13-620-62, 13-620-45, 13-620-53

### Fisher Scientific Filling Solution: 4M KCl sat. with AgCl

**SP135-500** - Each for \$48.10 and Case of 6 for \$231.09  
Filling Solution/Electrolyte; 4M KCl saturated with AgCl, Fisher; For all single-junction Ag/AgCl electrodes, including Calcium Combination ISEs 13-620-536 and 13-620-537; inner chamber of many double-junction electrodes. 500mL

### Fisher Scientific Filling Solution: Saturated KCl

**SP138-500** - Each for \$39.85 and Case of 6 for \$189.18  
Filling Solution/Electrolyte; Saturated KCl, Fisher; For Calomel single-junctions; outer chamber of Ag/AgCl double-junction electrodes; Fluoride Combination ISEs 123-620-528 and 13-620-529; Sodium Combination ISEs 13-620-502, -503; 500mL

### Ammonia Calibration Standard, Ricca Chemical

**ACCU0801500** - Each for \$38.92  
Ammonia, Ricca Chemical, 1000ppm NH<sub>3</sub>

### Ammonia pH/Ionic Strength Adjuster; Ricca Chemical

**ACCU0802500** - Each for \$38.74  
pH/Ionic Strength Adjuster for Ammonia, Ricca Chemical; 10M NaOH

### Buffer Concentrate, pH 4.00 (Certified), Fisher Chemical

**SB99-500** - Each for \$81.13 and Case of 6 for \$380.82  
Buffer Concentrate, pH 4.00 (Certified), Fisher Chemical; 500mL; Poly Bottle  
**SB99-1** - Each for \$111.52 and Case of 6 for \$523.12  
Poly Bottle; 1L

### Buffer Concentrate, pH 7.00 (Certified), Fisher Chemical

**SB109-500** - Each for \$81.13 and Case of 6 for \$380.82  
Buffer Concentrate, pH 7.00 (Certified), Fisher Chemical; 500mL; Poly Bottle  
**SB109-1** - Each for \$114.24 and Case of 6 for \$535.82  
Poly Bottle; 1L

### Buffer Concentrate, pH 10.00 (Certified), Fisher Chemical

**SB141-500** - Each for \$76.64 and Case of 6 for \$358.05  
Buffer Concentrate, pH 10.00 (Certified), Fisher Chemical; 500mL; Poly Bottle; CAS: (10043-35-3 (Boric Acid))

### Buffer Concentrate, pH 11.00 (Certified), Fisher Chemical

**SB142-500** - Each for \$81.56 and Case of 6 for \$382.85  
Buffer Concentrate, pH 11.00 (Certified); 500mL; Poly Bottle

### Buffer Precision Reference Standard, pH 4.00 +/- 0.002 at 25C (Color Coded Red), Ricca Chemical

**1502-16** - Each for \$20.26  
Buffer, Precision Reference Standard, pH 4.00 +/- 0.002 at 25 deg. C, Clear, red liquid; Ricca Chemical; 500mL; Poly Bottle; CAS: 877-24-7 (Potassium Acid Phthalate); 7732-18-5 (Water, Deionized)

### Buffer Precision Reference Standard, pH 7.000 (Color Coded Yellow), Ricca Chemical

**1552-16** - Each for \$20.26  
Buffer; Precision Reference Standard; pH 7.000 +/- 0.002 at 25 deg. C; Yellow; Plastic; 500mL; Ricca

### Buffer Precision Reference Standard, pH 10.000 (Color Coded Blue), Ricca Chemical

**1602-16** - Each for \$20.26  
Buffer; Precision Reference Standard; pH 10.000 +/- 0.005 at 25 deg. C; Blue; Plastic; 500mL; Ricca

### Buffer Reference Standard, pH 4.00 (Color Coded Red), Ricca Chemical

**1501-16** - Each for \$12.64  
Buffer; Reference Standard; pH 4.00 +/- 0.01 at 25 deg. C; Red; Plastic; 500mL; Ricca  
**1501-32** - Each for \$20.63  
1L  
**15011CT** - Each for \$42.43  
4L  
**1501-1** - Each for \$42.30  
Poly Bottle; 4L  
**1501-25** - Each for \$63.88  
10L  
**1501-5** - Each for \$85.88  
20L  
**150120** - Pack of 20 for \$35.35  
Pouch (20/Box)

### Buffer Reference Standard, pH 4.00 +/- 0.01 at 25 deg C, Ricca Chemical

**1500-16** - Each for \$12.64  
Buffer; Reference Standard; pH 4.00 +/- 0.01 at 25 deg. C; Plastic; 500mL; Ricca  
**1500-32** - Each for \$20.63  
1L; Plastic  
**15001CT** - Each for \$42.43  
4L; Cubitainer  
**1500-1** - Each for \$42.30  
4L; Plastic  
**1500-25** - Each for \$60.44  
10L; Cubitainer  
**1500-5** - Each for \$85.88  
20L; Cubitainer

### Buffer Reference Standard pH 7.00 0.01 at 25C (Color Coded Green) Ricca Chemical

**15514-16** - Each for \$13.31  
Buffer Reference Std pH 7.00 0.01 at 25C (Green) Ricca Chemical; 500mL; Plastic; CAS: 7558-79-4(Sodium Phosphate, Dibasic), 7732-18-5(Water, Deionized), 7778-77-0(Potassium Phosphate, Monobasic), Proprietary(Inert Dye)  
**15514-32** - Each for \$20.90  
1L; Poly Bottle  
**15514-1** - Each for \$42.85  
4L; Poly Bottle  
**15514-25** - Each for \$65.37  
10L; Cubitainer  
**15514-5** - Each for \$90.34  
20L; Cubitainer

### Buffer Reference Standard, pH 7.00 +/- 0.01 at 25 deg C (Color Coded Yellow), Ricca Chemical

**155120** - Pack of 20 for \$35.35  
Buffer, Reference Standard; pH 7.00 +/- 0.01 at 25 deg C; Color Coded Yellow; Ricca; 20mL; Pouch (20/Box)  
**1551-16** - Each for \$12.64  
Plastic Bottle, 500mL  
**1551-32** - Each for \$20.63  
1L  
**15511CT** - Each for \$42.43  
4L; Cubitainer  
**1551-1** - Each for \$42.30  
Poly Bottle; 4L  
**1551-25** - Each for \$63.88  
10L  
**1551-5** - Each for \$84.58  
20L

**Buffer Reference Standard, pH 7.00 +/- 0.01 at 25 deg C, Ricca Chemical**

**1550-16** - Each for \$12.52  
 Buffer; Reference Standard; pH 7.00 +/- 0.01 at 25 deg. C; Plastic; 500mL; Ricca

**1550-32** - Each for \$20.63  
 1L; Plastic

**15501CT** - Each for \$42.44  
 4L; Cubitainer

**1550-1** - Each for \$42.30  
 4L; Plastic

**1550-25** - Each for \$63.88  
 10L; Cubitainer

**1550-5** - Each for \$84.58  
 20L; Cubitainer

**Buffer Reference Standard, pH 10.00 (Color Coded Blue), Ricca Chemical**

**160120** - Pack of 20 for \$35.35  
 Buffer, Reference Standard; pH 10.00 +/- 0.01 at 25 deg C; Color Coded Blue; Ricca; 20mL; Pouch (20/Box)

**1601-16** - Each for \$12.64  
 500mL; Plastic

**1601-32** - Each for \$20.63  
 Poly Bottle; 1L

**1601-1CT** - Each for \$42.43  
 4L; Cubitainer

**1601-1** - Each for \$42.18  
 4L; Plastic

**160125** - Each for \$62.73  
 10L; Cubitainer

**1601-5** - Each for \$84.47  
 20L; Cubitainer

**Buffer Reference Standard, pH 10.00 +/- 0.01 at 25 deg C, Ricca Chemical**

**1600-16** - Each for \$12.64  
 Buffer; Reference Standard; pH 10.00 +/- 0.01 at 25 deg. C; Plastic; 500mL; Ricca

**1600-32** - Each for \$20.63  
 Plastic Bottle, 1L

**1600-1** - Each for \$42.17  
 4L

**16001CT** - Each for \$42.43  
 4L; Cubitainer

**1600-25** - Each for \$62.72  
 10L

**1600-5** - Each for \$84.48  
 20L

**Buffer Salt, pH 4.01 (Certified), Fisher Chemical**

**B79** - Pack of 12 for \$92.35 and Case of 6 Packs for \$435.00  
 Buffer Salt, pH 4.01 (Certified); Potassium Acid Phthalate; 12 packets per pack; Envelopes; CAS: (877-24-7)

**Buffer Salt, pH 6.86 (Certified), Fisher Chemical**

**B78** - Pack of 12 for \$94.77 and Case of 6 Packs for \$446.39  
 Buffer Salt, pH 6.86 (Certified); Potassium Phosphate Monobasic/Sodium Phosphate Dibasic; 12 packets per pack; Envelopes; CAS: (7778-77-0 and 7558-79-4)

**Buffer Salt, pH 7.41 (Certified), Fisher Chemical**

**B82** - Pack of 12 for \$95.27 and Case of 6 Packs for \$446.99  
 Buffer Salt, pH 7.41 (Certified); Potassium Phosphate Monobasic/Sodium Phosphate Dibasic; 12 packets per pack; Envelopes; CAS: (7778-77-0 and 7558-79-4)

**Buffer Salt, pH 9.18 (Certified), Fisher Chemical**

**B80** - Pack of 12 for \$94.30 and Case of 6 Packs for \$444.17  
 Buffer Salt, pH 9.18 (Certified); Sodium Tetraborate Decahydrate; 12 packets per pack; Envelopes; CAS: (1303-96-4)

**Buffer Salt, pH 10.4 (Certified), Fisher Chemical**

**B77** - Pack of 12 for \$93.47 and Case of 6 Packs for \$438.13  
 Buffer Salt, pH 10.4 (Certified); Tris(hydroxymethyl)aminomethane; 12 packets per pack; Envelopes; CAS: (77-86-1)

**Buffer Solution, pH 1.00 (Certified), Fisher Chemical**

**SB140-500** - Each for \$42.39 and Case of 6 for \$204.15  
 Buffer Solution, pH 1.00; Certified; Poly Bottle; 500mL; Fisher Chemical; CAS: 7647-01-0

**Buffer Solution, pH 2.00 (Certified), Fisher Chemical**

**SB96-500** - Each for \$32.30 and Case of 6 for \$156.49  
 Buffer Solution, Potassium Chloride/Hydrochloric Acid, pH 2.00; pH 2 0.02 at 25 deg. C; Certified; Poly Bottle; 500mL; Fisher Chemical; CAS: 7447-40-7

**SB96-1** - Each for \$51.02 and Case of 6 for \$243.08  
 Poly Bottle; 1L

**SB96-20** - Each for \$215.94  
 PolyPac; 20L

**Buffer Solution, pH 3.00 (Certified), Fisher Chemical**

**SB97-500** - Each for \$33.67 and Case of 6 for \$164.48  
 Buffer Solution, pH 3.00; Certified; Poly Bottle; 500mL; Fisher Chemical; CAS: 67-56-1

**SB97-20** - Each for \$227.31  
 PolyPac; 20L

**Buffer Solution, pH 4.00 (Certified), Fisher Chemical**

**SB98-500** - Each for \$32.68 and Case of 6 for \$157.84  
 Buffer Solution, pH 4.00 (Certified), Fisher Chemical; 500mL; Poly Bottle; CAS: 877-24-7 (Potassium hydrogen phthalate), 50-00-0 (Formaldehyde), 67-56-1 (Methyl Alcohol)

**SB98-1** - Each for \$49.14 and Case of 6 for \$239.93  
 Poly Bottle; 1L

**SB98-10** - Each for \$192.76  
 PolyPac; 10L

**SB98-20** - Each for \$250.58  
 PolyPac; 20L

**Buffer Solution, pH 4.00, Color-Coded Red (Certified), Fisher Chemical**

**SB101-500** - Each for \$29.11 and Case of 6 for \$137.89  
 Buffer Solution, pH 4.00, Color-Coded Red; Certified; Fisher Chemical; 500mL; Poly Bottle; CAS: 877-24-7 (Potassium hydrogen phthalate), 50-00-0 (Formaldehyde), 67-56-1 (Methyl alcohol), 16423-68-0 (Red #3)

**SB101-4** - Each for \$94.82 and Case of 4 for \$301.30  
 Poly Bottle; 4L

**SB101-20** - Each for \$185.12  
 PolyPac; 20L

**Buffer Solution (Acetate), pH 4.00 (Certified), Fisher Chemical**

**SB85-1** - Each for \$50.71 and Case of 6 for \$241.76  
 Buffer Solution (Acetate), pH 4.00 (Certified), Fisher Chemical; Chlorine Titrimeter Reagent; 1L; Poly Bottle

**Buffer Solution, pH 4.63 (Certified), Fisher Chemical**

**SB100-1** - Each for \$56.54 and Case of 6 for \$267.18  
 Buffer Solution, pH 4.63 (Certified); 1L; Poly Bottle

**Buffer Solution, pH 5.00 (Certified), Fisher Chemical**

**SB102-500** - Each for \$33.54 and Case of 6 for \$161.81  
 Buffer Solution, pH 5.00; Certified; Poly Bottle; 500mL; Fisher Chemical; CAS: 877-24-7

**SB102-1** - Each for \$46.01 and Case of 6 for \$224.38  
 Poly Bottle; 1L

**Buffer Solution, pH 6.00 (Certified), Fisher Chemical**

**SB104-500** - Each for \$32.64 and Case of 6 for \$155.71  
 Buffer Solution, pH 6.00; Certified; Poly Bottle; 500mL; Fisher Chemical; CAS: (122-39-4)

**SB104-1** - Each for \$53.11 and Case of 6 for \$257.02  
 Poly Bottle; 1L

**SB104-20** - Each for \$234.82  
 PolyPac; 20L

**Buffer Solution Concentrate, pH 6.00 (Certified), Fisher Chemical**

**SB106-500** - Each for \$58.40 and Case of 6 for \$277.24  
 Buffer Concentrate, pH 6.00 (Certified); 500mL; Poly Bottle



### Buffer Solution, pH 7.00 (Certified), Fisher Chemical

**SB108-20** - Each for \$284.75  
Buffer Solutions, pH 7.00, Certified; Fisher Chemical; 20L; PolyPac; 1310-73-2 (Sodium hydroxide), 7778-77-0 (Potassium phosphate monobasic)  
**SB108-500** - Each for \$32.73 and Case of 6 for \$154.70  
Poly Bottle; 500mL  
**SB108-1** - Each for \$48.78 and Case of 6 for \$233.28  
Poly Bottle; 1L  
**SB108-10** - Each for \$219.38  
PolyPac; 10L

### Buffer Solution, pH 7.00, Color-Coded Yellow (Certified), Fisher Chemical

**SB107-500** - Each for \$28.58 and Case of 6 for \$135.35  
Buffer Solution, pH 7.00 Color-coded Yellow; Certified; Fisher Chemical; 500mL; Poly Bottle; CAS: 7778-77-0 (Potassium phosphate monobasic), 1310-73-2 (Sodium hydroxide), 1934-21-0 (FD and C Yellow 5)  
**SB107-4** - Each for \$94.27 and Case of 4 for \$299.62  
Poly Bottle; 4L  
**SB107-20** - Each for \$183.29  
PolyPac; 20L

### Buffer Solution, Phosphate, pH 7.00, APHA, Ricca Chemical

**5803-16** - Each for \$35.41  
Phosphate Buffer Solution; pH 7; 500mL; Poly natural; APHA for Chlorine and Chlorine Dioxide (Amperometric Method); Ricca  
**5803-32** - Each for \$53.55  
Poly natural; 1L  
**5803-1** - Each for \$151.05  
Poly natural; 4L

### Buffer Solution, pH 7.40 (Certified), Fisher Chemical

**SB110-500** - Each for \$34.60 and Case of 6 for \$164.41  
Buffer Solution, pH 7.40 (Certified); 500mL; Poly Bottle  
**SB110-1** - Each for \$52.71 and Case of 6 for \$250.19  
Poly Bottle; 1L

### Buffer Solution, pH 8.00 (Certified), Fisher Chemical

**SB112-500** - Each for \$29.91 and Case of 6 for \$144.17  
Buffer Solution, pH 8.00; Certified; Poly Bottle; 500mL; Fisher Chemical; CAS: 7778-77-0  
**SB112-1** - Each for \$46.47 and Case of 6 for \$218.83  
Poly Bottle; 1L  
**SB112-20** - Each for \$228.29  
PolyPac; 20L

### Buffer Solution, pH 9.00 (Certified), Fisher Chemical

**SB114-500** - Each for \$32.82 and Case of 6 for \$158.98  
Buffer Solution, pH 9.00; Certified; Fisher Chemical; 500mL; Poly Bottle  
**SB114-1** - Each for \$51.22 and Case of 6 for \$247.04  
Poly Bottle; 1L  
**SB114-20** - Each for \$241.41  
PolyPac; 20L

### Buffer Solution, pH 10.00 (Certified), Fisher Chemical

**SB116-500** - Each for \$33.68 and Case of 6 for \$160.08  
Buffer Solution, pH 10.00; Certified; Poly Bottle; 500mL; Fisher Chemical; CAS: (6381-92-6)  
**SB116-1** - Each for \$50.78 and Case of 6 for \$243.93  
Poly Bottle; 1L  
**SB116-10** - Each for \$160.00  
PolyPac; 10L  
**SB116-20** - Each for \$226.09  
PolyPac; 20L

### Buffer Solution, pH 10.00, Color-Coded Blue (Certified), Fisher Chemical

**SB115-500** - Each for \$29.26 and Case of 6 for \$139.22  
Buffer Solution, pH 10.00 Color-coded Blue; Certified; Fisher Chemical; 500mL; Poly Bottle; Potassium Hydrogen Phthalate, +/-0.01 at 25 deg. C; CAS: 931-88-4  
**SB115-4** - Each for \$97.58 and Case of 4 for \$320.34  
Poly Bottle; 4L  
**SB115-20** - Each for \$185.12  
PolyPac; 20L

### Corning Coliform Sample Container



**09-730-91** - Case of 100 for \$62.79  
Containers, Sample; Water and wastewater testing; Corning; Automatically dechlorinates sample; Sterile-by-process; Disposable; With a tablet of sodium thiosulfate; Snap-tight lid with locking arrow; Tie-down leash on the cap  
**09-730-91A** - Case of 100 for \$57.49  
Without Tablet

### Filling Solution, Ammonia ISE, Ricca Chemical

**ACCU0800500** - Each for \$40.56  
Ammonium Chloride, Ricca Chemical; 0.1M

### Mettler Toledo pH and Metallic Electrode Detachable Cables

**01-911-279** - Each for \$50.00  
Cable, Detachable; Mettler Toledo; Connect to electrodes with S7 screw heads (InLab Models 201, 301, 412, 420, 421, 423, 426, 427, 501); Length: 3.9 ft.; 2mm Pin Connector  
**01-911-278** - Each for \$56.00  
BNC Connector  
**01-911-280** - Each for \$64.22  
US Standard Connector

### Orbeco-Hellige Simplex Chlorine and pH Comparator Test Kits - For pH Testing



**15-398-394** - Each for \$44.43  
Water Testing Supplies; Uses eight built-in, nonfading, color standards mounted in a durable, corrosion-resistant housing; pH Test Kit; Method: Phenol Red; Range: 6.8-8.2

### Thermo Scientific Orion 3-Star Benchtop Dissolved Oxygen Meter



**13-642-053** - Each for \$1077.20  
Orion 3-Star Dissolved Oxygen Benchtop Meter; measures dissolved oxygen in mg/L and % saturation. Meter Only package.  
**13-645-103** - Each for \$1555.50  
Meter Kit with stainless-steel DO probe, 3m cable, overflow funnel with stri box, probe service kit, DO calibration sleeve, benchtop electrode stand, instruction manual.

### Thermo Scientific Orion 4-Star pH/Conductivity Benchtop Meter




**13-642-057** - Each for \$1210.74  
Meter, Electrochemistry, Benchtop pH/Conductivity, Orion 4-Star; Meter Only; -2.000 to +19.999pH, 0.000 to 3000mS/cm, -5 to +105 deg. C ranges; Includes meter, manual  
**13-645-109** - Each for \$1833.96  
Meter Kit

### Thermo Scientific Orion 4-Star pH/Dissolved Oxygen Benchtop Meter



**13-642-056** - Each for \$1138.97  
Orion 4-Star pH/Dissolved Oxygen Benchtop Meter; measures pH and dissolved oxygen in mg/L and % saturation. Meter Only package.  
**13-645-108** - Each for \$1797.24  
Meter Kit, Includes Ross Ultra pH electrode, pH buffers, stainless-steel DO probe, 3m cable, overflow funnel with stri box, probe service kit, DO calibration sleeve, benchtop electrode stand, instruction manual

Thermo Scientific Orion 4-Star pH/ISE Benchtop Meter



**13-642-055** - Each for \$1101.60  
 Meter; Benchtop; Orion 4-star; pH/ISE; Dual display of pH or ISE and temperature; Auto/manual pH calibration at 1 to 5 points; Manual ISE calibration at 1 to 5 points; 3-button pad; LCD with ready indication; Full complement of GLP features  
**13-645-107** - Each for \$1334.16  
 Meter Kit with Ross ultra pH electrode, pH buffers, stainless-steel DO probe, 3m cable, overflow funnel with stri box, probe service kit, DO calibration sleeve, benchtop electrode stand, instruction manual.

Thermo Scientific Orion 5-Star pH/ISE/ORP/DO/Conductivity Benchtop Meter - For pH Testing



**13-645-110** - Each for \$2598.96  
 Meter, Electrochemistry, Benchtop Multiparameter, Orion 5-Star; Meter Kit: -2 to +19pH, +/-1999mV. 0 to 90mg/L DO, 0 to 19,900 mg/L/M/%/ppb; Includes: meter; software; pH, ATC, DO and Conductivity probes, power supply, manual

Thermo Scientific Orion 81-65 ROSS Sure-Flow pH Electrode

**13-642-141** - Each for \$455.83  
 Electrode, pH; Orion; Sure-Flow; Model 81-65 ROSS; pH Range: 0-14; Temperature Range: 0-100 deg.C; Internal Reference: ROSS; Junction: Sure-Flow; Dimensions: 120 x 12mm

Thermo Scientific Orion 91-02 Combination pH Electrode

**13-641-13** - Each for \$192.48  
 Electrode, pH Combination, Thermo Scientific; Orion 91-02; Glass Body Combination; Model: General Purpose/Standard Size/Standard Bulb; Ranges: 0-14pH, 0-90deg.C; Ag/AgCl Internal Reference; Screw Cap connector, requires separate cable

Thermo Scientific Orion Activity Standard

**13-641-862** - Each for \$85.00  
 Control, Standard; Thermo Scientific Orion; For Calcium and Water Hardness ion measurements. 100ppm Ca<sup>2+</sup> as CaCO<sub>3</sub>. 475mL; CAS: (10043-52-4)  
**13-641-811** - Each for \$83.00  
 For Calcium Ion measurements. 0.1M CaCl<sub>2</sub>; 475mL; CAS: (10043-52-4)  
**13-641-835** - Each for \$99.50  
 For Cupric Ion measurements. 0.1M Cu(NO<sub>3</sub>)<sub>2</sub>; 475mL; CAS: (3251-23-8)  
**13-641-773** - Each for \$97.00  
 For Lead Ion measurements. 0.1M Pb(ClO<sub>4</sub>)<sub>2</sub>; 475mL; CAS: (63916-96-1)  
**13-641-888** - Each for \$75.00  
 For Nitrate Ion measurements. 0.1M NaNO<sub>3</sub>; 475mL; CAS: (7631-99-4)  
**13-641-910** - Each for \$75.00  
 For Nitrate Ion measurements. 1000ppm as N; 475mL.  
**13-641-924** - Each for \$75.00  
 For Nitrate Ion measurements. 100ppm as N; 475mL  
**13-641-917** - Each for \$83.00  
 For Potassium Ion measurements. 0.1M KCl; 475mL

Thermo Scientific Orion Ammonia HP Ion Selective Electrode



**13-643-500** - Each for \$595.00  
 Electrode, Ion Selective, Thermo Scientific; Orion Ammonia Gas-Sensing Combination; Ranges: 1.0 to 5 x 10E-7M, 17,000 to 0.01 ppm; 0 deg. to 50 deg. C; Model 95-12; Connector: Waterproof BNC

Thermo Scientific Orion Aquapro Electrodes



**13-645-154** - Each for \$300.00  
 Electrode, pH Combination; AquaPro; Thermo Scientific Orion; Epoxy Body; General purpose, rugged use, lab or field use; Waterproof BNC connector  
**13-645-153** - Each for \$315.00  
 Epoxy Body; Moist surfaces, solids, semisolids, small sample sizes; BNC connector  
**13-645-151** - Each for \$287.00  
 Epoxy Body; Rugged use; Waterproof BNC connector  
**13-645-152** - Each for \$322.56  
 Epoxy Body; Small sample sizes, test tubes, aqueous solutions only; Waterproof BNC connector  
**13-641-212** - Each for \$277.00  
 Glass Body pH; General purpose; BNC connector  
**13-645-150** - Each for \$328.00  
 Glass Body pH; Small sample sizes, test tubes; Waterproof BNC connector

Thermo Scientific Orion ATC Probes

**13-641-260** - Each for \$204.00  
 Probe, ATC; Orion; Epoxy body; For pH meters models 920A, 720A, 710A, 620, 610, 525A, 520A, 420A, 410A, 290A, 250A, 230A, 210A

Thermo Scientific Orion Automatic Temperature Compensation Probes



**13-642-618** - Each for \$204.00  
 perpHect Epoxy Body Atc Probe; Accessory; Orion No.: 927005; Description: ATC Probe for perpHect Meters and SensorLink pH System

Thermo Scientific Orion Bromide Electrodes

**13-641-157** - Each for \$693.95  
 Electrode, Ion Selective, Thermo Scientific Orion; Bromide Combination; ionplus Sure-Flow solid state combination; Concentration Range: 1.0 to 5 x 10<sup>-6</sup>M, 79,900 to 0.40 ppm; Optimum Temp. Range: 0 - 80 deg.C; Connector: U.S. Standard  
**13-645-158** - Each for \$687.00  
 Orion Bromide Combination Electrode with Waterproof BNC connector

Thermo Scientific Orion Economy Series pH Combination Electrode Accessories and Solutions

**13-641-897** - Pack of 5 for \$86.11  
 Outer Chamber Filling Solution; (5 x 2 oz.); Description: Outer Chamber Solution for Double-Junction Electrodes; 10% KNO<sub>3</sub>; 50mL, CAS: (7757-79-1)  
**13-641-908** - Each for \$55.00  
 475mL (1 pt.) bottle  
**13-641-685** - Pack of 5 for \$86.11  
 2M KCl, saturated with Ag  
**13-641-755** - Pack of 5 for \$95.00  
 Filling Solution/Electrolyte, 3M KCl without AgCl  
**13-641-686** - Pack of 5 for \$86.11  
 Filling Solution/Electrolyte, 4M KCl saturated with Ag  
**13-641-899** - Pack of 5 for \$82.01  
 Filling Solution/Electrolyte, Equitransferent Solution for 13-641-898 Single-Junction Electrode; 5 x 50mL (5 x 2 oz.)  
**13-641-901** - Pack of 5 for \$85.08  
 Internal Filling Sol 5 x 2oz/pk

### Thermo Scientific Orion Economy Series pH Combination Electrodes



**13-641-869B** - Each for \$189.00  
Electrode, pH Combination; Thermo Electron; Epoxy body; Gelled Ag/AgCl reference; pH range: 0-12; Model: Flat Surface; With BNC Connector  
**13-641-865A** - Each for \$148.00  
Orion Economy pH Combination Electrode; Semimicro Size; 5-15/16 in. L; 39-3/8 in. (1m) cable; BNC connector

### Thermo Scientific Orion Fluoride Solid state ionplus Sure-Flow ISE Combination with WP Connector

**13-642-265** - Each for \$692.00  
Electrodes; Fluoride; ionplus Sure-Flow; Solid-State; Orion; Concentration Range: Saturated to  $10^{-6}$ M; Saturated to 0.02ppm; Optimum Temp: 0 - 80 deg. C

### Thermo Scientific Orion Gas-Sensing ISE Sensor Membranes

**13-641-929** - Pack of 20 for \$108.00  
Membrane, Sensor, Gas Sensing, 20 Loose, For Cat. Nos. 951201 And 9512Bn Thermo Orion Ion Selective Ammonia Electrodes  
**13-641-931** - Pack of 3 for \$132.00  
For use with Ammonia Electrodes, 13-641-922, 13-299-96; 3, bonded to caps  
**13-641-767** - Pack of 4 for \$159.00  
For use with Carbon Dioxide Electrodes 13-641-765, 13-299-95; 4 membranes; with O-rings

### Thermo Scientific Orion Iodide Electrode

**13-645-160** - Each for \$685.00  
Electrode, Iodide; Orion 96-53; Concentration Range: 1.0 to  $5 \times 10^{-8}$ M, 127,000 to  $5 \times 10^{-3}$  ppm; Optimum Temp. Range: 0 - 80 deg.C; Connector: waterproof

### Thermo Scientific Orion Ion Selective Plastic-Membrane Half-Cell Electrodes



**13-641-933** - Each for \$692.16  
Electrode, Ion Selective; Thermo Scientific Orion; Plastic-membrane; Type: Calcium; Range: 1 to  $5 \times 10^{-7}$ M; 40,100 to 0.02ppm; Interferences:  $Pb^{2+}$ ,  $Na^{+}$ ,  $Hg^{2+}$ ,  $Na^{+}$ ,  $Hg^{2+}$ ,  $H^{+}$ ,  $Sr^{2+}$ ,  $Fe^{2+}$ ,  $Cu^{2+}$ ,  $N$ ; BNC Connector  
**13-641-781** - Each for \$969.23  
Fluoroborate; U.S. Standard Connector  
**13-642-261** - Each for \$692.00  
Nitrate; Waterproof BNC Connector  
**13-641-950** - Each for \$697.31  
Nitrite; BNC Connector  
**13-641-951** - Each for \$705.55  
Nitrite; U.S. Standard Connector  
**13-641-926** - Each for \$715.00  
Potassium; BNC Connector  
**13-642-262** - Each for \$752.00  
Water Hardness; Waterproof BNC Connector

### Thermo Scientific Orion Ionic Strength Adjuster: 2M Ammonium Sulfate

**13-641-850** - Each for \$75.00  
Ionic Strength Adjustor For Polymer Membrane And Solid State ISES Electrodes; Orion; 475mL;  $2m(nh_4)_2so_4$ , CAS: (7783-20-2)

### Thermo Scientific Orion Ionic Strength Adjuster: 4M Potassium Chloride

**13-641-851** - Each for \$90.00  
Ionic Strength Adjuster, ISE Meter Accessory, Orion; For Calcium measurements; 4M KCl; In 475mL (1 pt.) bottle

### Thermo Scientific Orion Ionic Strength Adjuster: 5M Sodium Chloride

**13-641-927** - Each for \$92.00  
Ionic Strength Adjuster; ISE Meter Accessory; Orion; For Potassium measurements; 5M NaCl; 475mL (1 pt.) bottle

### Thermo Scientific Orion Ion-Selective Gas-Sensing Combination Electrodes



**13-645-156** - Each for \$690.00  
Electrode, Combination; Thermo Scientific Orion; Gas-Sensing, Ion-Selective; Carbon Dioxide; Range: 10-2 to 10-4M; 440 to 4.4ppm; Waterproof BNC Connector  
**13-299-99** - Each for \$803.00  
Nitrogen Oxide; Range:  $5 \times 10^{-3}$  to  $4 \times 10^{-6}$ M; 230 to 0.18ppm; BNC Connector

### Thermo Scientific Orion Ion-Selective Plastic-Membrane Combination Electrodes

**13-642-272** - Each for \$778.00  
Electrode, Half-Cell; Thermo Scientific Orion; Ion-Selective; Calcium; Model 97-20; Concentration Range: 1.0 to  $5 \times 10^{-7}$ M, 40,100 to 0.02 ppm; Optimum Temperature Range: 0 - 40 deg.C; Ionplus Sure-Flow; Waterproof BNC connector  
**13-642-270** - Each for \$808.00  
Half-Cell Electrode, Nitrate, Model 97-07, Ionplus Sure-Flow Plastic Membrane Combination, Connector: Waterproof BNC  
**13-642-271** - Each for \$829.00  
Potassium ionplus Combination ISE, BNC Waterproof connector

### Thermo Scientific Orion Ion-Selective Ross Glass-Membrane Combination Electrode



**13-642-245** - Each for \$555.00  
Electrode, Ion-Selective; Thermo Scientific Orion; Glass-Membrane; Model 86-11 ROSS; Concentration Range: Saturated to  $10^{-6}$  M, saturated to 0.02 ppm; Connector: Waterproof; ROSS Combination

Thermo Scientific Orion Ion-Selective Ross Glass-Membrane Half-Cell Electrode



**13-641-822** - Each for \$399.99  
 Electrode, Ion-Selective; Thermo Scientific Orion; Glass-Membrane; Sodium Half Cell; Range: Saturated to 10-6M; to 0.02ppm; Interferences: Ag+, H+, Li+, Cs+, K+, Tl+; BNC Connector

**13-641-34** - Each for \$696.00  
 Lead; Screw Cap Connector  
**13-641-949** - Each for \$577.00  
 Silver/Sulfide; BNC Connector

Thermo Scientific Orion ISE Activity Standards

**13-641-923** - Each for \$64.00  
 Standard, Activity; ISE; Thermo Scientific Orion; For Ammonia Electrode; 0.1M NH4Cl  
**13-641-924C** - Each for \$65.00  
 For Ammonia Electrode; 1000ppm as N  
**13-641-866** - Each for \$78.00  
 For Bromide Electrode; 0.1M NaBr  
**13-641-768** - Each for \$85.00  
 For Carbon Dioxide Electrode; 0.1M NaHCO3  
**13-641-769** - Each for \$85.00  
 For Carbon Dioxide Electrode; NaHCO3, 100ppm as CaCO3  
**13-641-877** - Each for \$60.00  
 For Chloride Electrode; 100ppm as Cl-  
**13-641-824** - Each for \$72.00  
 For Chlorine Electrode; 100ppm as Cl2  
**13-641-871** - Each for \$72.00  
 For Fluoride Electrode; 0.1M NaF  
**13-641-872** - Each for \$60.00  
 For Fluoride Electrode; 100ppm as F-  
**13-641-752** - Each for \$70.00  
 For Fluoride Electrode; 10ppm as F- with TISAB  
**13-641-869** - Each for \$97.00  
 For Iodide Electrode; 0.1M NaI  
**13-641-774** - Each for \$101.48  
 For Lead Electrode; 0.1M Na2SO4 (Sulfate)  
**13-641-938** - Each for \$95.00  
 For Nitrogen Oxide Electrode; 0.1M NaNO2  
**13-641-210** - Each for \$53.00  
 For Redox Electrode; 420mV; 1 pt.  
**13-641-211** - Each for \$77.91  
 For Redox Electrode; 420mV; 5 x 2 oz.  
**13-641-876** - Each for \$86.00  
 For Sodium Electrode; 0.1M NaCl  
**13-641-747** - Each for \$60.00  
 For Sodium Electrode; 1000ppm as Na+  
**13-641-787** - Each for \$86.00  
 For Sodium Electrode; 1000ppm as Na+ with ISA  
**13-641-909** - Each for \$60.00  
 For Sodium Electrode; 100ppm as Na+  
**13-641-948** - Each for \$61.00  
 For Sodium Electrode; 10ppm as Na+

Thermo Scientific Orion Ion-Selective Solid-State Combination Electrodes



**13-641-902** - Each for \$670.00  
 Electrode, Ion Selective, Thermo Scientific; Orion Chloride Solid State Combination, Ranges: 1 to 5 x 10E5M; 35,500 to 0.18ppm; 0 deg. to 80 deg. C; U.S. Standard/Pin connectors  
**13-642-274** - Each for \$548.00  
 Chlorine; Waterproof BNC Connector  
**13-642-264** - Each for \$678.00  
 Cyanide; Waterproof BNC Connector  
**13-641-904** - Each for \$705.00  
 Fluoride; U.S. Standard Connector  
**13-642-266** - Each for \$702.00  
 Silver/Sulfide; Waterproof BNC Connector

Thermo Scientific Orion Ion-Selective Solid-State Half-Cell Electrodes



**13-299-89** - Each for \$538.00  
 Electrode, Ion-Selective; Thermo Scientific Orion; Half-Cell; Solid-State; Type: ; Range: 1 to 5 x 10-6M; 79,900 to 0.40ppm.; Interferences: S=, I-, CN-, high levels of Cl-, NH3; BNC Connector  
**13-641-27** - Each for \$651.00  
 Cadmium; Screw Cap Connector  
**13-299-86** - Each for \$538.00  
 Chloride; BNC connector  
**13-641-28** - Each for \$362.71  
 Chloride; Screw Cap Connector  
**13-299-88** - Each for \$709.00  
 Cupric; BNC Connector  
**13-641-940** - Each for \$544.00  
 Cyanide; BNC Connector  
**13-641-942** - Each for \$577.00  
 Fluoride; BNC Connector  
**13-641-32** - Each for \$565.00  
 Fluoride; Screw Cap Connector  
**13-641-870** - Each for \$589.00  
 Fluoride; U.S. Standard Connector  
**13-299-91** - Each for \$538.00  
 Iodide; BNC Connector  
**13-641-33** - Each for \$509.00  
 Iodide; Screw Cap Connector  
**13-642-574** - Each for \$716.00  
 Lead; BNC Connector

Thermo Scientific Orion ISE Filling/Maintenance Solutions

**13-642-576** - Each for \$110.16  
 Solution, Filling; ISE; Thermo Scientific Orion; For Ammonium Electrodes; 2 oz.  
**13-641-766** - Each for \$72.00  
 Filling Solution for Carbon Dioxide Electrodes; 2 oz.  
**13-641-903** - Pack of 5 for \$75.00  
 Filling Solution for Chloride Combination Electrodes; 2 oz.  
**13-641-953** - Pack of 5 for \$88.00  
 Filling Solution for Nitrite Electrodes; 2 oz.  
**13-641-936** - Each for \$99.00  
 Filling Solution for Nitrogen Oxide Electrodes; 2 oz.  
**13-641-847** - Pack of 5 for \$110.71  
 Filling Solution for Sodium 0.1M NH4Cl Electrodes; 2 oz.  
**13-641-846** - Pack of 5 for \$106.00  
 Filling Solution for Sodium 2M NH4Cl Electrodes; 2 oz.  
**13-641-749** - Each for \$84.00  
 Reconditioning Solution for Sodium Electrodes; 475mL  
**13-641-743** - Each for \$57.35  
 Storage Solution for Sodium Electrodes; 475mL

Thermo Scientific Orion ISE Ionic Strength Adjusters

**13-641-883** - Each for \$95.00  
 Reagent; ISE; Thermo Scientific Orion; Ionic Strength Adjuster; For Ammonia Electrode; pH Adjusting ISA 475mL  
**13-641-852** - Each for \$72.00  
 For Bromide, Cadmium, Chloride, Cupric, Iodide, Silver/Sulfide, Thiocyanate Electrodes; 475mL  
**13-641-770** - Each for \$88.00  
 For Carbon Dioxide Electrode; 475mL  
**13-641-878** - Each for \$249.00  
 For Chloride Electrode; CISA Reagent Pack. Complexation ionic strength adjustor reagents: 2 x 1L 1M HNO3, 2 x 15g NaBrO3

**13-642-578** - Each for \$118.00

For Fluoride Electrode; TISAB II 1 gal.

**13-641-873** - Case of 4 for \$380.00

For Fluoride Electrode; TISAB II 4 x 1 gal.

**13-641-874** - Each for \$140.00

For Fluoride Electrode; TISAB III (concentrated) 475mL

**13-641-954** - Each for \$78.00

For Nitrite Electrode; ISA/Buffer 475mL

**13-641-748** - Each for \$50.00

For Sodium Electrode; 475mL

### Thermo Scientific Orion ISE Replacements

**13-641-821** - Each for \$257.00

Electrodes: For Chlorine Electrode; Voltage Source -600mV

**13-641-771** - Pack of 24 for \$76.89

24 x 6 in.

### Thermo Scientific Orion ISE Special Reagents and Kits

**13-641-853** - Each for \$88.00

Reagent; ISE; Thermo Scientific Orion; For Ammonia and Cyanide Electrode; Alkaline Reagent. 10M NaOH; 475mL

**13-641-726** - Each for \$284.00

For Ammonia Electrode; Reducing Agent Refill; 475mL

**13-641-854** - Each for \$72.00

For Chlorine Electrode; Acid Reagent; 475mL

**13-641-823** - Each for \$83.00

For Chlorine Electrode; Iodide Reagent; 475mL

**13-641-879** - Pack of 4 for \$368.00

For Fluoride Electrode; Standards Bulk Pack; 4 x 475mL with F- with TISAB II and 10ppm F- with TISAB II

**13-641-802** - Each for \$74.00

For Nitrate Electrode; Nitrate Interference Suppressor (NISaB); 475mL

**13-641-724** - Each for \$543.00

Nitrate Test Kit

### Thermo Scientific Orion Lead Solid State ionplus Combination Electrodes

**13-641-153** - Each for \$871.38

Electrode, Lead; ionplus; Thermo Scientific Orion; Sure-Flow, Solid State; Range: 0.1 to 10-6M, 20,700 to 0.2 ppm; U.S. Standard Connector

**13-645-161** - Each for \$859.00

Waterproof BNC Connector

### Thermo Scientific Orion Metallic Combination Electrodes



**13-299-109** - Each for \$361.00

Electrode, Combination; Thermo Scientific Orion; Metallic; Dual Platinum for KF Titrations; U.S. Standard Connector

**13-641-905** - Each for \$387.00

Epoxy Body Platinum Redox/ORP; U.S. Standard Connector

### Thermo Scientific Orion Model 81-01 ROSS Half-Cell pH Electrodes

**13-642-236** - Each for \$250.80

Electrode, Half-Cell; Orion; Model 81-01 ROSS; pH Range: 0-14; Temperature Range: 0-100 deg.C; Dimensions: 120 x 12mm; Cap Diameter: 16mm; Connector: Water Proof; 1m cable

### Thermo Scientific Orion Model 81-15 ROSS Combination pH Electrode

**13-641-816** - Each for \$385.40

Electrode, pH Combination, Orion; ROSS Internal Reference; Semi-Micro Epoxy Body, Glass Fiber Junction, 6-1/2 in.L (165mm), 1/4 in. (6mm) dia. at tip, 16mm Cap dia.; 0-14pH, 0-100 deg. C; 3M KCl electrolyte; 1m cable, BNC connector

### Thermo Scientific Orion Model 81-72 ROSS Sure-Flow pH Electrode

**13-642-142** - Each for \$455.83

Electrode, pH; Sure-Flow; Thermo Scientific Orion; Model 81-72 ROSS; pH Range: 0-14; Temperature Range: 0-100 deg.C; Internal Reference: ROSS; Junction: Sure-Flow; Dimensions: 120 x 12mm; Cap dia: is 16mm

### Thermo Scientific Orion Model 91-06 Combination pH Electrode

**13-642-249** - Each for \$102.00

Electrode, Combination pH; Orion; Model 91-06; pH Range: 0-14; Temperature Range: 0-80 deg.C; Type Reference: Ag/AgCl; Junction: Wick; Dimensions: 120 x 12mm; Cap Diameter: 16mm; Connector: Waterproof; 1m cable

### Thermo Scientific Orion Model 91-55/56 Combination pH Electrodes

**13-642-251** - Each for \$138.00

Electrode, Combination pH; Orion; Model 91-56; pH Range: 0-14; Temperature Range: 0-90 deg.C; Type Reference: Ag/AgCl; Junction: Glass Fiber; Dimensions: 120 x 12mm; Connector: Waterproof, 1m cable

### Thermo Scientific Orion Model 91-61 Low Resistance pH Half-Cell

**13-641-17** - Each for \$244.50

Electrode, pH; Low Resistance; Thermo Scientific Orion 91-62; Silver/silver chloride; Glass body; With rugged bulb; Cap diameter is 16mm; Screw cap

### Thermo Scientific Orion Model 91-72 Sure-Flow pH Electrode

**13-642-254** - Each for \$238.00

pH Electrode; Sure-Flow; General purpose; BNC Connector; 1m cable; 16mm cap dia.

### Thermo Scientific Orion Model 96-29 Cupric combination electrodes

**13-645-157** - Each for \$858.00

Electrode, Ion Selective, Thermo Scientific; Orion Cupric Combination; Orion; Model 96-29; Concentration Range: 0.1 to 10-8M, 6350 to 6.4 x 104 ppm; Optimum Temperature Range: 0- 80 deg.C; Connector: waterproof bnc

### Thermo Scientific Orion Model 96-48 Cadmium combination electrodes

**13-645-159** - Each for \$814.00

Electrode, Ion Selective, Thermo Scientific; Orion Cadmium Combination; Model 96-48; Concentration Range: 10-1 to 10-7M, 11,200 to 0.01 ppm; Optimum Temperature Range: 0- 80 deg.C; Connector: Waterproof BNC

### Thermo Scientific Orion pH Combination Electrodes

**13-642-247** - Each for \$263.99

Electrodes, Combination; Thermo Scientific Orion; pH Combination; AquaPro; Model 91-03; pH Range: 0-14; Temperature Range: 0-90 deg.C; Type Reference: Ag/AgCl; Junction: Ceramic; Dimensions: 140 x 6mm; Connector: Waterproof, 1m cable

### Thermo Scientific Orion pH Combination Electrodes with WP Connector

**13-642-246** - Each for \$167.00

Electrode, pH Combination; Orion; Glass body; Ag/AgCl Internal Reference; Ceramic Junction; General purpose pH for accurate QC and research work; Ranges: 0-14pH, 0-90 deg. C; 120mmL x 12mm dia. 1m cable; BNC waterproof connector

**13-642-248** - Each for \$205.00

pH Combination Electrode, Glass body, Rugged bulb

**13-642-253** - Each for \$233.00

pH Combination Electrode, Sure-Flow Epoxy body

### Thermo Scientific Orion pH Micro-Combination Electrodes

**13-299-514** - Each for \$383.00

Electrode, pH/Combination; Thermo Electron; Glass Micro pH; Ag/AgCl reference; 0-14 pH range; For test tubes or small containers; Requires 5uL of sample; 1m cable

**13-299-511** - Each for \$440.00

pH Micro-Combination Electrode, For gels or sample volumes as small as 0.5microL

**13-299-512** - Each for \$440.00

pH Micro-Combination Electrode; For small test tubes or microtiter plates

Thermo Scientific Orion Plastic-Membrane ISE Sensor Modules



- 13-642-568** - Each for \$347.00  
Sensor, Interchangeable; ISE; Thermo Scientific Orion; Plastic-Membrane; Combination sensors can be used in combination electrodes; half-cell sensors in half-cell models; Ammonium Sensor Module
- 13-641-803** - Each for \$219.00  
Calcium Sensor Module
- 13-641-40** - Each for \$347.00  
Chloride Sensor Module
- 13-641-944** - Pack of 3 for \$268.00  
Nitrate Sensor Module
- 13-641-952** - Pack of 3 for \$276.00  
Nitrite Sensor Module
- 13-641-41** - Each for \$361.00  
Perchlorate Sensor Module
- 13-641-22** - Each for \$381.00  
pH Sensor Module
- 13-641-912** - Each for \$219.00  
Potassium Sensor Module
- 13-641-947** - Each for \$232.00  
Water Hardness Sensor Module

Thermo Scientific Orion Ross Combination Electrode

- 13-643-100** - Each for \$164.00  
Electrode, Combination; Ross; Thermo Scientific Orion; More stable and accurate measurements; Unparalleled pH response to temperature changes; Double Junction Fillable Glass Epoxy Tris
- 13-643-102** - Each for \$155.00  
Epoxy Tris
- 13-643-101** - Each for \$175.99  
Micro Glass
- 13-642-235** - Each for \$488.84  
Ultra Flat Surface

Thermo Scientific Orion Ross PerpHecT Electrode

- 13-642-800** - Each for \$479.60  
Electrode, pH Combination; Ross PerpHecT; Thermo Scientific Orion; Glass body Micror Tip; Ranges: 0 to 14pH, 0 to 100 deg. C; 155mmL x 3mm dia. at tip; 1m cable, Waterproof BNC connector

Thermo Scientific Orion Ross pH Combination Electrodes with WP Connector



- 13-642-244** - Each for \$429.00  
Electrode, pH Combination; Orion Ross Semimicro Epoxy body; Ross Internal Reference; Sure-Flow Junction; For use in test tube and small sample; For soil/viscous sample; Range 0-14pH, 0-100 deg. C; 165mmL x 6mm dia.; 1m cable; BNC connector

Thermo Scientific Orion Ross Series Combination Electrodes



- 13-641-807** - Each for \$412.00  
Electrode, Combination; Ross; Thermo Scientific Orion; Epoxy Body/Liquid-Filled Combination; Flat Surface/Standard Size; BNC Connector
- 13-641-6** - Each for \$414.58  
Epoxy Body/Liquid-Filled Combination; Flat Surface; Screw Cap Connector
- 13-642-565** - Each for \$367.00  
Epoxy Body/Liquid-Filled Combination; General Purpose PerpHecT/Standard Size; BNC Connector

- 13-641-7** - Each for \$334.00  
Epoxy Body/Liquid-Filled Combination; General Purpose Standard Size Standard Bulb; Screw Cap Connector
- 13-641-760** - Each for \$349.00  
Epoxy Body/Liquid-Filled Combination; General Purpose/Standard Size for viscous samples; BNC Connector
- 13-641-759** - Each for \$362.00  
Epoxy Body/Liquid-Filled Combination; General Purpose/Standard Size for viscous samples; U.S. Standard Connector
- 13-642-564** - Each for \$443.00  
Epoxy Body/Liquid-Filled Combination; PerpHecT Flat Surface/Standard Size; BNC Connector
- 13-642-242** - Each for \$415.00  
Epoxy Body/Liquid-Filled Combination; pH Meter; Waterproof BNC Connector
- 13-641-5** - Each for \$367.00  
Epoxy Body/Liquid-Filled Combination; Semimicro Size; Screw Cap Connector
- 13-642-562** - Each for \$362.00  
Glass Body Combination; General Purpose PerpHecT Standard Size; BNC Connector
- 13-642-566** - Each for \$426.00  
Glass Body Combination; General Purpose PerpHecT Sure-Flow/Standard Size; BNC Connector
- 13-641-805** - Each for \$372.00  
Glass Body Combination; General Purpose Standard Size Rugged Bulb; BNC Connector
- 13-641-804** - Each for \$386.00  
Glass Body Combination; General Purpose Standard Size Rugged Bulb; U.S. Standard Connector
- 13-641-729** - Each for \$342.00  
Glass Body Combination; General Purpose Standard Size Standard Bulb; BNC Connector
- 13-641-4** - Each for \$361.00  
Glass Body Combination; General Purpose Standard Size Standard Bulb; Screw Cap Connector
- 13-641-762** - Each for \$355.00  
Glass Body Combination; General Purpose Standard Size Standard Bulb; U.S. Standard Connector
- 13-642-563** - Each for \$477.00  
Glass Body Combination; PerpHecT Semimicro Size; BNC Connector
- 13-641-8** - Each for \$362.00  
Glass Body Combination; pH Meter; Screw Cap Connector
- 13-641-2** - Each for \$327.00  
Glass Body Combination; pH Meter; Screw Cap Connector; Requires detachable cable
- 13-642-243** - Each for \$422.00  
Glass Body Combination; pH Meter; Waterproof BNC Connector
- 13-641-731** - Each for \$456.00  
Glass Body Combination; Semimicro Size; BNC Connector
- 13-641-3** - Each for \$441.00  
Glass Body Combination; Semimicro Size; Screw Cap Connector
- 13-641-817** - Each for \$469.00  
Glass Body Combination; Semimicro Size; U.S. Standard Connector

Thermo Scientific Orion Ross Series pH Half-Cell Electrodes



- 13-641-757** - Each for \$254.99  
Electrode, Half-cell; Ross; Thermo Scientific Orion; pH Range: 0-14; Temperature Range: 0-100 deg.C; Dimensions: 120 x 12mm; Cap Diameter is 16mm; Connector: U.S. Std.

Thermo Scientific Orion Ross Series Reference Half-Cell Electrodes



- 13-641-756** - Each for \$208.82  
Electrodes, Half-Cell; Orion; Ross Series; Connector: Pin; Orion; Model: Reference; pH Range: 0-14
- 13-641-795** - Each for \$342.00  
Sure Flow Reference; pH Range 0 to 14

### Thermo Scientific Orion Ross Ultra pH Combination Electrodes



- 13-642-238** - Each for \$502.00  
Electrode, pH Combination; Orion; Ross Ultra; Designed for the most difficult samples
- 13-642-241** - Each for \$383.00  
pH Combination Electrode, Epoxy Body
- 13-642-237** - Each for \$392.00  
pH Combination Electrode, General Purpose
- 13-642-239** - Each for \$422.00  
pH Combination Electrode, Rugged Bulb
- 13-642-240** - Each for \$428.00  
pH Combination Electrode, Semimicro Epoxy Body

### Thermo Scientific Orion SAOB Reagent Pack

- 13-641-882** - Pack of 4 for \$229.00  
Special Reagents And Kits; Reagent Pack For Silver/sulfide Electrode 1 Pt, Saob Reagent Pack. Makes 4 x 1 Pt. (475mL) Sulfide Antioxidant Buffer: 4 x 1 Pt. 0.2m Disodium Edta/2m Naoh Base; 4 x 17g Ascorbic Acid

### Thermo Scientific Orion Standard Series Combination Electrodes



- 13-642-560** - Each for \$125.00  
Electrode, pH Combination; PerpHecT; Thermo Scientific Orion; Epoxy Body Combination; General Purpose PerpHecT Standard Size Gel Filled; BNC Connector
- 13-642-559** - Each for \$165.00  
Epoxy Body Combination; General Purpose PerpHecT Standard Size Liquid Filled; BNC Connector
- 13-641-700** - Each for \$164.00  
Epoxy Body Combination; General Purpose/Standard Size Liquid Filled; U.S. Standard Connector
- 13-642-619** - Each for \$193.00  
Epoxy Body Combination; PerpHecT Triode pH/Reference/ATC Gel Filled; BNC Connector
- 13-642-557** - Each for \$204.00  
Glass Body Combination; General Purpose PerpHecT Standard Size; BNC Connector
- 13-642-561** - Each for \$223.00  
Glass Body Combination; General Purpose PerpHecT Sure-Flow Standard Size; BNC Connector
- 13-642-558** - Each for \$246.00  
Glass Body Combination; PerpHecT Semimicro Size; BNC Connector

### Thermo Scientific Orion Standard Series pH Half-Cell Electrodes



- 13-641-856** - Each for \$161.00  
Electrode, pH Half Cell; Thermo Scientific Orion 9101BN; Connector: BNC; Glass Body General-Purpose pH Electrode

### Thermo Scientific Orion Standard Series Reference Half-Cell Electrodes



- 13-641-900** - Each for \$218.00  
Electrode, pH; Thermo Scientific Orion; ORP Titration; Epoxy body; Double junction reference; For ISE determinations; Connector: Pin
- 13-641-907** - Each for \$377.27  
Reservoir Reference Electrode
- 13-641-898** - Each for \$180.00  
Single junction reference

### Thermo Scientific Orion Star Dissolved Oxygen Probes

- 13-642-230** - Each for \$442.00  
Electrode, Polarographic Dissolved Oxygen Probe, Orion; For Star meters with DO mode; 12mm dia. body; with overflow funnel; Mini-DIN connector

### Thermo Scientific Orion Star Navigator 21 Software



- 13-645-127** - Each for \$527.29  
Software, Electrochemistry, Thermo Scientific; Orion Star Navigator 21 Data Collection Software

### Thermo Scientific Orion Triode 3-in-1 pH/ATC Probe



- 13-642-252** - Each for \$299.00  
Probe, 3-in-1 pH/ATC; Orion; 91-57 Triode; Ag/AgCl internal reference system; built-in thermistor for Automatic Temperature Compensation (ATC); Epoxy body; Refillable; Connector: mini DIN, 1m cable

### Yellow Springs Instrument Cable

- 15-177-475** - Each for \$345.00  
Cable; Yellow Springs Instrument Company; For Conductivity / Temperature probes; 10m

### Yellow Springs Instrument Cables and DO/Temp/Conductivity Probes for 556 Multi-Probe System

- 13-298-70** - Each for \$950.00  
Electrode, Probe; DO/Temperature/Conductivity; For YSI Model 556 Multi-probe System; With 4m cable
- 13-298-71** - Each for \$1050.00  
10m Cable
- 13-298-72** - Each for \$1150.00  
20m Cable

### Yellow Springs Instrument Company Galvanic Probe

- 15-177-458** - Each for \$160.60  
Probe; Yellow Springs Instrument; Galvanic Dissolved Oxygen Probe

### Yellow Springs Instrument Company Polrographic Probe

- 15-177-459** - Each for \$160.60  
Probe; Yellow Springs Instrument; Polrographic Dissolved Oxygen Probe

### Yellow Springs Instrument Model 556 Multi-Probe System



- 13-298-64** - Each for \$1750.00  
Meter, Electrochemistry Multiparameter, Yellow Springs Instrument Model 556; Handheld; 0 to 500% air saturation; 0 to 50mg/L DO, 0 to 14pH, 0 to 100mS/cm Conductivity; 4-11/16W x 9 in.H; Multi Probe System Instrument
- 13-298-65** - Each for \$1995.00  
Multi Probe System with Barometer

### Yellow Springs Instrument pH and pH/ORP Probe Kits for Model 556 Multi-Probe System

- 13-298-67** - Each for \$206.00  
System, Probe; Yellow Springs Instrument; For Model 556 Handheld Multi-Probe System; pH Probe with Connector
- 13-298-66** - Each for \$312.00  
pH/ORP probe

### Yellow Springs Instrument Pro Series Dissolved Oxygen Cables

- 15-177-470** - Each for \$235.88  
Cable; Dissolved Oxygen/Temperature; 4m cable assembly
- 15-177-471** - Each for \$285.36  
10m cable assembly
- 15-177-472** - Each for \$335.42  
20m cable assembly

## Filtration

### Fisherbrand Filter Forceps



- 09-753-50** - Each for \$14.71  
Forcep, Filter; Fisherbrand; Stainless-steel construction; Serrated grip on blades; Won't corrode in acids or acidic atmospheres; Length: 4-1/2 in.

### Fisherbrand Filters for TCLP



- 09-804-142H** - Pack of 100 for \$27.00  
Filters for TCLP; Fisherbrand; Diameter: 47mm; Recommended Filter Holder: 09-753-1A
- 09-804-142J** - Pack of 100 for \$58.12  
Diameter: 90mm; Recommended Filter Holder: 09-753-2
- 09-804-142G** - Pack of 100 for \$109.50  
Diameter: 142mm; Recommended Filter Holder: 09-753-25J

### Fisherbrand Fluted Qualitative Circles



- 09-790-14D** - Pack of 100 for \$54.82  
Filter Paper; Fluted; Qualitative Circles; Fisherbrand; Diameter: 12.5cm; Grade: P8--Fluted
- 09-790-14E** - Pack of 100 for \$59.58  
Diameter: 15cm
- 09-790-14F** - Pack of 100 for \$64.90  
Diameter: 18.5cm
- 09-790-14G** - Pack of 100 for \$68.27  
Diameter: 24cm

### Fisherbrand Glass Fiber Circles



- 09-804-125A** - Pack of 100 for \$87.19  
Filters; Glass Fiber Circles; Fisherbrand; Ideal as prefilters and for gravimetric analyses; Fast flow; High retention; Diameter: 125mm; Grade G1
- 09-804-21B** - Pack of 100 for \$36.29  
Grade G2; Diameter: 21mm
- 09-804-42B** - Pack of 100 for \$48.08  
Grade G2; Diameter: 42.5mm
- 09-804-55B** - Pack of 100 for \$63.29  
Grade G2; Diameter: 55mm
- 09-804-21C** - Pack of 100 for \$36.77  
Grade G4; Diameter: 21mm
- 09-804-24C** - Pack of 100 for \$39.48  
Grade G4; Diameter: 24mm
- 09-804-42C** - Pack of 100 for \$47.53  
Grade G4; Diameter: 42.5mm
- 09-804-55C** - Pack of 100 for \$60.13  
Grade G4; Diameter: 55mm
- 09-804-70C** - Pack of 100 for \$77.97  
Grade G4; Diameter: 70mm
- 09-804-90C** - Pack of 100 for \$109.37  
Grade G4; Diameter: 90mm
- 09-804-21A** - Pack of 100 for \$18.86  
Grade G6; Diameter: 21mm
- 09-804-24A** - Pack of 100 for \$20.16  
Grade G6; Diameter: 24mm
- 09-804-42A** - Pack of 100 for \$24.32  
Grade G6; Diameter: 42.5mm

- 09-804-55A** - Pack of 100 for \$26.88  
Grade G6; Diameter: 55mm
- 09-804-70A** - Pack of 100 for \$31.90  
Grade G6; Diameter: 70mm
- 09-804-90A** - Pack of 100 for \$51.47  
Grade G6; Diameter: 90mm
- 09-804-110A** - Pack of 100 for \$80.58  
Grade G6; Diameter: 110mm
- 09-804-150A** - Pack of 100 for \$90.43  
Grade G6; Diameter: 150mm
- 09-804-21D** - Pack of 100 for \$21.93  
Grade G8; Diameter: 21mm
- 09-804-25D** - Pack of 100 for \$23.52  
Grade G8; Diameter: 25mm
- 09-804-42D** - Pack of 100 for \$28.37  
Grade G8; Diameter: 42.5mm
- 09-804-55D** - Pack of 100 for \$40.30  
Grade G8; Diameter: 55mm
- 09-804-70D** - Pack of 100 for \$52.99  
Grade G8; Diameter: 70mm

### Fisherbrand Glass Microanalysis Vacuum Filter Holders



- 09-753A** - Each for \$212.45  
Holder, Filter; Fisherbrand; Glass; For microanalysis vacuum filters; Filter: 25mm; Prefilter: Not recommended; No. 5 silicone stopper; For 100mL Funnels
- 09-753C** - Each for \$234.74  
Filter: 25mm; Prefilter: Not recommended; No. 5 silicone stopper; For 13mL/100mL Funnels
- 09-753-102** - Each for \$326.35  
Filter: 47mm; Prefilter: 35mm; 40/35 ST manifold adapter; Fritted Glass Support
- 09-753-1A** - Each for \$214.43  
Filter: 47mm; Prefilter: 35mm; No. 8 silicone stopper; Fritted Glass Support
- 09-753-1E** - Each for \$342.00  
Filter: 47mm; Prefilter: 35mm; No. 8 silicone stopper; PTFE Gasket and Flange
- 09-753-1C** - Each for \$233.35  
Filter: 47mm; Prefilter: 35mm; No. 8 silicone stopper; Steel Support (100 mesh)
- 09-753-2** - Each for \$576.13  
Filter: 90mm(82mm, microbiology); Prefilter: 70mm; No. 8 silicone stopper; Fritted Glass Support
- 09-753E** - Each for \$194.81  
Small Biological Particulate; Filter: 25mm; No. 5 silicone stopper; Fritted Glass Support
- 09-753G** - Each for \$224.51  
Small Biological Particulate; Filter: 25mm; No. 5 silicone stopper; Stainless Steel Support

### Fisherbrand Qualitative Grade Plain Circles and Sheets - P2 Grade



- 09-803-5B** - Pack of 100 for \$8.42  
Filter Paper, Qualitative; Fisherbrand; Grade P2; Cellulose fiber; Particle Retention: 1-5um; Porosity: Fine; Filtration Speed: Herzberg, 1400 seconds; Flowrate: Slow-5mL/min.; Circles; 7cm dia.
- 09-803-5C** - Pack of 100 for \$10.63  
Circles; 9cm dia.
- 09-803-5D** - Pack of 100 for \$17.01  
Circles; 11cm dia.
- 09-803-5E** - Pack of 100 for \$15.33  
Circles; 12.5cm dia.
- 09-803-5F** - Pack of 100 for \$20.70  
Circles; 15cm dia.
- 09-803-5A** - Pack of 100 for \$6.04  
Circles; 5.5cm dia.

### Fisherbrand Qualitative Grade Plain Circles and Sheets - P4 Grade



- 09-803-6A** - Pack of 100 for \$7.14  
Filter Paper, Qualitative; Fisherbrand; Grade P4; Cellulose fiber; Particle Retention: 4-8um; Porosity: Fine; Filtration Speed: Herzberg, 730 seconds; Flowrate: Slow-25mL/min.; Circles; 4.25cm dia.
- 09-803-6B** - Pack of 100 for \$7.12  
Circles; 5.5cm dia.
- 09-803-6C** - Pack of 100 for \$8.24  
Circles; 7cm dia.



**09-803-6D** - Pack of 100 for \$13.16  
Circles; 9cm dia.  
**09-803-6G** - Pack of 100 for \$26.35  
Circles; 15cm dia.  
**09-803-6E** - Pack of 100 for \$16.80  
Circles; 11cm dia.  
**09-803-6F** - Pack of 100 for \$17.90  
Circles; 12.5cm dia.  
**09-803-6H** - Pack of 100 for \$33.14  
Circles; 18.5cm dia.  
**09-803-6J** - Pack of 100 for \$51.44  
Circles; 20.5cm dia.  
**09-803-6K** - Pack of 100 for \$58.14  
Circles; 24cm dia.

### Fisherbrand Qualitative Grade Plain Circles and Sheets - P5 Grade



**09-801AA** - Pack of 100 for \$5.58  
Filter Paper, Qualitative; Fisherbrand; Grade P5;  
Cellulose fiber; Particle Retention: 5-10um; Porosity:  
Medium; Filtration Speed: Herzberg, 230 seconds;  
Flowrate: Slow-60mL/min.; Circles; 2.5cm dia.  
**09-801BB** - Pack of 100 for \$5.31  
Circles; 3.5cm dia.  
**09-801J** - Pack of 100 for \$6.74  
Circles; 4.25cm dia.  
**09-801K** - Pack of 100 for \$5.57  
Circles; 5.5cm dia.  
**09-801A** - Pack of 100 for \$6.67  
Circles; 7cm dia.  
**09-801B** - Pack of 100 for \$7.59  
Circles; 9cm dia.  
**09-801C** - Pack of 100 for \$7.93  
Circles; 11cm dia.  
**09-801D** - Pack of 100 for \$12.88  
Circles; 12.5cm dia.  
**09-801E** - Pack of 100 for \$21.83  
Circles; 15cm dia.  
**09-801F** - Pack of 100 for \$21.28  
Circles; 19cm dia.  
**09-801G** - Pack of 100 for \$37.50  
Circles; 24cm dia.  
**09-801H** - Pack of 100 for \$74.31  
Circles; 33cm dia.  
**09-802-1A** - Pack of 100 for \$132.97  
Sheets; 46 x 57cm  
**09-802** - Pack of 500 for \$265.62  
Sheets; 50 x 50cm

### Fisherbrand Qualitative Grade Plain Circles and Sheets - P8 Grade



**09-795AA** - Pack of 100 for \$5.05  
Filter Paper, Qualitative; Fisherbrand; Grade P8;  
Cellulose fiber; Particle Retention: 20-25um; Porosity:  
Coarse; Filtration Speed: Herzberg, 55 seconds;  
Flowrate: Fast-160mL/min.; Circles; 2.5cm dia.  
**09-795BB** - Pack of 100 for \$5.51  
Circles; 3.5cm dia.  
**09-795A** - Pack of 100 for \$5.34  
Circles; 5.5cm dia.  
**09-795B** - Pack of 100 for \$6.16  
Circles; 7cm dia.  
**09-795C** - Pack of 100 for \$7.27  
Circles; 9cm dia.  
**09-795D** - Pack of 100 for \$8.66  
Circles; 11cm dia.  
**09-795E** - Pack of 100 for \$8.95  
Circles; 12.5cm dia.  
**09-795F** - Pack of 100 for \$12.01  
Circles; 15cm dia.  
**09-795G** - Pack of 100 for \$16.51  
Circles; 18.5cm dia.  
**09-804** - Pack of 100 for \$21.64  
Circles; 19cm dia.  
**09-795H** - Pack of 100 for \$25.17  
Circles; 20.5cm dia.  
**09-795J** - Pack of 100 for \$26.30  
Circles; 24cm dia.  
**09-795K** - Pack of 100 for \$50.33  
Circles; 33cm dia.

**09-802-1B** - Pack of 100 for \$108.88  
Sheets; 46 x 57cm  
**09-800** - Pack of 500 for \$251.64  
Sheets; 50 x 50cm

### Fisherbrand Quantitative Grade Circles



**09-790-2A** - Pack of 100 for \$12.98  
Filter Paper, Quantitative; Fisherbrand; Circles; Grade:  
Q2; Particle retention: 1-5um; Porosity: Fine; Filtration  
speed: Slow; Surface: Smooth, dense texture; Diameter:  
5.5cm  
**09-790-2B** - Pack of 100 for \$15.73  
Grade Q2; Diameter: 7cm  
**09-790-2C** - Pack of 100 for \$22.60  
Grade Q2; Diameter: 9cm  
**09-790-2D** - Pack of 100 for \$27.98  
Grade Q2; Diameter: 11cm  
**09-790-2E** - Pack of 100 for \$33.55  
Grade Q2; Diameter: 12.5cm  
**09-790-2F** - Pack of 100 for \$41.72  
Grade Q2; Diameter: 15cm  
**09-790-2G** - Pack of 100 for \$62.49  
Grade Q2; Diameter: 18.5cm  
**09-790-4C** - Pack of 100 for \$22.58  
Grade Q5; Diameter: 9cm  
**09-790-4D** - Pack of 100 for \$28.24  
Grade Q5; Diameter: 11 cm  
**09-790-4E** - Pack of 100 for \$31.73  
Grade Q5; Diameter: 12.5cm  
**09-790-4F** - Pack of 100 for \$42.53  
Grade Q5; Diameter: 15cm  
**09-790A** - Pack of 100 for \$13.05  
Grade Q8; Diameter: 5.5cm  
**09-790B** - Pack of 100 for \$15.77  
Grade Q8; Diameter: 7cm  
**09-790C** - Pack of 100 for \$21.97  
Grade Q8; Diameter: 9cm  
**09-790D** - Pack of 100 for \$27.99  
Grade Q8; Diameter: 11 cm  
**09-790E** - Pack of 100 for \$35.82  
Grade Q8; Diameter: 12.5cm  
**09-790F** - Pack of 100 for \$42.51  
Grade Q8; Diameter: 15cm  
**09-790G** - Pack of 100 for \$64.65  
Grade Q8; Diameter: 18.5cm


### Fisherbrand Vacuum Filter Holder Replacement Parts and Accessories

**09-753-4** - Each for \$35.98  
Accessory, Replacement; Fisherbrand; Replacement parts for Vacuum Filter  
Holders; Anodized Aluminum Clamp; For Diameter: 13, and 25mm  
**09-753-31A** - Each for \$29.77  
Anodized Aluminum Clamp; For Diameter: 47mm  
**09-753-31B** - Each for \$113.36  
Anodized Aluminum Clamp; For Diameter: 90mm  
**09-753-104** - Each for \$111.34  
Filtration Flask; Capacity: 1000mL, Joint: 40/35  
**09-753-101** - Each for \$64.30  
Filtration Flask; Capacity: 1000mL, Joint: 8  
**09-753-100** - Each for \$36.12  
Filtration Flask; Capacity: 125mL, Joint: 5  
**09-753-3** - Each for \$69.84  
Glass Funnel; Capacity: 100mL  
**09-753-34A** - Each for \$102.84  
Glass Funnel; Capacity: 100mL, 47mm, Straightwall  
**09-753-7** - Each for \$84.06  
Glass Funnel; Capacity: 100mL, Adapter/Micro  
**09-753-8** - Each for \$62.62  
Glass Funnel; Capacity: 13mL  
**09-753-19** - Each for \$132.02  
Glass Funnel; Capacity: 150mL  
**09-753-13** - Each for \$61.98  
Glass Funnel; Capacity: 15mL; 25mm  
**09-753-26B** - Each for \$249.73  
Glass Funnel; Capacity: 1L, Diameter: 90mm  
**09-753-20** - Each for \$132.34  
Glass Funnel; Capacity: 300mL, Diameter: 25mm  
**09-753-26A** - Each for \$70.57  
Glass Funnel; Capacity: 300mL, Diameter: 47mm  
**09-753-26C** - Each for \$101.70  
Glass Funnel; Capacity: 300mL, Diameter: 47mm, PTFE Coated

- 09-753-34B** - Each for \$130.44  
Glass Funnel; Capacity: 500mL, 47mm
- 09-753-17** - Each for \$86.78  
Glass Support Base; 25mm; Stainless steel support
- 09-753-14** - Each for \$107.64  
Glass Support Base; 25mm; With: fritted support
- 09-753-103** - Each for \$177.53  
Glass Support Base; 47mm; Joint: 40/35; With fritted support
- 09-753-27A** - Each for \$101.22  
Glass Support Base; Diameter: 47mm; With fritted support
- 09-753-28C** - Each for \$141.76  
Glass Support Base; Diameter: 47mm; With PTFE gasket/flange
- 09-753-28A** - Each for \$92.74  
Glass Support Base; Diameter: 47mm; With stainless steel support
- 09-753-27B** - Each for \$391.98  
Glass Support Base; Diameter: 90mm; With fritted support
- 09-753-30B** - Each for \$39.84  
PTFE Flange; 47mm
- 09-753-18** - Each for \$3.47 and Pack of 25 for \$63.27  
PTFE Gasket; 25mm
- 09-753-30A** - Each for \$3.57 and Pack of 25 for \$65.03  
PTFE Gasket; 47mm
- 09-753-6** - Each for \$8.52  
Silicone Rubber Stoppers; No. 5; Perforated
- 09-753-32A** - Each for \$7.95  
Silicone Rubber Stoppers; No. 8; Perforated
- 09-753-9** - Each for \$26.69  
Silicone Rubber Stoppers; No. 8B, Adapts To Manifold
- 09-753-15** - Each for \$96.60  
Stainless Steel Support Screen; 25mm
- 09-753-29A** - Each for \$62.96  
Stainless Steel Support Screen; 47mm

- G25WP02200** - Pack of 100 for \$47.73  
Grade G25, With Binders; Diameter: 22mm
- G25WP02500** - Pack of 100 for \$43.57  
Grade G25, with Binders; Diameter: 25mm
- G25WP04700** - Pack of 100 for \$55.96  
Grade G25, with Binders; Diameter: 47mm
- G25WP09025** - Pack of 25 for \$41.26  
Grade G25, With Binders; Diameter: 90mm
- G25WP12425** - Pack of 25 for \$63.00  
Grade G25, with Binders; Diameter: 124mm
- G25WP14225** - Pack of 25 for \$73.57  
Grade G25, with Binders; Diameter: 142mm
- G40WP03705** - Pack of 500 for \$141.75  
Grade G40, Without Binders; Diameter: 37mm
- G40WP04705** - Pack of 500 for \$176.17  
Grade G40; Without Binders; Diameter: 47mm

GE PCTE Filter Membranes: Plain Black for Epifluorescence




- 09-732-15** - Pack of 100 for \$73.70  
Filter, Membrane; GE; Plain; Black color to aid in epifluorescence; Polycarbonate, Track-Etched membrane; Pore Size: 0.1um; Diameter: 25mm
- 09-732-2** - Pack of 100 for \$63.55  
Pore Size: 0.2um; Diameter: 13mm
- 09-732-18** - Pack of 100 for \$72.57  
Pore Size: 0.2um; Diameter: 25mm
- 09-732-20** - Pack of 100 for \$72.57  
Pore Size: 0.4um; Diameter: 25mm

Fisherbrand Wet-Strengthened Qualitative Circles




- 09-790-12C** - Pack of 100 for \$8.39  
Filter Paper; Qualitative; Fisherbrand; Wet-Strengthened; Circles; Coarse cellulose fiber; Creped surface; Fast flowrate; Particle Retention >25um; Diameter: 9cm
- 09-790-12D** - Pack of 100 for \$10.06  
Diameter: 11cm
- 09-790-12E** - Pack of 100 for \$13.97  
Diameter: 12.5cm
- 09-790-12F** - Pack of 100 for \$16.82  
Diameter: 15cm
- 09-790-12G** - Pack of 100 for \$23.48  
Diameter: 18.5cm

GE PCTE Filter Membranes: Plain Hydrophilic




- 09-732** - Pack of 100 for \$86.11  
Filter, Membrane; GE; Plain; Hydrophilic; Polycarbonate, Track-Etched; Pore Size: 0.1um; Diameter: 13mm
- 09-732-16** - Pack of 100 for \$98.68  
Pore Size: 0.1um; Diameter: 25mm
- 09-732-34** - Pack of 100 for \$149.07  
Pore Size: 0.1um; Diameter: 47mm
- 09-732-1** - Pack of 100 for \$54.91  
Pore Size: 0.2um; Diameter: 13mm
- 09-732-17** - Pack of 100 for \$62.39  
Pore Size: 0.2um; Diameter: 25mm
- 09-732-35** - Pack of 100 for \$100.79  
Pore Size: 0.2um; Diameter: 47mm
- 09-732-3** - Pack of 100 for \$54.91  
Pore Size: 0.4um; Diameter: 13mm
- 09-732-19** - Pack of 100 for \$62.39  
Pore Size: 0.4um; Diameter: 25mm
- 09-732-32** - Pack of 100 for \$80.86  
Pore Size: 0.4um; Diameter: 37mm
- 09-732-37** - Pack of 100 for \$100.79  
Pore Size: 0.4um; Diameter: 47mm
- 09-732-21** - Pack of 100 for \$70.55  
Pore Size: 0.6um; Diameter: 25mm
- 09-732-41** - Pack of 100 for \$109.20  
Pore Size: 1.0um; Diameter: 47mm
- 09-732-7** - Pack of 100 for \$61.95  
Pore Size: 2.0um; Diameter: 13mm
- 09-732-23** - Pack of 100 for \$72.44  
Pore Size: 2.0um; Diameter: 25mm
- 09-732-9** - Pack of 100 for \$61.95  
Pore Size: 3.0um; Diameter: 13mm
- 09-732-25** - Pack of 100 for \$70.39  
Pore Size: 3.0um; Diameter: 25mm
- 09-732-42** - Pack of 100 for \$109.20  
Pore Size: 3.0um; Diameter: 47mm
- 09-732-11** - Pack of 100 for \$61.95  
Pore Size: 5.0um; Diameter: 13mm
- 09-732-27** - Pack of 100 for \$72.44  
Pore Size: 5.0um; Diameter: 25mm
- 09-732-43** - Pack of 100 for \$109.20  
Pore Size: 5.0um; Diameter: 47mm
- 09-731-89** - Pack of 100 for \$61.95  
Pore Size: 8.0um; Diameter: 13mm
- 09-732-44** - Pack of 100 for \$109.20  
Pore Size: 8.0um; Diameter: 47mm

GE Glass Prefilters




- G15WP02200** - Pack of 100 for \$51.76  
Filters; GE; Glass; Grade G15, with Binders; Borosilicatematrix bonded by acrylic resin; Extra thick for increased throughput; High wet strength; Diameter: 22mm
- G15WP02500** - Pack of 100 for \$51.76  
Grade G15, with Binders; Diameter: 25mm
- G15WP04200** - Pack of 100 for \$56.83  
Grade G15, with Binders; Diameter: 42mm
- G15WP04700** - Pack of 100 for \$70.57  
Grade G15, with Binders; Diameter: 47mm
- G15WP07525** - Pack of 25 for \$78.71  
Grade G15, with Binders; Diameter: 75mm
- G15WP09025** - Pack of 25 for \$86.11  
Grade G15, with Binders; Diameter: 90mm
- G15WP12425** - Pack of 25 for \$88.58  
Grade G15, with Binders; Diameter: 124mm
- G15WP14225** - Pack of 25 for \$88.21  
Grade G15, with Binders; Diameter: 142mm
- G20WP01300** - Pack of 100 for \$46.38  
Grade G20; With Binders; Diameter: 13mm
- G20WP02500** - Pack of 100 for \$46.38  
Grade G20; With Binders; Diameter: 25mm
- G20WP04200** - Pack of 100 for \$55.96  
Grade G20; With Binders; Diameter: 42mm
- G20WP04700** - Pack of 100 for \$55.96  
Grade G20; With Binders; Diameter: 47mm
- G20WP09025** - Pack of 25 for \$43.57  
Grade G20; With Binders; Diameter: 90mm
- G20WP12425** - Pack of 25 for \$63.35  
Grade G20; With Binders; Diameter: 124mm
- G25WP01000** - Pack of 100 for \$41.26  
Grade G25, with Binders; Diameter: 10mm
- G25WP01300** - Pack of 100 for \$42.56  
Grade G25, with Binders; Diameter: 13mm

### Millipore Glass Fiber Filters



- AP1502200** - Pack of 100 for \$33.00  
Filters; Glass Fiber; Millipore; For prefiltration and contamination analysis; Made of borosilicate microfiber glass with acrylic binder resin; Grade: AP15; Thickness: 0.790mm; Flowrate: 3–3.5 sec./100mL; Diameter: 22mm
- AP1502500** - Pack of 100 for \$34.00  
Grade: AP15; Diameter: 25mm
- AP1504200** - Pack of 100 for \$50.00  
Grade: AP15; Diameter: 42mm
- AP1504700** - Pack of 100 for \$53.00  
Grade: AP15; Diameter: 47mm
- AP1507500** - Pack of 100 for \$76.00  
Grade: AP15; Diameter: 75mm
- AP1509000** - Pack of 100 for \$88.00  
Grade: AP15; Diameter: 90mm
- AP1512450** - Pack of 50 for \$113.00  
Grade: AP15; Diameter: 124mm
- AP1514250** - Pack of 50 for \$136.00  
Grade: AP15; Diameter: 142mm
- AP2001000** - Pack of 100 for \$33.00  
Grade: AP20; Diameter: 10mm
- AP2001300** - Pack of 100 for \$34.00  
Grade: AP20; Diameter: 13mm
- AP2002500** - Pack of 100 for \$34.00  
Grade: AP20; Diameter: 25mm
- AP2004200** - Pack of 100 for \$50.00  
Grade: AP20; Diameter: 42mm
- AP2004700** - Pack of 100 for \$53.00  
Grade: AP20; Diameter: 47mm
- AP2007500** - Pack of 100 for \$76.00  
Grade: AP20; Diameter: 75mm
- AP2009000** - Pack of 100 for \$88.00  
Grade: AP20; Diameter: 90mm
- AP2012450** - Pack of 50 for \$113.00  
Grade: AP20; Diameter: 124mm
- AP2014250** - Pack of 50 for \$136.00  
Grade: AP20; Diameter: 142mm
- AP2501000** - Pack of 100 for \$34.00  
Grade: AP25; Diameter: 10mm
- AP2501300** - Pack of 100 for \$34.00  
Grade: AP25; Diameter: 13mm
- AP2502200** - Pack of 100 for \$34.00  
Grade: AP25; Diameter: 22mm
- AP2502500** - Pack of 100 for \$34.00  
Grade: AP25; Diameter: 25mm
- AP2504200** - Pack of 100 for \$50.00  
Grade: AP25; Diameter: 42mm
- AP2504700** - Pack of 100 for \$53.00  
Grade: AP25; Diameter: 47mm
- AP2507500** - Pack of 100 for \$66.00  
Grade: AP25; Diameter: 75mm
- AP2509000** - Pack of 100 for \$88.00  
Grade: AP25; Diameter: 90mm
- AP2512450** - Pack of 50 for \$113.00  
Grade: AP25; Diameter: 124mm
- AP2514250** - Pack of 50 for \$136.00  
Grade: AP25; Diameter: 142mm


### Millipore Glass Fiber Filters without Binders



- APFA02500** - Pack of 100 for \$23.00  
Filters; Glass Fiber; Millipore; Without binders; Autoclavable; For wastewater monitoring, collection of suspended particles, cell collection, and filtration; Grade: APFA; Particle Retention 1.6um; Diameter: 25mm
- APFA04700** - Pack of 100 for \$34.00  
Grade: APFA; Particle Retention 1.6um; Diameter: 47mm
- APFA09050** - Pack of 50 for \$44.00  
Grade: APFA; Particle Retention 1.6um; Diameter: 90mm
- APFB02500** - Pack of 100 for \$44.00  
Grade: APFB; Particle Retention 1.0um; Diameter: 25mm
- APFB04700** - Pack of 100 for \$53.00  
Grade: APFB; Particle Retention 1.0um; Diameter: 47mm
- APFC02500** - Pack of 100 for \$44.00  
Grade: APFC; Particle Retention 1.2um; Diameter: 25mm
- APFC04700** - Pack of 100 for \$53.00  
Grade: APFC; Particle Retention 1.2um; Diameter: 47mm
- APFC09050** - Pack of 50 for \$59.00  
Grade: APFC; Particle Retention 1.2um; Diameter: 90mm
- APFD02500** - Pack of 100 for \$23.00  
Grade: APFD; Particle Retention 2.7um; Diameter: 25mm


- APFD04700** - Pack of 100 for \$34.00  
Grade: APFD; Particle Retention 2.7um; Diameter: 47mm
- APFD09050** - Pack of 50 for \$44.00  
Grade: APFD; Particle Retention 2.7um; Diameter: 90mm
- APFF02500** - Pack of 100 for \$68.00  
Grade: APFF; Particle Retention 0.7um; Diameter: 25mm
- APFF04700** - Pack of 100 for \$82.00  
Grade: APFF; Particle Retention 0.7um; Diameter: 47mm
- APFF09050** - Pack of 50 for \$97.00  
Grade: APFF; Particle Retention 0.7um; Diameter: 90mm

### Millipore Quartz Fiber Filters



- AQFA03200** - Pack of 100 for \$84.00  
Filters; Quartz Fiber; Millipore; Perfect for measuring heavy metal concentrations and small amounts of particles; Suitable for use in U.S. EPA PM10 ambient air monitoring method; Can be sterilized by EtO, gamma, autoclave; Diameter: 32mm
- AQFA03700** - Pack of 100 for \$97.00  
Diameter: 37mm
- AQFA04700** - Pack of 100 for \$112.00  
Diameter: 47mm
- AQFA05500** - Pack of 100 for \$117.00  
Diameter: 55mm
- AQFA09050** - Pack of 50 for \$117.00  
Diameter: 90mm
- AQFA11050** - Pack of 50 for \$140.00  
Diameter: 110mm

### Millipore Reinforced Membrane Filters



- RW0304700** - Pack of 100 for \$52.00  
Filters; Millipore; Reinforced membrane; Made of homogenous microporous polymers of cellulose esters around a polyester web; Autoclavable; Grade: RW03; Particle retention: 0.45um; Diameter: 47mm
- RW0309000** - Pack of 100 for \$97.00  
Grade: RW03; Particle retention: 0.45um; Diameter: 90mm
- RW0614250** - Pack of 50 for \$112.00  
Grade: RW06; Particle retention: 0.8um; Diameter: 142mm
- RW0604700** - Pack of 100 for \$52.00  
Grade: RW06; Particle retention: 0.8um; Diameter: 47mm
- RW0609000** - Pack of 100 for \$97.00  
Grade: RW06; Particle retention: 0.8um; Diameter: 90mm
- RW1914250** - Pack of 50 for \$112.00  
Grade: RW19; Particle retention: 1.2um; Diameter: 142mm
- RW1904700** - Pack of 100 for \$52.00  
Grade: RW19; Particle retention: 1.2um; Diameter: 47mm
- RW1909000** - Pack of 100 for \$97.00  
Grade: RW19; Particle retention: 1.2um; Diameter: 90mm

### Millipore Silver Membrane Filters



- AG4502550** - Pack of 50 for \$381.00  
Filters, Membrane; Millipore; Pure Metallic Silver Disc; Type: Plain; 0.45um Pore Size; Diameter: 25mm
- AG8003750** - Pack of 50 for \$677.60  
0.8um Pore size; Diameter: 37mm

### Whatman Binder-Free Glass Microfiber Filters: Type 934-AH



- 09-873A** - Pack of 100 for \$19.49  
Filters; Binder-free glass microfiber; Whatman; Type 934-AH; Circle; High retention efficiency at high flowrate; Autoclavable to 500 deg. C; For air and water pollution monitoring, cell harvesting, liquid scintillation; Dia.: 2.1cm
- 09-873B** - Pack of 100 for \$23.32  
Circle; Diameter: 2.4cm
- 09-870A** - Pack of 100 for \$21.80  
Circle; Diameter: 2.5cm
- 09-870C** - Pack of 100 for \$23.80  
Circle; Diameter: 3.0cm

- 09-873BB** - Pack of 100 for \$25.57  
Circle; Diameter: 3.2cm
- 09-870D** - Pack of 100 for \$28.31  
Circle; Diameter: 3.5cm
- 09-873C** - Pack of 100 for \$28.31  
Circle; Diameter: 3.7cm
- 09-873D** - Pack of 100 for \$30.95  
Circle; Diameter: 4.25cm
- 09-873DD** - Pack of 100 for \$39.22  
Circle; Diameter: 4.7cm
- 09-873E** - Pack of 100 for \$42.40  
Circle; Diameter: 5.5cm
- 09-873F** - Pack of 100 for \$51.11  
Circle; Diameter: 7.0cm
- 09-874** - Each for \$75.34  
Circle; Diameter: 8.26cm
- 09-873G** - Pack of 100 for \$85.86  
Circle; Diameter: 9.0cm
- 09-870F** - Pack of 100 for \$97.25  
Circle; Diameter: 10.5cm
- 09-873H** - Pack of 100 for \$97.52  
Circle; Diameter: 11.0cm
- 09-873J** - Pack of 100 for \$118.72  
Circle; Diameter: 12.5cm
- 09-873K** - Pack of 100 for \$152.38  
Circle; Diameter: 15cm
- 09-870H** - Pack of 100 for \$229.57  
Circle; Diameter: 18.5cm
- 09-870J** - Pack of 100 for \$388.03  
Circle; Diameter: 24.0cm
- 09-870K** - Pack of 100 for \$650.61  
Circle; Diameter: 32.0cm
- 09-870Q** - Pack of 100 for \$294.68  
Sheet; Dimensions: 20L x 25cmW
- 09-870S** - Pack of 100 for \$590.44  
Sheet; Dimensions: 30L x 38cmW
- 09-874-65** - Pack of 100 for \$93.73  
Sheet; Dimensions: 5L x 31cmW

Whatman Binder Free Glass Microfiber Filters: Type GF/A



- 09-874-10** - Pack of 100 for \$24.40  
Filters; Binder-free glass microfiber; Whatman; Type GF/A; Circle; Extra thick; For water and air pollution monitoring, filtering water, algae, bacterial cultures, Foodstuff analyses; Protein filtration; Radioimmunoassay; Diameter: 2.1cm
- 09-874-12** - Pack of 100 for \$24.51  
Circle; Diameter: 2.4cm
- 09-874-12A** - Pack of 100 for \$24.51  
Circle; Diameter: 2.5cm
- 09-874-12B** - Pack of 100 for \$27.88  
Circle; Diameter: 3.7cm
- 09-874-14** - Pack of 100 for \$29.61  
Circle; Diameter: 4.25cm
- 09-874-14A** - Pack of 100 for \$33.49  
Circle; Diameter: 4.7cm
- 09-874-16** - Pack of 100 for \$35.60  
Circle; Diameter: 5.5cm
- 09-874-16A** - Pack of 100 for \$42.93  
Circle; Diameter: 7.0cm
- 09-874-16B** - Pack of 100 for \$63.61  
Circle; Diameter: 9.0cm
- 09-874-16G** - Pack of 25 for \$483.81  
Sheet; Dimensions: 46L x 57cmW
- 09-874-16C** - Pack of 100 for \$100.96  
Circle; Diameter: 11cm
- 09-874-16D** - Pack of 100 for \$128.59  
Circle; Diameter: 12.5cm
- 09-874-16E** - Pack of 100 for \$217.60  
Circle; Diameter: 15.0cm

Whatman Binder-Free Glass Microfiber Filters: Type GF/B



- 09-874-20** - Pack of 100 for \$44.66  
Filters; Binder-free glass microfiber; Whatman; Type GF/B; Circle; Extra thick; High wet strength and loading capacity; Used in LSC techniques; Can be used as a finely retentive membrane filter; Diameter: 2.1cm
- 09-874-22** - Pack of 100 for \$46.18  
Circle; Diameter: 2.4cm
- 09-874-22A** - Pack of 100 for \$48.57  
Circle; Diameter: 2.5cm

- 09-874-22B** - Pack of 100 for \$59.03  
Circle; Diameter: 3.7cm
- 09-874-24** - Pack of 100 for \$64.37  
Circle; Diameter: 4.25cm
- 09-874-24A** - Pack of 100 for \$76.40  
Circle; Diameter: 4.7cm
- 09-874-26** - Pack of 100 for \$82.74  
Circle; Diameter: 5.5cm
- 09-874-26A** - Pack of 100 for \$110.71  
Circle; Diameter: 7.0cm
- 09-874-26B** - Pack of 25 for \$39.62  
Circle; Diameter: 9.0cm
- 09-874-26C** - Pack of 25 for \$54.93  
Circle; Diameter: 11.0cm
- 09-874-26D** - Pack of 25 for \$70.07  
Circle; Diameter: 12.5cm
- 09-874-26E** - Pack of 25 for \$105.21  
Circle; Diameter: 15.0cm
- 09-874-28A** - Pack of 25 for \$1065.72  
Sheet; Dimensions: 46L x 57cmW; 25 per pack
- 09-874-28** - Pack of 5 for \$270.51  
Sheet; Dimensions: 46L x 57cmW; 5 per pack

Whatman Binder-Free Glass Microfiber Filters: Type GF/C



- 09-874-30** - Pack of 100 for \$49.43  
Filters; Binder-free glass microfiber; Whatman; Type GF/C; Circle; For air monitoring, collection of suspended solids, clarification of aqueous liquids, cell harvesting, liquid scintillation counting, radioimmunoassay; Diameter: 2.1cm
- 09-874-32** - Pack of 100 for \$51.52  
Circle; Diameter: 2.4cm
- 09-874-32A** - Pack of 100 for \$51.52  
Circle; Diameter: 2.5cm
- 09-874-32B** - Pack of 100 for \$58.65  
Circle; Diameter: 3.7cm
- 09-874-34** - Pack of 100 for \$58.65  
Circle; Diameter: 4.25cm
- 09-874-35** - Pack of 100 for \$78.38  
Circle; Diameter: 4.7cm
- 09-874-36** - Pack of 100 for \$90.92  
Circle; Diameter: 5.5cm
- 09-874-38** - Pack of 100 for \$100.97  
Circle; Diameter: 7.0cm
- 09-874-39** - Pack of 100 for \$141.11  
Circle; Diameter: 9cm
- 09-874-36A** - Pack of 100 for \$218.76  
Circle; Diameter: 11cm
- 09-874-37** - Pack of 100 for \$241.63  
Circle; Diameter: 12.5cm
- 09-874-37A** - Pack of 100 for \$419.64  
Circle; Diameter: 15.0cm
- 09-874-40A** - Pack of 25 for \$770.22  
Sheet; Dimensions: 46L x 57cmW

Whatman Binder-Free Glass Microfiber Filters: Type GF/D



- 09-874-40B** - Pack of 100 for \$28.79  
Filters; Binder-free glass microfiber; Whatman; Type GF/D; Circle; Autoclavable; For general purpose, routine, solvent filtrations; Effective prefilter for membranes; Very high loading capacity and wet strength; Diameter: 1.0cm
- 09-874-41** - Pack of 100 for \$28.79  
Circle; Diameter: 2.1cm
- 09-874-42A** - Pack of 100 for \$28.79  
Circle; Diameter: 2.4cm
- 09-874-44** - Pack of 100 for \$28.79  
Circle; Diameter: 2.5cm
- 09-874-46B** - Pack of 100 for \$37.35  
Circle; Diameter: 4.25cm
- 09-874-48** - Pack of 100 for \$43.52  
Circle; Diameter: 4.7cm
- 09-874-46C** - Pack of 100 for \$50.04  
Circle; Diameter: 5.5cm
- 09-874-47** - Pack of 100 for \$69.49  
Circle; Diameter: 7.0cm
- 09-874-47A** - Pack of 25 for \$28.81  
Circle; Diameter: 9.0cm
- 09-874-47B** - Pack of 25 for \$38.21  
Circle; Diameter: 11.0cm
- 09-874-47C** - Pack of 25 for \$52.48  
Circle; Diameter: 12.5cm

- 09-874-47H** - Pack of 25 for \$83.51  
Circle; Diameter: 14.2cm  
**09-874-47D** - Pack of 25 for \$86.93  
Circle; Diameter: 15.0cm  
**09-874-47E** - Pack of 25 for \$115.26  
Circle; Diameter: 25.7cm

### Whatman Binder-Free Glass Microfiber Filters: Type GF/F



- 09-874-60** - Pack of 100 for \$77.72  
Filters; Binder-free glass microfiber; Whatman; Type GF/F; Retain fine particles down to 0.7µm; Very rapid flowrate; Very high loading capacity; Autoclavable to 500 deg. C; For filtering finely precipitated proteins; Diameter: 2.1cm  
**09-874-62** - Pack of 100 for \$81.33  
Circle; Diameter: 2.4cm  
**09-874-64** - Pack of 100 for \$86.07  
Circle; Diameter: 2.5cm  
**09-874-70** - Pack of 100 for \$99.94  
Circle; Diameter: 3.7cm  
**09-874-66** - Pack of 100 for \$108.81  
Circle; Diameter: 4.25cm  
**09-874-71** - Pack of 100 for \$117.34  
Circle; Diameter: 4.7cm  
**09-874-68** - Pack of 100 for \$137.67  
Circle; Diameter: 5.5cm  
**09-874-72** - Pack of 100 for \$160.18  
Circle; Diameter: 7.0cm  
**09-874-73** - Pack of 25 for \$56.13  
Circle; Diameter: 9cm  
**09-874-74** - Pack of 25 for \$83.19  
Circle; Diameter: 11.0cm  
**09-874-75** - Pack of 25 for \$98.74  
Circle; Diameter: 12.5cm  
**09-874-80** - Pack of 25 for \$131.12  
Circle; Diameter: 14.2cm  
**09-874-76** - Pack of 76 for \$152.42  
Circle; Diameter: 15.0cm  
**09-874-78** - Pack of 25 for \$583.64  
Circle; Diameter: 29.3cm

### Whatman Prepleated Qualitative Circles



- 09-832K** - Pack of 100 for \$56.83  
Filter Papers; Whatman; 113V Grade; Qualitative; Prepleated circles; Increase total loading capacity; Particle retention: >30µm; Surface: Creped; Porosity: Coarse; Filtration speed: ASTM, 8 seconds - Herzberg, 28 seconds; 12.5cm dia.  
**09-832L** - Pack of 100 for \$65.33  
113V Grade; Diameter: 15cm  
**09-832P** - Pack of 100 for \$149.41  
113V Grade; Diameter: 27cm  
**09-834A** - Pack of 100 for \$54.08  
114V Grade; Diameter: 12.5cm  
**09-834B** - Pack of 100 for \$59.49  
114V Grade; Diameter: 15cm  
**09-834C** - Pack of 100 for \$70.94  
114V Grade; Diameter: 18.5cm  
**09-834D** - Pack of 100 for \$90.99  
114V Grade; Diameter: 24cm  
**09-834F** - Pack of 100 for \$149.82  
114V Grade; Diameter: 32cm  
**09-832A** - Pack of 100 for \$48.56  
2V Grade; Diameter: 12.5cm  
**09-832B** - Pack of 100 for \$53.75  
2V Grade; Diameter: 15cm  
**09-832C** - Pack of 100 for \$60.05  
2V Grade; Diameter: 18.5cm  
**09-832D** - Pack of 100 for \$82.08  
2V Grade; Diameter: 24cm  
**09-832E** - Pack of 100 for \$129.37  
2V Grade; Diameter: 32cm  
**09-832F** - Pack of 100 for \$192.36  
2V Grade; Diameter: 38.5cm  
**09-832H** - Pack of 100 for \$215.21  
2V Grade; Diameter: 40cm  
**09-832G** - Pack of 100 for \$251.48  
2V Grade; Diameter: 50cm

### Whatman Qualitative Grade Circles and Sheets - Grade 1



- 09-805-1A** - Pack of 500 for \$29.55  
Paper, Filter, Qualitative Grade, Whatman 1 Grade, >11micrometer Particle Retention, Medium Porosity, Astm (40 Sec.)/herzberg (150 Sec.) Filtration Speed, Smooth Surface, 1cm Dia.  
**09-805-1B** - Pack of 500 for \$29.55  
Grade 1; Diameter: 1.5cm  
**09-805-1G** - Pack of 100 for \$6.11  
Grade 1; Diameter: 2.5cm  
**09-805** - Pack of 100 for \$6.55  
Grade 1; Diameter: 3.2cm  
**09-805P** - Pack of 100 for \$6.42  
Grade 1; Diameter: 3cm  
**09-805A** - Pack of 100 for \$6.46  
Grade 1; Diameter: 4.25cm  
**09-805B** - Pack of 100 for \$6.89  
Grade 1; Diameter: 5.5cm  
**09-805C** - Pack of 100 for \$7.01  
Grade 1; Diameter: 7cm  
**09-805H** - Pack of 100 for \$23.81  
Grade 1; Diameter: 8.5cm  
**09-805D** - Pack of 100 for \$8.79  
Grade 1; Diameter: 9cm  
**09-805E** - Pack of 100 for \$10.66  
Grade 1; Diameter: 11cm  
**09-805F** - Pack of 100 for \$11.41  
Grade 1; Diameter: 12.5cm  
**09-805G** - Pack of 100 for \$16.61  
Grade 1; Diameter: 15cm  
**09-805J** - Pack of 100 for \$38.09  
Grade 1; Diameter: 24cm  
**09-805K** - Pack of 100 for \$47.27  
Grade 1; Diameter: 27cm  
**09-805L** - Pack of 100 for \$64.51  
Grade 1; Diameter: 32cm  
**09-805-1C** - Pack of 100 for \$106.98  
Grade 1; Diameter: 38.5cm  
**09-805-1E** - Pack of 100 for \$155.45  
Grade 1; Diameter: 50cm  
**09-805-1D** - Pack of 100 for \$106.98  
Grade 2; Diameter: 40cm  
**09-805-1F** - Pack of 500 for \$644.83  
Grade 1; Dimensions: 46 x 57 cm  
**09-806A** - Pack of 100 for \$146.50  
Grade 1; Dimensions: 46 x 57cm

### Whatman Qualitative Grade Circles and Sheets - Grade 2



- 09-810A** - Pack of 100 for \$8.46  
Filter Papers; Whatman; Grade 2; Qualitative; Circles and sheets; Particle retention: >8µm; Surface: Smooth; Porosity: Medium fine; Filtration speed: ASTM, 55 seconds; Herzberg, 240 seconds; 4.25cm dia.  
**09-810B** - Pack of 100 for \$8.74  
Grade 2; Diameter: 5.5cm  
**09-810C** - Pack of 100 for \$9.75  
Grade 2; Diameter: 7cm  
**09-810D** - Pack of 100 for \$12.00  
Grade 2; Diameter: 9.0cm  
**09-810E** - Pack of 100 for \$11.85  
Grade 2; Diameter: 11.0cm  
**09-810F** - Pack of 100 for \$14.98  
Grade 2; Diameter: 12.5cm  
**09-810G** - Pack of 100 for \$21.20  
Grade 2; Diameter: 15.0cm  
**09-810H** - Pack of 100 for \$29.09  
Grade 2; Diameter: 18.5cm  
**09-810J** - Pack of 100 for \$47.92  
Grade 2; Diameter: 24cm  
**09-810K** - Pack of 100 for \$63.31  
Grade 2; Diameter: 27cm  
**09-810L** - Pack of 100 for \$97.56  
Grade 2; Diameter: 32cm  
**09-810M** - Pack of 100 for \$129.11  
Grade 2; Diameter: 385mm  
**09-810P** - Pack of 100 for \$238.53  
Grade 2; Diameter: 50cm  
**09-810Q** - Pack of 100 for \$220.56  
Grade 2; Dimensions: 46 x 57cm  
**09-815A** - Pack of 100 for \$273.45  
Grade 2; Dimensions: 58 x 68cm

## Whatman Qualitative Grade Circles and Sheets - Grade 3



- 09-820AA** - Pack of 100 for \$8.74  
Filter Paper; Whatman Qualitative Grade Circle; Grade 3; Porosity: Medium Fine; Particle Retention: >6um; Surface: Smooth; Filtration speed: ASTM, 90 sec. Herzberg, 325 sec.; Dia.: 2.3cm
- 09-820H** - Pack of 100 for \$10.36  
Grade 3; Diameter: 5.5cm
- 09-820J** - Pack of 100 for \$12.49  
Grade 3; Diameter: 7cm
- 09-820A** - Pack of 100 for \$15.54  
Grade 3; Diameter: 9cm
- 09-820B** - Pack of 100 for \$19.24  
Grade 3; Diameter: 11cm
- 09-820C** - Pack of 100 for \$23.24  
Grade 3; Diameter: 12.5cm
- 09-820D** - Pack of 100 for \$34.32  
Grade 3; Diameter: 15cm
- 09-820E** - Pack of 100 for \$45.06  
Grade 3; Diameter: 18.5cm
- 09-820F** - Pack of 100 for \$77.18  
Grade 3; Diameter: 24cm
- 09-820P** - Pack of 100 for \$353.22  
Grade 3; Dimensions: 46 x 57cm

## Whatman Qualitative Grade Circles and Sheets - Grades 4, 5, and 6



- 09-825J** - Pack of 100 for \$6.69  
Filter Paper; Whatman Qualitative Grade Circle; Grade 4; Porosity: Coarse; Particle Retention: >20-25um; Surface: Smooth; Filtration speed: ASTM, 12 sec. Herzberg, 37 sec.; Dia.: 4.25cm
- 09-825K** - Pack of 100 for \$7.96  
Grade 4; Diameter: 5.5cm
- 09-825A** - Pack of 100 for \$8.30  
Grade 4; Diameter: 7cm Dia
- 09-825B** - Pack of 100 for \$10.28  
Grade 4; Diameter: 9cm
- 09-825C** - Pack of 100 for \$12.89  
Grade 4; Diameter: 11cm
- 09-825D** - Pack of 100 for \$17.08  
Grade 4; Diameter: 12.5cm
- 09-825E** - Pack of 100 for \$21.59  
Grade 4; Diameter: 15cm
- 09-825F** - Pack of 100 for \$32.61  
Grade 4; Diameter: 18.5cm
- 09-825G** - Pack of 100 for \$56.52  
Grade 4; Diameter: 24cm
- 09-825L** - Pack of 100 for \$73.31  
Grade 4; Diameter: 27cm
- 09-825H** - Pack of 100 for \$106.12  
Grade 4; Diameter: 32cm
- 09-825M** - Pack of 100 for \$157.16  
Grade 4; Diameter: 40cm
- 09-825P** - Pack of 100 for \$203.90  
Grade 4; Diameter: 46 x 57cm
- 09-830G** - Pack of 100 for \$6.97  
Grade 5; Diameter: 4.25cm
- 09-830H** - Pack of 100 for \$8.30  
Grade 5; Diameter: 5.5cm
- 09-830K** - Pack of 100 for \$9.85  
Grade 5; Diameter: 7 cm
- 09-830A** - Pack of 100 for \$13.56  
Grade 5; Diameter: 9cm
- 09-830B** - Pack of 100 for \$17.51  
Grade 5; Diameter: 11cm
- 09-830C** - Pack of 100 for \$21.59  
Grade 5; Diameter: 12.5cm
- 09-830D** - Pack of 100 for \$32.28  
Grade 5; Diameter: 15cm
- 09-830E** - Pack of 100 for \$47.16  
Grade 5; Diameter: 18.5cm
- 09-830F** - Pack of 100 for \$78.25  
Grade 5; Diameter: 24cm
- 09-830M** - Pack of 100 for \$136.15  
Grade 5; Diameter: 32 cm
- 09-831A** - Pack of 100 for \$7.08  
Grade 6; Diameter: 4.25cm
- 09-831D** - Pack of 100 for \$12.34  
Grade 6; Diameter: 9cm

- 09-831E** - Pack of 100 for \$16.79  
Grade 6; Diameter: 11cm
- 09-831F** - Pack of 100 for \$19.94  
Grade 6; Diameter: 12.5cm
- 09-831G** - Pack of 100 for \$30.95  
Grade 6; Diameter: 15cm
- 09-831J** - Pack of 100 for \$76.62  
Grade 6; Diameter: 24cm

## Whatman Qualitative Grade Paper for IS Measurement



- 09-940-100** - Pack of 100 for \$24.05  
Filter Paper; Qualitative Grade; Whatman; Grade 2 Paper for IS Measurement; Specifically developed for measuring the Ignition Strength (IS) of Cigarettes; Each lot is guaranteed to meet the ASTM E2187-04 specifications

## Whatman Quantitative Grade Papers Ashless Circles and Sheets



- 09-845J** - Pack of 100 for \$15.59  
Filter Papers; Whatman; Quantitative; Grade 40 Papers; Contd.; Particle retention: >8um; Surface: Smooth; Porosity: Medium; Filtration speed: ASTM, 75 seconds; Herzberg, 340 seconds; 3cm dia.
- 09-845H** - Pack of 100 for \$18.89  
Grade 40; Diameter: 4.25cm
- 09-845A** - Pack of 100 for \$21.09  
Grade 40; Diameter: 5.5cm
- 09-845B** - Pack of 100 for \$21.97  
Grade 40; Diameter: 7cm
- 09-845C** - Pack of 100 for \$30.42  
Grade 40; Diameter: 9cm
- 09-845D** - Pack of 100 for \$36.14  
Grade 40; Diameter: 11.0cm
- 09-845E** - Pack of 100 for \$41.73  
Grade 40; Diameter: 12.5cm
- 09-845F** - Pack of 100 for \$54.91  
Grade 40; Diameter: 15 cm
- 09-845G** - Pack of 100 for \$81.67  
Grade 40; Diameter: 18.5cm
- 09-845K** - Pack of 100 for \$129.08  
Grade 40; Diameter: 24cm
- 09-845M** - Pack of 100 for \$258.25  
Grade 40; Diameter: 32cm
- 09-845P** - Pack of 100 for \$539.07  
Grade 40; Diameter: 46 x 57cm
- 09-850G** - Pack of 100 for \$15.49  
Grade 41; Diameter: 4.25cm
- 09-850H** - Pack of 100 for \$17.02  
Grade 41; Diameter: 4.7cm
- 09-850J** - Pack of 100 for \$17.02  
Grade 41; Diameter: 5.5cm
- 09-850A** - Pack of 100 for \$21.53  
Grade 41; Diameter: 7cm
- 09-850B** - Pack of 100 for \$28.33  
Grade 41; Diameter: 9cm
- 09-850C** - Pack of 100 for \$34.38  
Grade 41; Diameter: 11cm
- 09-850D** - Pack of 100 for \$40.52  
Grade 41; Diameter: 12.5cm
- 09-850E** - Pack of 100 for \$55.12  
Grade 41; Diameter: 15cm
- 09-850L** - Pack of 100 for \$81.67  
Grade 41; Diameter: 18.5cm
- 09-850M** - Pack of 100 for \$129.08  
Grade 41; Diameter: 24cm
- 09-850P** - Pack of 100 for \$257.96  
Grade 41; Diameter: 32cm
- 09-850Q** - Pack of 100 for \$156.23  
Grade 41; Diameter: 8 x 10 in.
- 09-856A** - Pack of 100 for \$16.48  
Grade 42; Diameter: 4.25cm
- 09-855A** - Pack of 100 for \$23.07  
Grade 42; Diameter: 7cm
- 09-855B** - Pack of 100 for \$30.86  
Grade 42; Diameter: 9cm
- 09-855C** - Pack of 100 for \$37.56  
Grade 42; Diameter: 11.0cm
- 09-855D** - Pack of 100 for \$43.28  
Grade 42; Diameter: 12.5 cm

**09-855E** - Pack of 100 for \$54.91  
Grade 42; Diameter: 15.0cm  
**09-855F** - Pack of 100 for \$81.67  
Grade 42; Diameter: 18.5cm  
**09-856B** - Pack of 100 for \$131.28  
Grade 42; Diameter: 24cm  
**09-856D** - Pack of 100 for \$264.70  
Grade 42; Diameter: 32cm  
**09-855AA** - Pack of 100 for \$19.01  
Grade 42; Diameter: 42.5cm  
**09-856J** - Pack of 100 for \$30.86  
Grade 43; Diameter: 9cm  
**09-856K** - Pack of 100 for \$37.56  
Grade 43; Diameter: 11cm  
**09-856L** - Pack of 100 for \$43.28  
Grade 43; Diameter: 12.5cm  
**09-856M** - Pack of 100 for \$54.91  
Grade 43; Diameter: 15cm  
**09-856N** - Pack of 100 for \$81.67  
Grade 43; Diameter: 18.5cm  
**09-860A** - Pack of 100 for \$22.41  
Grade 44; Diameter: 7cm  
**09-860B** - Pack of 100 for \$30.86  
Grade 44; Diameter: 9cm  
**09-860C** - Pack of 100 for \$37.56  
Grade 44; Diameter: 11cm  
**09-860D** - Pack of 100 for \$43.28  
Grade 44; Diameter: 12.5cm  
**09-860E** - Pack of 100 for \$54.91  
Grade 44; Diameter: 15cm  
**09-860G** - Pack of 100 for \$82.69  
Grade 44; Diameter: 18.5cm  
**09-860H** - Pack of 100 for \$130.61  
Grade 44; Diameter: 24cm

### Whatman Quantitative Grade Papers Hardened Ashless Circles



**09-869B** - Pack of 100 for \$16.57  
Filter Papers; Whatman; Quantitative; Grade 540 Papers;  
Particle retention: >8um; Surface: Smooth, hard; Porosity:  
Medium; Filtration speed: ASTM, 55 seconds; Herzberg,  
200 seconds; 2.1cm dia.  
**09-869C** - Pack of 100 for \$16.57  
Grade 540; Diameter: 2.4 cm  
**09-869L** - Pack of 100 for \$143.55  
Grade 540; Diameter: 24cm  
**09-869A** - Pack of 100 for \$16.86  
Grade 540; Diameter: 4.25cm  
**09-869D** - Pack of 100 for \$18.96  
Grade 540; Diameter: 5.5cm  
**09-869E** - Pack of 100 for \$23.17  
Grade 540; Diameter: 7cm  
**09-869F** - Pack of 100 for \$31.00  
Grade 540; Diameter: 9cm  
**09-869G** - Pack of 100 for \$37.75  
Grade 540; Diameter: 11cm  
**09-869H** - Pack of 100 for \$43.48  
Grade 540; Diameter: 12.5cm  
**09-869J** - Pack of 100 for \$60.92  
Grade 540; Diameter: 15cm  
**09-851G** - Pack of 100 for \$16.57  
Grade 541; Diameter: 4.25cm  
**09-851H** - Pack of 100 for \$18.31  
Grade 541; Diameter: 4.7cm  
**09-851J** - Pack of 100 for \$19.09  
Grade 541; Diameter: 5.5cm  
**09-851A** - Pack of 100 for \$23.17  
Grade 541; Diameter: 7cm  
**09-851B** - Pack of 100 for \$31.00  
Grade 541; Diameter: 9cm  
**09-851C** - Pack of 100 for \$35.75  
Grade 541; Diameter: 11cm  
**09-851D** - Pack of 100 for \$42.71  
Grade 541; Diameter: 12.5cm  
**09-851E** - Pack of 100 for \$61.02  
Grade 541; Diameter: 15cm  
**09-851K** - Pack of 100 for \$91.00  
Grade 541; Diameter: 18.5cm  
**09-851L** - Pack of 100 for \$143.76  
Grade 541; Diameter: 24cm  
**09-851N** - Pack of 100 for \$294.20  
Grade 541; Diameter: 32cm

**09-851P** - Pack of 100 for \$394.52  
Grade 541; Diameter: 40cm  
**09-852D** - Pack of 100 for \$19.09  
Grade 542; Diameter: 5.5cm  
**09-852E** - Pack of 100 for \$23.17  
Grade 542; Diameter: 7cm  
**09-852F** - Pack of 100 for \$31.00  
Grade 542; Diameter: 9cm  
**09-852G** - Pack of 100 for \$37.75  
Grade 542; Diameter: 11cm  
**09-852H** - Pack of 100 for \$43.48  
Grade 542; Diameter: 12.5cm  
**09-852J** - Pack of 100 for \$60.92  
Grade 542; Diameter: 15cm  
**09-852K** - Pack of 100 for \$91.00  
Grade 542; Diameter: 18.5cm

### Whatman Quantitative Grade Papers Hardened Low Ash Circles and Sheets



**09-865J** - Pack of 100 for \$16.48  
Filter Papers; Whatman; Grade 50 Papers; Quantitative;  
Particle retention: >2.7um; Surface: Smooth, hard;  
Porosity: Fine; Filtration speed: ASTM, 250 seconds;  
Herzberg, 2685 seconds; 4.25cm dia.  
**09-865A** - Pack of 100 for \$19.01  
Grade 50; Diameter: 5.5cm  
**09-865B** - Pack of 100 for \$21.53  
Grade 50; Diameter: 7cm  
**09-865C** - Pack of 100 for \$28.44  
Grade 50; Diameter: 9cm  
**09-865D** - Pack of 100 for \$37.56  
Grade 50; Diameter: 11cm  
**09-865E** - Pack of 100 for \$43.28  
Grade 50; Diameter: 12.5cm  
**09-865F** - Pack of 100 for \$50.85  
Grade 50; Diameter: 15cm  
**09-865G** - Pack of 100 for \$63.91  
Grade 50; Diameter: 18.5cm  
**09-865H** - Pack of 100 for \$113.91  
Grade 50; Diameter: 24cm  
**09-865L** - Pack of 100 for \$206.88  
Grade 50; Diameter: 32cm  
**09-865M** - Pack of 100 for \$371.84  
Grade 50; Diameter: 40cm  
**09-866D** - Pack of 100 for \$30.86  
Grade 52; Diameter: 9cm  
**09-866E** - Pack of 100 for \$37.56  
Grade 52; Diameter: 11cm  
**09-866F** - Pack of 100 for \$43.28  
Grade 52; Diameter: 12.5cm  
**09-866G** - Pack of 100 for \$50.85  
Grade 52; Diameter: 15cm  
**09-866J** - Pack of 100 for \$115.71  
Grade 52; Diameter: 24cm  
**09-868F** - Pack of 100 for \$19.01  
Grade 54; Diameter: 5.5cm  
**09-868N** - Pack of 100 for \$439.93  
Grade 54; Diameter: 50cm  
**09-868G** - Pack of 100 for \$21.53  
Grade 54; Diameter: 7cm  
**09-868A** - Pack of 100 for \$30.86  
Grade 54; Diameter: 9cm  
**09-868B** - Pack of 100 for \$37.56  
Grade 54; Diameter: 11cm  
**09-868C** - Pack of 100 for \$43.28  
Grade 54; Diameter: 12.5cm  
**09-868D** - Pack of 100 for \$50.85  
Grade 54; Diameter: 15cm  
**09-868H** - Pack of 100 for \$64.02  
Grade 54; Diameter: 18.5cm  
**09-868J** - Pack of 100 for \$113.91  
Grade 54; Diameter: 24cm  
**09-868L** - Pack of 100 for \$204.43  
Grade 54; Diameter: 32cm  
**09-868P** - Pack of 100 for \$550.34  
Grade 54; Diameter: 46 x 57cm

### Whatman Reeve Angel 230 Creped Qualitative Circles



**09-803A** - Pack of 50 for \$5.41  
Filter Papers; Whatman; Qualitative; Reeve Angel 230; Creped circles; Strong and thick; Ideal for use in oil chemistry; Reliable; Particle retention: 30um; 0.41mm thick; 9cm dia.  
**09-803D** - Pack of 50 for \$11.02  
15cm

### Whatman Reeve Angel 802 Prepleated Qualitative Circles



**09-901A** - Pack of 100 for \$24.34  
Filter Paper; Whatman; Reeve Angel 802 Prepleated Qualitative Circles; Diameter: 12.5cm  
**09-901B** - Pack of 100 for \$62.58  
15cm  
**09-901C** - Pack of 100 for \$29.56  
18.5cm  
**09-901D** - Pack of 100 for \$67.37  
24cm  
**09-901E** - Pack of 100 for \$79.80  
32cm  
**09-805-18F** - Pack of 100 for \$103.51  
38.5cm

### Whatman SG Student Grade (Grade 93) Qualitative Circles

**09-805-10A** - Pack of 1250 for \$92.89  
Filter Papers; Whatman; Grade 93; Qualitative circles; SG student; Contains 50 envelopes of 25 circles each in handy dispenser box; Flowrate and retention fall between those for Grade 1 and 4; 11cm dia.  
**09-805-10B** - Pack of 1250 for \$101.61  
Diameter: 12.5cm

### Whatman Shark Skin Filter Paper



**09-924-390** - Pack of 100 for \$37.59  
Filter Paper; Whatman; Shark Skin; General use; white, creped surface; for qualitative work; ideal for industrial work; Diameter: 12.5cm  
**09-924-392** - Pack of 100 for \$30.67  
Diameter: 15cm

### Whatman Wet-Strengthened Qualitative Circles



**09-853A** - Pack of 100 for \$14.87  
Filter Papers; Whatman; Grade 113; Particle retention: >25um; Surface: Smooth; Porosity: Coarse; Filtration speed: ASTM, 12 seconds; Herzberg, 38 seconds; 9cm dia.  
**09-853B** - Pack of 100 for \$17.23  
113 Grade; Diameter: 11cm  
**09-853C** - Pack of 100 for \$21.81  
113 Grade; Diameter: 12.5cm  
**09-833G** - Pack of 100 for \$23.92  
113 Grade; Diameter: 15cm  
**09-833H** - Pack of 100 for \$35.94  
113 Grade; Diameter: 18.5cm  
**09-853F** - Pack of 100 for \$72.15  
113 Grade; Diameter: 24cm  
**09-833D** - Pack of 100 for \$10.81  
114 Grade; Diameter: 9cm  
**09-833F** - Pack of 100 for \$19.13  
114 Grade; Diameter: 12.5 cm  
**09-853D** - Pack of 100 for \$30.76  
114 Grade; Diameter: 15cm  
**09-853E** - Pack of 100 for \$47.06  
114 Grade; Diameter: 18.5cm  
**09-833J** - Pack of 100 for \$58.84  
114 Grade; Diameter: 24cm  
**09-853H** - Pack of 100 for \$130.43  
114 Grade; Diameter: 32cm  
**09-833M** - Pack of 100 for \$176.54  
114 Grade; Diameter: 40 cm  
**09-853K** - Pack of 100 for \$306.24  
114 Grade; Diameter: 50cm

## Fluoride and Glycol

### Orbeco Model 942: Test Kits for 975MP Analyst and 942 Mini Analysts - With Reagent Tablets - For Fluoride and Glycol Testing

**15-398-454** - Each for \$35.53  
Reagent, Test Kit; For use with 975MP and 942 Mini Analysts; 50 tests; Test: Fluoride; Range: 0-3mg/L

### Orbeco-Hellige SC400 Series Colorimeters - For Fluoride and Glycol Testing



**09-053-280** - Each for \$320.00  
Colorimeter; Orbeco-Hellige SC400; Fluoride; Range, 0.1-2.0mg/L

### Thermo Scientific Orion AQUAfast II Colorimeters Single Parameter Kits - For Fluoride and Glycol Testing



**13-642-024** - Each for \$463.58  
Colorimeter; AQUAfast II; Thermo Scientific Orion; Single parameter; Ideal for fast, accurate water quality testing in the laboratory and the field; Analyte: Fluoride; Range: 0.1 to 2.0mg/L

## General Labware

### Fisherbrand Amber Wide-Mouth HDPE Bottles



**03-007-51** - Pack of 12 for \$19.55 and Case of 6 Packs for \$78.23  
Bottle; Wide-Mouth; Fisherbrand; HDPE; Polyethylene; Amber; Reduces UV light transmission to protect light-sensitive liquids; 60mL  
**03-007-52** - Pack of 12 for \$21.48 and Case of 6 Packs for \$85.92  
125mL  
**03-007-53** - Pack of 12 for \$32.74 and Case of 6 Packs for \$130.96  
250mL  
**03-007-54** - Pack of 12 for \$44.55 and Case of 4 Packs for \$118.80  
500mL  
**03-007-55** - Pack of 6 for \$51.01 and Case of 4 Packs for \$136.02  
1L

### Fisherbrand Bulk-Packaged HDPE Field-Sample Bottles



**02-895-1A** - Case of 500 for \$419.53  
Bottles; HDPE; Field-Sample; Fisherbrand; Bulk-Packaged; Screw Cap Size: 38mm; Case of: 500; Capacity: 4 oz. (125mL)  
**02-895-1B** - Case of 250 for \$295.70  
8 oz.  
**02-895-1C** - Case of 125 for \$229.73  
16 oz.  
**02-895-1D** - Case of 50 for \$140.18  
32 oz.



### Fisherbrand HDPE Round Bottles



- 02-896-2A** - Pack of 12 for \$24.08 and Case of 6 Packs for \$96.31  
Bottle, Round; Fisherbrand; HDPE; Leakproof; May be radiation, EtO, or chemically sterilized; Not autoclavable; With polypropylene screw cap; Capacity: 1 oz. (30mL); Screw cap size: 28mm; Translucent
- 02-896-2B** - Pack of 12 for \$24.39 and Case of 6 Packs for \$97.56  
2 oz.
- 02-896-2C** - Pack of 12 for \$29.35 and Case of 6 Packs for \$117.40  
4 oz.
- 02-896-2D** - Pack of 12 for \$44.15 and Case of 6 Packs for \$176.60  
8 oz.
- 02-896-2E** - Pack of 12 for \$61.39 and Case of 4 Packs for \$163.73  
16 oz.
- 02-896-2F** - Pack of 6 for \$55.87 and Case of 4 Packs for \$148.98  
32 oz.

### Fisherbrand HDPE Wide-Mouth Round Bottles with Foamed PE-lined Closures



- 02-912-037** - Case of 48 for \$86.81  
Bottle, Wide-Mouth; Fisherbrand; HDPE; Round; With foamed PE-lined closures; Translucent; 1 oz.; Case of 48
- 02-912-104** - Case of 1650 for \$650.77  
1 oz.; Case of 1650
- 02-912-031** - Case of 48 for \$36.59  
2 oz.; Case of 48
- 02-912-019** - Case of 950 for \$580.14  
2 oz.; Case of 950
- 02-912-032** - Case of 48 for \$104.40  
4 oz.; Case of 48
- 02-912-021** - Case of 500 for \$364.57  
4 oz.; Case of 500
- 02-912-034** - Case of 48 for \$61.16  
8 oz.; Case of 48
- 02-912-022** - Case of 260 for \$262.09  
8 oz.; Case of 260
- 02-912-030** - Case of 24 for \$45.83  
16 oz.; Case of 24
- 02-912-018** - Case of 137 for \$172.64  
16 oz.; Case of 137
- 02-912-038** - Case of 12 for \$58.48  
32 oz.; Case of 12
- 02-912-020** - Case of 72 for \$125.45  
32 oz.; Case of 72
- 02-912-033** - Case of 6 for \$69.92  
64 oz.; Case of 6
- 02-911-990** - Case of 75 for \$268.16  
64 oz.; Case of 75
- 02-912-035** - Case of 4 for \$54.09  
96 oz.; Case of 4
- 02-912-103** - Case of 33 for \$129.04  
96 oz.; Case of 33
- 02-912-036** - Case of 4 for \$41.20  
130 oz.; Case of 4

### Fisherbrand HDPE Wide-Mouth Round Bottles without Closures



- 02-911-886** - Case of 500 for \$537.47  
Bottle, High-density Polyethylene; Fisherbrand; Wide-mouth; Round bottles; Without closures; Natural color; 4 oz.; 38mm-400 screw cap size
- 02-912-105** - Case of 260 for \$258.23  
8 oz.; 53mm-400 screw cap size
- 02-912-110** - Case of 137 for \$183.63  
16 oz.; 53mm-400 screw cap size
- 02-912-023** - Case of 72 for \$407.66  
32 oz.; 53mm-400 screw cap size
- 02-911-874** - Case of 4 for \$41.10  
130 oz.; 89mm-400 screw cap size

### Fisherbrand Intermediate Form Polypropylene Beakers with Handles



- 02-591-36** - Pack of 5 for \$23.73  
Beaker, Intermediate Form; Fisherbrand; Polypropylene; With handle; Capacity: 50mL
- 02-591-37** - Pack of 5 for \$24.59  
Capacity: 100mL
- 02-591-38** - Pack of 1 for \$7.36  
Capacity: 250mL
- 02-591-39** - Pack of 1 for \$8.00  
Capacity: 500mL
- 02-591-40** - Pack of 1 for \$9.34  
Capacity: 1000mL
- 02-591-41** - Pack of 1 for \$11.63  
Capacity: 2000mL
- 02-591-42** - Pack of 1 for \$13.63  
Capacity: 3000mL
- 02-591-43** - Pack of 1 for \$38.30  
Capacity: 5000mL

### Fisherbrand Leak-Resistant HDPE Wide-Mouth Bottles



- 02-911-974** - Case of 72 for \$82.85  
Bottle; Fisherbrand; HDPE; Narrow-Mouth; Leak-Resistant; Attached linerless screw caps; Translucent; 1 oz. (30mL); 28mm-410 screw cap size
- 02-911-975** - Case of 72 for \$85.74  
2 oz.
- 02-911-958** - Case of 72 for \$100.95  
4 oz.
- 02-911-961** - Case of 72 for \$152.40  
8 oz.
- 02-911-955** - Case of 48 for \$147.45  
16 oz.
- 02-911-976** - Case of 24 for \$116.40  
32 oz.

### Fisherbrand Low Form Polypropylene Beakers with Handles



- 02-543-36A** - Case of 24 for \$127.61  
Beaker, Low Form; Fisherbrand; Polypropylene; With handle; Capacity: 250mL
- 02-543-36B** - Case of 24 for \$163.31  
Capacity: 500mL
- 02-543-36C** - Case of 24 for \$150.79  
Capacity: 1000mL
- 02-543-36D** - Case of 12 for \$101.41  
Capacity: 2000mL
- 02-543-36E** - Case of 12 for \$131.02  
Capacity: 3000mL
- 02-543-36F** - Case of 12 for \$495.52  
Capacity: 5000mL

### Fisherbrand PET Wide-Mouth Packers



- 02-911-849** - Case of 48 for \$20.73  
PET wide-mouth packers, With attached foamed PE-lined closures, Clear, 2 oz. (60mL), 33mm-400 screw cap size
- 02-911-795** - Case of 48 for \$20.35  
4 oz.; With foamed PTFE-lined Caps
- 02-911-808** - Case of 48 for \$102.97  
8 oz.; With foamed PTFE-lined Caps
- 02-912-350** - Case of 576 for \$1070.68  
4 oz.; With PTFE-lined Caps

### Fisherbrand Polypropylene Disposable Beakers



- 01-291-8** - Pack of 100 for \$16.65 and Case of 10 Packs for \$142.27  
Beaker, Disposable; Fisherbrand; Polypropylene; Unbreakable; Dripless lip; Rib construction; Base; Graduated in mL and oz.; Capacity: 15mL; Graduations: 5mL/1/8 oz.
- 01-291-9** - Pack of 100 for \$20.26 and Case of 10 Packs for \$173.12  
Capacity: 30mL
- 01-291-10** - Pack of 100 for \$21.56 and Case of 10 Packs for \$184.27  
Capacity: 50mL
- 01-291-7** - Pack of 100 for \$30.51 and Case of 10 Packs for \$260.81  
Capacity: 100mL

- 01-291-11** - Pack of 100 for \$52.09 and Case of 10 Packs for \$445.24  
Capacity: 150mL
- 01-291-5** - Pack of 50 for \$31.76 and Case of 10 Packs for \$271.49  
Capacity: 250mL
- 01-291-12** - Pack of 50 for \$43.38 and Case of 10 Packs for \$370.77  
Capacity: 400mL
- 01-291-6** - Pack of 25 for \$25.04 and Case of 20 Packs for \$428.01  
Capacity: 600mL

### Fisherbrand Wide Mouth LDPE Bottles



- 02-896-1A** - Pack of 12 for \$23.12 and Case of 6 Packs for \$92.48  
Bottle; Fisherbrand; LDPE; Ungraduated; Wide-Mouth; Screw Cap Size: 28mm; Capacity: 1 oz.
- 02-896-1B** - Pack of 12 for \$24.03 and Case of 6 Packs for \$96.10  
2 oz.
- 02-896-1C** - Pack of 12 for \$29.24 and Case of 6 Packs for \$116.99  
4 oz.
- 02-896-1D** - Pack of 12 for \$43.44 and Case of 6 Packs for \$173.79  
8 oz.
- 02-896-1E** - Pack of 12 for \$61.93 and Case of 4 Packs for \$165.13  
16 oz.
- 02-896-1F** - Pack of 6 for \$54.30 and Case of 4 Packs for \$144.80  
32 oz.

### Fisherbrand Wide Mouth Polypropylene Bottles



- 02-896A** - Pack of 12 for \$25.81 and Case of 6 Packs for \$103.23  
Bottle, General-purpose; Fisherbrand; Wide-mouth; Polypropylene; With polypropylene linerless screw closures; Rigid walls; Chemical resistant; Capacity: 1 oz. (30mL); Screw cap size: 43mm
- 02-896B** - Pack of 12 for \$26.42 and Case of 6 Packs for \$105.68  
2 oz.
- 02-896C** - Pack of 12 for \$34.64 and Case of 6 Packs for \$138.55  
4 oz.
- 02-896D** - Pack of 12 for \$53.45 and Case of 6 Packs for \$213.78  
8 oz.
- 02-896E** - Pack of 12 for \$72.68 and Case of 4 Packs for \$193.83  
16 oz.
- 02-896F** - Pack of 6 for \$61.61 and Case of 4 Packs for \$164.28  
32 oz.


### Kimax Griffin Beakers



- 02-539-1** - Pack of 12 for \$50.00 and Case of 4 Packs for \$145.96  
Beaker, Griffin; Kimax, with pouring spout; Uniform, sturdy walls; Designed from ASTM E960 Type I requirements; Matte-finish enameled marking area; Graduated; Capacity: 20mL
- 02-539F** - Pack of 12 for \$49.61 and Case of 4 Packs for \$144.95  
Capacity: 30mL
- 02-539G** - Pack of 12 for \$49.61 and Case of 4 Packs for \$144.95  
Capacity: 50mL
- 02-539H** - Pack of 12 for \$52.36 and Case of 4 Packs for \$153.00  
Capacity: 100mL
- 02-539Q** - Pack of 4 for \$56.96 and Case of 4 Packs for \$166.42  
Capacity: 1500mL
- 02-539J** - Pack of 12 for \$50.13 and Case of 4 Packs for \$146.46  
Capacity: 150mL

- 02-539K** - Pack of 12 for \$50.13 and Case of 4 Packs for \$146.46  
Capacity: 250mL
- 02-539L** - Pack of 12 for \$58.91 and Case of 4 Packs for \$172.13  
Capacity: 400mL
- 02-539M** - Pack of 6 for \$37.55 and Case of 6 Packs for \$164.58  
Capacity: 600mL
- 02-539N** - Pack of 6 for \$51.68 and Case of 4 Packs for \$150.99  
Capacity: 800mL
- 02-539P** - Pack of 6 for \$70.54 and Case of 4 Packs for \$206.10  
Capacity: 1000mL
- 02-539R** - Pack of 4 for \$93.26 and Case of 2 Packs for \$136.23  
Capacity: 2000mL
- 02-539T** - Each for \$73.82 and Case of 6 for \$323.50  
Capacity: 4000mL

### Nalgene Amber Rectangular HDPE Bottles



- 02-924-10A** - Pack of 12 for \$44.01 and Case of 6 Packs for \$176.00  
Bottles; Nalgene; Rectangular; HDPE; Screw Cap Size: 28mm-415; Capacity: 4 oz.
- 02-924-10C** - Pack of 12 for \$58.93 and Case of 6 Packs for \$235.75  
8 oz.
- 02-924-10E** - Pack of 12 for \$84.10 and Case of 4 Packs for \$224.25  
16 oz.
- 02-924-10G** - Pack of 6 for \$96.19 and Case of 4 Packs for \$256.50  
32 oz.
- 02-924-10J** - Pack of 4 for \$98.88 and Case of 3 Packs for \$197.75  
64 oz.

### Nalgene HDPE Large Square Bottles



- 02-925-4** - Each for \$32.57 and Case of 6 for \$130.25  
Bottles; Square; Nalgene; Large; HDPE; Wide-mouth; Polypropylene screw cap size: 100mm-415; Capacity: 1-1/8 gal.

### Nalgene Large Square Polypropylene Bottles



- 03-313** - Each for \$36.63 and Case of 6 for \$146.50  
Bottle, Large; Nalgene; Wide-mouth Nalgene; Square; Polypropylene; Autoclavable; 4L; 279mm x 140 in.

### Nalgene Narrow-Mouth Square HDPE Bottles



**03-311-1N** - Pack of 12 for \$20.81 and Case of 6 Packs for \$83.25

Bottles, Square; Nalgene; HDPE; Translucent; With polypropylene screw closures; Leakproof; Not autoclavable; 2 oz. (60mL); Screw cap size: 24mm

**03-311-1P** - Pack of 12 for \$21.20 and Case of 6 Packs for \$84.75

2 oz.

**03-311-1Q** - Pack of 12 for \$24.82 and Case of 6 Packs for \$99.25

4 oz.

**03-311-1R** - Pack of 12 for \$37.82 and Case of 6 Packs for \$151.25

8 oz.

**03-311-1S** - Pack of 12 for \$51.94 and Case of 4 Packs for \$138.50

16 oz.

**03-311-1T** - Pack of 6 for \$48.01 and Case of 4 Packs for \$128.00

32 oz.

### Nalgene Rectangular HDPE Bottles



**02-924-5A** - Pack of 12 for \$28.01 and Case of 6 Packs for \$112.00

Bottles; Nalgene; Rectangular; HDPE; Screw Cap Size: 28mm-415; Capacity: 4 oz. (125mL)

**02-924-5C** - Pack of 12 for \$40.82 and Case of 6 Packs for \$163.25

Capacity: 8 oz. (250mL)

**02-924-5E** - Pack of 12 for \$63.38 and Case of 4 Packs for \$169.00

Capacity: 16 oz. (500mL)

**02-924-5G** - Pack of 6 for \$73.22 and Case of 4 Packs for \$195.25

Capacity: 32 oz. (1000mL)

**02-924-5J** - Pack of 4 for \$81.00 and Case of 3 Packs for \$162.00

Capacity: 64 oz. (2000mL)

### Pyrex Griffin Beakers



**02-540C** - Pack of 12 for \$58.06 and Case of 4 Packs for \$174.15

Beaker, Griffin; Pyrex; Low Form; Double Scale; Graduated; Capacity: 10mL

**02-540E** - Pack of 12 for \$51.63 and Case of 4 Packs for \$150.73

Capacity: 20mL

**02-540F** - Pack of 12 for \$48.49 and Case of 4 Packs for \$149.21

Capacity: 30mL

**02-540G** - Pack of 12 for \$48.49 and Case of 4 Packs for \$149.21

Capacity: 50mL

**02-540H** - Pack of 12 for \$52.71 and Case of 4 Packs for \$157.86

Capacity: 100mL

**02-540J** - Pack of 12 for \$53.14 and Case of 4 Packs for \$150.73

Capacity: 150mL

**02-540K** - Pack of 12 for \$52.31 and Case of 4 Packs for \$152.71

Capacity: 250mL

**02-540L** - Pack of 12 for \$60.84 and Case of 4 Packs for \$177.73

Capacity: 400mL

**02-540M** - Pack of 6 for \$39.33 and Case of 6 Packs for \$169.19

Capacity: 600mL

**02-540N** - Pack of 6 for \$51.54 and Case of 4 Packs for \$155.83

Capacity: 800mL

**02-540P** - Pack of 6 for \$72.83 and Case of 4 Packs for \$212.60

Capacity: 1000mL

**02-540Q** - Pack of 4 for \$56.87 and Case of 4 Packs for \$171.78

Capacity: 1500mL

**02-540R** - Pack of 4 for \$96.26 and Case of 2 Packs for \$140.54

Capacity: 2000mL

**02-540S** - Each for \$42.34 and Case of 6 for \$181.22

Capacity: 3000mL

**02-540T** - Each for \$78.02 and Case of 6 for \$334.06

Capacity: 4000mL

## Hardness and Hydrazine

### EM Science Quant Test Strips - For Hardness Testing



**M100831** - Pack of 60 for \$76.04

Test: Calcium Kit; Pack of: 60; Range: 10-25-50-100ppm

**M100081** - Pack of 100 for \$55.75

Test: Silver, Fixing Bath; Range: 0.5-10g/L

**M100251** - Pack of 100 for \$54.20

Test: Total hardness; Range: 40 to 230ppm

**M100461** - Pack of 100 for \$47.37

Test: Total Hardness; Range: 75 to 500ppm

### LaMotte Series 1200 Colorimeter Single-Test Kits - For Hardness Testing



**22-307-861** - Each for \$48.50

Colorimeter; Series 1200; LaMotte; Single-parameter;

Water-resistant, handheld single-parameter meters;

Analyte: Hardness; Range (ppm): 1 drop = 10 or 1ppg;

Method: Calcium, Magnesium, Total Hardness Dropper Bottle

### Orbeco Model 942 Mini Analysts Ordering Information - With Reagent Tablets - For Hardness Testing

**15-405-112** - Each for \$302.10

Spectrophotometer; Model 942; Orbeco; With reagent tablets; 50 tests; Test:

Calcium Hardness; Range: 0-500mg/L

### Orbeco Model 942: Test Kits for 975MP Analyst and 942 Mini Analysts - With Reagent Tablets - For Hardness Testing

**15-410-G** - Each for \$24.13

Reagent, Test Kit; For use with 975MP and 942 Mini Analysts; 50 tests; Test:

Calcium Hardness; Range: 0-500mg/L

**15-399-C** - Each for \$28.27

Test: Hardness, total; Range: 0-500mg/L

## Hydrogen Peroxide

### CHEMetrics Chemets Self-Filling Ampules - For Hydrogen Peroxide Testing



**13-299-232A** - Each for \$57.84

Kit, Test; Chemets; CHEMetrics; Provide results in two

minutes or less; Analyte: Hydrogen Peroxide; Testing

Range: 0-1 and 1-10ppm; Analytical Method: Ammonium

Thiocyanate and Ferrous Iron; Complete Test Kit

**13-299-232B** - Each for \$24.13

Hydrogen Peroxide; Testing Range: 0-1 and 1-10ppm;

Analytical Method: Ammonium Thiocyanate and Ferrous

Iron; Refil Ampule

### EM Science Quant Test Strips - For Hydrogen Peroxide Testing



**M100111** - Pack of 100 for \$53.95

Strips, Test; EM; Quant; Test: Peroxide; Pack of: 100;

Range: 0.5-2-5-10-25ppm

**M100811** - Pack of 100 for \$54.19

Test: Peroxide; Range: 1-3-10-30-100ppm

# Iron and Lead

## CHEMetrics Chemets Self-Filling Ampules - For Iron Testing



**13-299-213A** - Pack of 30 for \$24.13  
 Kit, Test; Chemets; CHEMetrics; Provide results in two minutes or less; Analyte: Iron; Testing Range: 0-1.0 and 1-10ppm; Analytical Method: 1, 10 Phenanthroline; Refill Ampule

## EM Science Quant Test Strips - For Iron and Lead Testing



**M100041** - Pack of 100 for \$54.19  
 Testing Supplies; Water Quality; Strips; Test; EM Quant; Test: Ammonium Kit; Range: 10 to 400ppm; Ready-to-use; Detection chemicals, buffers, masking agents, stabilizers are incorporated; Supplied in sturdy aluminum cylinders

**M100771** - Pack of 100 for \$92.97  
 Test: Lead kit; Range: 20 to 500ppm

## Orbeco Model 942 Mini Analysts Ordering Information - With Reagent Tablets - For Iron and Lead Testing

**15-405-121** - Each for \$302.66  
 Spectrophotometer; Model 942; Orbeco; With reagent tablets; 50 tests; Test: Iron, high range; Range: 0-10mg/L

## Orbeco Model 942: Test Kits for 975MP Analyst and 942 Mini Analysts - With Reagent Tablets - For Iron and Lead Testing

**15-410-J** - Each for \$27.81  
 Reagent, Test Kit; For use with 975MP and 942 Mini Analysts; 50 tests; Test: Iron, low range; Range: 0-1.5mg/L

**15-398-456** - Each for \$17.65  
 Test: Iron, high range; Range: 0-10mg/L

## Orbeco-Hellige Powder Packs for Metals - For Iron and Lead Testing



**09-053-228** - Each for \$14.95  
 Reagent, Colorimeter; Powder Pack; Total Iron; Iron Ferro; 10mL; Pack of 100

**09-053-227** - Each for \$21.60  
 Iron TPTZ

## Orbeco-Hellige SC400 Series Colorimeters - For Iron and Lead Testing



**09-053-281** - Each for \$320.00  
 Colorimeter; Orbeco-Hellige SC400; Iron; Range, 0.02-5.00, 0.01-1.70mg/L

**09-053-296** - Each for \$320.00  
 Iron, TPTZ

# Lab Equipment and Instruments

## Fisher Scientific Isotemp Basic Magnetic Stirrers



**11-100-16S** - Each for \$266.00  
 Stirrer, Magnetic; Fisher Scientific Isotemp; Analog; Stir range 60-1200rpm; 4x4, Ceramic, 120V

**11-102-16S** - Each for \$294.00  
 4x4, Ceramic, 230V

**11-200-49S** - Each for \$295.01  
 7x7, Aluminum, 120V

**1120249S** - Each for \$356.00  
 7x7, Aluminum, 230V

**11-100-49S** - Each for \$257.01  
 7x7, Ceramic, 120V

**11-102-49S** - Each for \$294.00  
 7x7, Ceramic, 230V

**11-100-100S** - Each for \$393.00  
 10x10, Ceramic, 120V

**11-102-100S** - Each for \$424.00  
 10x10, Ceramic, 230V

## Fisher Scientific Isotemp Chromatography Refrigerators



**13-986-138G** - Each for \$6417.00  
 Refrigerator, Fisher Scientific Isotemp Chromatography; Model: Basic; Capacity: 38 cu. ft.; 2 glass sliding doors; 6 full and 3 half shelves; 1 deg. to 12 deg. C; 115V 60Hz

**13-986-127G** - Each for \$6400.00  
 Model: Basic; 27 cu. ft.

**13-986-145G** - Each for \$7485.23  
 Model: Basic; 45.4 cu. ft.

**13-986-149G** - Each for \$8115.00  
 Model: Basic; 49 cu. ft.

**13-986-172G** - Each for \$10207.00  
 Model: Basic; 72 cu. ft.

**13-986-127GA** - Each for \$7904.00  
 Recorder/Alarm Model, 27 cu. ft.

**13-986-138GA** - Each for \$7631.00  
 Recorder/Alarm Model, 38 cu. ft.

**13-986-145GA** - Each for \$9427.00  
 Recorder/Alarm Model, 45 cu. ft.

**13-986-149GA** - Each for \$10127.00  
 Recorder/Alarm Model, 49 cu. ft.

**13-986-172GA** - Each for \$12184.00  
 Recorder/Alarm Model, 72 cu. ft.

## Fisher Scientific Isotemp Digital Magnetic Stirrers



**11-300-49S** - Each for \$666.99  
 Stirrer, Isotemp; Fisher Scientific; Digital; Speed control from 60-1200rpm; Ceramic top; 7.25 x 7.25 in. top plate; 120V 50/60Hz; Load capacity: 25 lb. (11kg); Includes: Detachable 3-wire line cord and plug, PTFE stir bar

**11-302-49S** - Each for \$743.40  
 230V

## Fisher Scientific Isotemp Economy Lab Incubators



**11-690-525D** - Each for \$1281.00  
 Incubators, Standard; Fisher Scientific Isotemp; Gravity flow convection; Model: Small; Total chamber capacity: 2.5 cu. ft; 1 shelf; Temp range: 30-75 deg. C; Air changes/hour: 6; 120V 60Hz, 260w, 2.2A

**11-690-537D** - Each for \$1600.00  
 Model: Medium

**11-690-550D** - Each for \$1713.00  
 Model: Large

## Fisher Scientific Isotemp Lab Refrigerators



- 13-986-227RA** - Each for \$6532.00  
Refrigerator, General-purpose with Recorder/Alarm, Fisher Scientific Isotemp, 27 cu. ft., 1 deg. to 12 deg. C, 1 hinged solid lockable door, 1/3 hp, 115V 60Hz
- 13-986-238GA** - Each for \$7291.00  
General-purpose with Recorder/Alarm; 33 cu. ft.
- 13-986-249RA** - Each for \$8562.00  
General-purpose with Recorder/Alarm; 49 cu. ft.
- 13-986-227G** - Each for \$4902.39  
Model: Basic; Capacity: 27 cu. ft.; 1 hinged glass door
- 13-986-227R** - Each for \$4953.00  
Model: Basic; Capacity: 27 cu.; 1 hinged solid door
- 13-986-238G** - Each for \$5723.00  
Model: Basic; Capacity: 38 cu. ft.; 2 hinged glass doors
- 13-986-245G** - Each for \$7064.15  
Model: Basic; Capacity: 45 cu. ft.; 2 hinged glass doors
- 13-986-249G** - Each for \$6818.00  
Model: Basic; Capacity: 49 cu. ft.; 2 hinged glass doors
- 13-986-249R** - Each for \$6690.00  
Model: Basic; Capacity: 49 cu. ft.; 2 hinged solid lockable doors
- 13-986-272G** - Each for \$8872.13  
Model: Basic; Capacity: 72 cu. ft.; 3 hinged glass doors
- 13-986-227GA** - Each for \$6425.00  
Model: Recorder/Alarm; Capacity: 27 cu. ft..
- 13-986-272GA** - Each for \$10801.73  
Model: Recorder/Alarm; Capacity: 27 cu. ft.; 1 hinged glass door
- 13-986-245GA** - Each for \$8646.00  
Model: Recorder/Alarm; Capacity: 45 cu. ft.
- 13-986-249GA** - Each for \$8744.00  
Model: Recorder/Alarm; Capacity: 49 cu. ft.

## Fisher Scientific Isotemp Plus Chromatography Refrigerators



- 13-986-134A** - Each for \$7458.00  
Refrigerator, Fisher Scientific Isotemp Plus Chromatography, Alarm Model, 23.1 cu. ft., 1 hinged glass door, 1 deg. to 12 deg. C, 115V 60Hz
- 13-986-136SA** - Each for \$9486.00  
Alarm Model, 45.5 cu. ft., 2 sliding glass doors; 115V 60Hz
- 13-986-137SA** - Each for \$9347.00  
Alarm Model, 45.5 cu. ft., 2 sliding glass doors; 208/230V 60Hz
- 13-986-138A** - Each for \$9869.00  
Alarm Model, 46.6 cu. ft., 2 sliding glass doors, 115V 60Hz
- 13-986-140A** - Each for \$12283.00  
Alarm Model, 74 cu. ft., 3 hinged glass doors, 115V 60Hz
- 13-986-134** - Each for \$6749.00  
Basic Model, 23.1 cu. ft., 1 hinged glass door; 115V 60Hz
- 13-986-136S** - Each for \$8766.00  
Basic Model, 45.5 cu. ft., 2 sliding glass doors; 115V 60Hz
- 13-986-137S** - Each for \$8661.00  
Basic Model, 45.5 cu. ft., 2 sliding glass doors; 208/230V 60Hz
- 13-986-138** - Each for \$9247.00  
Basic Model; Capacity: 46.6 cu. ft., 115V 60Hz
- 13-986-140** - Each for \$11634.00  
Basic Model, 74 cu. ft., 3 hinged glass doors, 115V 60Hz
- 13-986-136SR** - Each for \$10292.00  
Recorder Model, 45.5 cu. ft., 2 sliding glass doors, 115V 60Hz
- 13-986-138R** - Each for \$10957.00  
Recorder Model, 46.6 cu. ft., 2 sliding glass doors, 115V 60Hz
- 13-986-134RA** - Each for \$8266.00  
Recorder/Alarm Model, 23.1 cu. ft., 1 hinged glass door, 115V 60Hz
- 13-986-136RAV** - Each for \$10980.82  
Recorder/Alarm Model, 45.5 cu. ft., 2 sliding glass doors, 115V 60Hz
- 13-986-138RA** - Each for \$11596.00  
Recorder/Alarm Model, 46.6 cu. ft., 2 sliding glass doors
- 13-986-140RA** - Each for \$13938.00  
Recorder/Alarm Model, 74 cu. ft., 3 hinged glass doors, 115V 60Hz

## Fisher Scientific Small-Vessel Stirrers




- 14-493-120SQ** - Each for \$211.00  
Stirrer; Small-Vessel; Fisher; 6 diameter x 3 in. high (15.2 x 7.6cm); Power Requirements: 120V 60Hz, 0.4A, 48w; Stirring Speed: 200-2500rpm; 25 sq. in. (161cm<sup>2</sup>) surface area

## Fisher Scientific Twistir Mini Stirrers



- 11-510-52** - Each for \$185.00  
Stirrers, Twistir Mini; Fisher Scientific; 115V; Clear, Chemically-resistant Nylon top surface; Plastic base; 8.5cm dia.; Speed 350-2000rpm; Capacity 1L; Desktop; Alchemist; Power-on LED; Includes: Line adapter, stir bar and instructions
- 11-510-50** - Each for \$185.00  
Bacteria 115v
- 11-510-51** - Each for \$185.00  
Caffeine 115v
- 11-510-53** - Each for \$185.00  
DNA stirrer graphics
- 11-510-54** - Each for \$185.00  
Periodic Table 115v
- 11-510-55** - Each for \$185.00  
White Crystal 115v

## Fisherbrand Egg-Shaped Bars



- 14-512-122** - Each for \$11.47 and Case of 50 for \$458.70  
Stir Bar, Magnetic; Fisherbrand; Egg-shaped; PTFE; For round-bottom vessels; 6 dia. x 16mm L
- 14-513-53** - Each for \$13.26 and Case of 50 for \$530.33  
6 dia. x 32mm L
- 14-512-121** - Each for \$14.01 and Case of 50 for \$583.72  
9.5 dia. x 19mm L
- 14-512-120** - Each for \$12.86 and Case of 50 for \$514.50  
12.7 dia. x 25.4mm L
- 14-512-123** - Each for \$14.75 and Case of 50 for \$614.52  
16 dia. x 38mm L
- 14-513-54** - Each for \$17.26 and Case of 50 for \$719.24  
19 dia. x 41mm L
- 14-513-55** - Each for \$26.10 and Case of 50 for \$1087.47  
19 dia. x 64mm L

## Fisherbrand Magnetic Micro Stirring Bars



- 14-513-64** - Each for \$6.44 and Case of 50 for \$214.76  
Stir Bar, Magnetic; Fisherbrand Micro; PTFE; Packaged in snap-cap polyethylene vial; 1.5 dia. x 8mm L
- 14-513-63** - Each for \$6.44 and Case of 50 for \$214.76  
2 dia. x 7mm L
- 14-513-65** - Each for \$7.06 and Case of 50 for \$235.46  
5/16 in. dia.; 2 in. L

## Fisherbrand Octagonal Magnetic Stir Bars



- 14-513-58** - Each for \$5.90 and Case of 50 for \$196.65  
Stir Bar, Magnetic; Fisherbrand; Octagonal; 5/16 in. dia.; 1/2 in. L; pivot rings; Alnico\_V magnet encased in PTFE; flat surface
- 14-513-59** - Each for \$6.44 and Case of 50 for \$214.76  
5/16 in. dia.; 1 in. L
- 14-513-60** - Each for \$7.06 and Case of 50 for \$235.46  
5/16 in. dia.; 1-1/2 in. L
- 14-513-61** - Each for \$8.85 and Case of 50 for \$294.98  
5/16 in. dia.; 2 in. L
- 14-513-62** - Each for \$4.67 and Case of 50 for \$186.95  
5/16 in. dia.; 5/8 in. L
- 14-513-51** - Each for \$7.84 and Case of 50 for \$261.34  
3/8 in. dia.; 1 in. L
- 14-513-52** - Each for \$7.41 and Case of 50 for \$296.21  
3/8 in. dia.; 1-1/2 in. L
- 14-513-66** - Each for \$12.50 and Case of 50 for \$416.59  
3/8 in. dia.; 2 in. L

- 14-513-67** - Each for \$11.77 and Case of 50 for \$470.87  
3/8 in. dia.; 2-1/2 in. L;
- 14-513-56** - Each for \$18.23 and Case of 50 for \$759.61  
1/2 in. dia.; 1-1/2 in. L
- 14-513-68** - Each for \$20.01 and Case of 50 for \$833.63  
1/2 in. dia.; 3 in. L;
- 14-513-57** - Each for \$6.29 and Case of 50 for \$209.59  
1/8 in. dia.; 1/2 in. L

**Fisherbrand Polygon Stir Bars**



- 14-512-124** - Each for \$6.12 and Case of 50 for \$244.69  
Stir Bar, Magnetic; Fisherbrand; Polygon; PTFE PTFE-coated; Smooth; 8 dia. x 12.7mm L
- 14-512-125** - Each for \$6.12 and Case of 50 for \$244.69  
8 dia. x 20mm L
- 14-512-127** - Each for \$8.64 and Case of 50 for \$345.68  
8 dia. x 50mm L
- 14-512-126** - Each for \$6.84 and Case of 50 for \$273.70  
9.5 dia. x 25.4mm L
- 14-512-128** - Each for \$18.23 and Case of 50 for \$759.43  
10 dia. x 70mm L

**Corning Scholar 171 Stirrer**



- 11-497-22** - Case of 1 for \$174.47  
Stirrer, Magnetic; Corning Scholar 171; Stir range 100-1600rpm; 5L x 5 in.W plastic top plate; 5L x 5W x 3-2/32 in.H; 120V 60Hz, 0.24A, 29w

**Denver Instrument PI Series Analytical Balances with Internal Calibration**



- 01-914-20** - Each for \$2973.30  
Balance, Analytical; Denver PI Series; Model PI-114; Single range; With internal calibration; Readability/ Repeatability: 0.1mg; Weighing range: 0-110g; Linearity: 0.2mg
- 01-914-21** - Each for \$3381.30  
Model PI-214; Single range; Weighing Range: 0-210g
- 01-913-120** - Each for \$4584.90  
Model PI-225D; Dual range; Weighing: 0-60/60-220g
- 01-914-22** - Each for \$3789.30  
Model PI-314; Weighing/Taring Range: 0-310g

**Denver Instrument Pinnacle Series Analytical Balances**



- 01-913-81** - Each for \$2615.00  
Balance, Analytical; Denver Pinnacle P-114; Auto calibration; Weighing Range: 0-110g; Readability: 0.1mg; Linearity: 0.2mg; Includes built-in overload, leveling bubble, sealed keypad, and weigh-below port; 115V
- 01-913-82** - Each for \$3015.00  
Weighing Range: 0 to 210g
- 01-914-03** - Each for \$3415.00  
Weighing Range: 0 to 310g

**LaMotte SMART 2 Colorimeter**



- 22-278-615** - Each for \$825.00  
Colorimeter, SMART2, 120V/60Hz, Direct reading colorimeter onsite water analyses, 50+ pre-programmed tests, Multi LED optical system embedded in light chamber/optimized for LaMotte test reagent systems, w/4 sample tubes, AC adapter, manual
- 22-278-616** - Each for \$825.00  
Smart 2 Colorimeter Export

**LaMotte SMART Colorimeter Reagents**

- 22-278-500** - Each for \$33.70  
Reagent; SMART Colorimeter; LaMotte; High-quality reagents manufactured from ACS raw materials for high reproducibility; Analyte: Ammonia Nitrogen; Range (ppm): 0-3.0; Method: Diazotization/Coupling
- 22-278-501** - Each for \$45.00  
Analyte: Bromine/Chlorine/Iodine; Range (ppm): 0-9; 0-4.0; 0-16; Method: DPD tablets
- 22-278-510** - Each for \$13.90  
Analyte: Copper, High; Range (ppm): 0-5.0; Method: Diethyldithiocarbamate
- 22-278-512** - Each for \$78.00  
Analyte: Cyanide; Range (ppm): 0-0.5; Method: Pyridine-barbituric Acid
- 22-278-514** - Each for \$40.00  
Analyte: Fluoride; Range (ppm): 0-2.0; Method: SPADNS
- 22-278-517** - Each for \$35.50  
Analyte: Iron, High; Range (ppm): 0-6.0; Method: 1,10 Phenanthroline
- 22-278-522** - Each for \$36.90  
Analyte: Nitrate Nitrogen; Range (ppm): 0-3.0; Method: Cadmium Reduction
- 22-278-523** - Each for \$36.90  
Analyte: Nitrite Nitrogen; Range (ppm): 0-0.7; Method: Diazotization/Coupling
- 22-278-524** - Each for \$33.00  
Analyte: Oxygen (Dissolved); Range (ppm): 0-12.5; Method: Winkler Colorimetric
- 22-278-526** - Each for \$48.03  
Analyte: pH; Range (ppm): 5.0-9.5; Method: Colorimetric
- 22-278-528** - Each for \$17.50  
Analyte: Phosphate, High; Range (ppm): 0-80.0; Method: Molybdovanadate
- 22-278-529** - Each for \$31.20  
Analyte: Phosphate; Range (ppm): 0-3.0; Method: Ascorbic Acid Reduction
- 22-278-530** - Each for \$46.50  
Analyte: Potassium; Range (ppm): 1.0-10.0; Method: Tetraphenylboron
- 22-278-532** - Each for \$33.00  
Analyte: Silica, High; Range (ppm): 0-75; Method: Silicomolybdate

**LaMotte TC-3000 Tri-Meter**



- 22-278-589** - Each for \$1095.00  
Colorimeter, SMART2, 120V/60Hz, Direct reading colorimeter onsite water analyses, 50+ pre-programmed tests, Multi LED optical system embedded in light chamber/optimized for LaMotte test reagent systems, w/4 sample tubes, AC adapter, manual
- 22-278-590** - Each for \$1095.00  
TC-3000i

**MasterFlex E/S Portable Sampler**



- 13-310-490** - Each for \$1511.75  
Sampler, Portable; MasterFlex E/S; 115V 50/60Hz; Supplied w/ Masterflex Easy-Load pumphead, 50 ft. of L/S 24 Tygon LFL PVC tubing, AC adapter with 12 ft. cord, internal battery (12VDC), and instruction manual

**Mettler Toledo AB-S/FACT Classic Plus Series Analytical Balances**



- 01-916-250** - Each for \$3926.00  
Balance, Analytical; Full metal housing; Large; Permanent shock and overload protection; 0.1mg readability; 0.1mg repeatability; Weighing range: 0 to 51g; 12-5/8 x 9-5/8 x 13-1/2 in.
- 01-916-252** - Each for \$2308.00  
Weighing Range: 0 to 51g/0.1mg
- 01-916-251** - Each for \$4850.00  
Weighing Range: 0 to 61g/0 to 220g
- 01-916-253** - Each for \$2751.00  
Weighing Range: 0 to 101g
- 01-916-254** - Each for \$3445.00  
Weighing Range: 0 to 220g
- 01-916-255** - Each for \$4192.00  
Weighing Range: 0 to 320g

## Mettler Toledo AL Series Analytical Balances



- 01-910-150** - Each for \$1925.00  
Balance, Analytical; Mettler AL Series; Model AL54; Capacity: 51g; Readability: 0.0001g; Simple operation; Stored menu settings; 15 weigh units; Wide selection of user programs, Battery backup for field use; Incl. glass draft shield
- 01-910-152** - Each for \$2328.00  
110g; 1mg
- 01-910-154** - Each for \$2606.00  
210g; 1mg

## Mettler Toledo Excellence Plus XP Micro-Balances



- 01-910-670** - Each for \$17788.00  
Balance; Micro; Mettler; XP26; Capacity of 22g with 0.001mg readability; Taring range: 0 to 22g; Repeatability: 1.5ug; Linearity: 6 ug
- 01-910-671** - Each for \$15179.00  
Model XP26DR; Taring Range 0 to 22g, Repeatability 2ug
- 01-910-650** - Each for \$21079.00  
Model XP56; Taring Range 0 to 52g, Repeatability 1.5ug
- 01-910-651** - Each for \$19323.00  
Model XP56DR; Taring Range 0 to 52 g, Repeatability 2ug

## Oakton TDS Testrs 11 and ECTests 11 Series



- 13-200-278** - Each for \$103.94  
Meter, Conductivity; ECTestr 11 Plus; Oakton; Waterproof, dustproof, and chemical-resistant; Floatable Valox housing; For the analysis of Conductivity, Temperature; Resolution: 0.1uS, 1uS, 0.01mS
- 13-200-277** - Each for \$72.61  
Conductivity, Temperature; Resolution: 10uS; 0.10mS
- 13-200-276** - Each for \$103.94  
Total Dissolved Solids, Temperature; Resolution: 0.1ppm, 1ppm; 0.01ppt
- 13-200-275** - Each for \$72.61  
Total Dissolved Solids, Temperature; Resolution: 10ppm; 0.10ppt

## Ohaus Explorer Pro Series Analytical Balances



- 02-112-116** - Each for \$2382.00  
Balance, Analytical; Explorer Pro; Ohaus; With seven application modes; Advanced display features; 100/210g x 0.1/1mg
- 02-112-117** - Each for \$2698.00  
100/210gx0.1/1mg; With Auto Calibration System
- 02-112-112** - Each for \$2331.00  
110g x 0.1mg
- 02-112-114** - Each for \$2698.00  
210g x 0.1mg
- 02-112-115** - Each for \$3009.00  
210g x 0.1mg; With Auto Calibration System
- 02-112-110** - Each for \$2147.00  
62g x 0.1mg
- 02-112-111** - Each for \$2458.00  
62g x 0.1mg; With Auto Calibration System
- 02-112-113** - Each for \$2642.00  
Analytical Balance, 110g x 0.1mg, With Calibration System

## Ohaus Pioneer Analytical Balances



- 01-918-300** - Each for \$1640.00  
Balance, Analytical; Pioneer; Ohaus; Single-line LCD; No backlight; Three-button panel with dedicated and No functions; RS-232 bidirectional interface; Capacity: 65g
- 01-918-301** - Each for \$1890.00  
Capacity: 110g
- 01-918-302** - Each for \$2140.00  
Capacity: 210g

## Ohaus Voyager Pro Series Analytical Balances



- 02-114-18** - Each for \$2917.00  
Balance, Analytical; Ohaus; Voyager Pro; Capacity: 62g; Model VP64CN; With AutoCal internal calibration; Draftshield; Innovative user interface; RS232-C port with GLP/GMP data output
- 02-114-19** - Each for \$3101.00  
Model VP114CN; Capacity: 110g
- 02-114-20** - Each for \$3468.00  
Model VP214CN; Weighing Range: 0 to 210g; Readability: 0.1mg; 13.8L x 8.3W x 13.8 in.H
- 02-114-21** - Each for \$3157.00  
Model VP214DCN; Capacity: 100g/210g

## Thermo Scientific Cimarec Digital Stirrers



- 11-675-907Q** - Each for \$280.24  
Stirrer, Magnetic; Thermo Scientific Cimarec; Digital; Speed 60 tp 1200rpm; Digital rpm display; 18 sq. in. ceramic top with one stirring position; 15 lb. load capacity; 120V 60Hz; CSA
- 11-675-910Q** - Each for \$295.16  
56 sq. in. ceramic top with one stirring position; 25 lb. load capacity; 120V 60Hz; CSA
- 11-675-913Q** - Each for \$445.41  
110 sq. in. ceramic top with one stirring position; 35 lb. load capacity; 120V 60Hz; CSA

## Thermo Scientific Orion Aquafast IV Colorimeter



- 13-642-157** - Each for \$999.00  
Colorimeter, portable, AQUafast IV, Orion, auto-identification of species to be measured, waterproof to IP67 standards, stores up to 10 methods

## Thermo Scientific Revco General-Purpose Lab Refrigerator/Freezers



- 13-990-118** - Each for \$1758.00  
Refrigerator/Freezer, General-Purpose Lab; Thermo Electron Corporation; Revco; 2 deg. to 10 deg. C/-12 deg. to -20 deg. C Temperature Range; Upright; 18.5 cu. ft.; Three Adjustable Shelves; CFC Free; 115V 60Hz
- 13-991-90** - Each for \$1707.00  
General-Purpose Lab; 2 deg. to 10 deg. C/-12 deg. to -20 deg. C Temperature Range; Upright; 24.6 cu. ft.; 115V 60Hz

Thermo Scientific Revco General-Purpose Refrigerators



**13-990-327** - Each for \$2350.00  
Refrigerator, General-Purpose; Thermo Scientific Revco; 14.5 cu. ft.; Upright; One Solid Door; 3 Interior Shelves; 5 Door Shelves; 2 deg. to 10 deg. C Temperature Range; Manual Defrost; 115V 60Hz  
**13-990-328** - Each for \$2713.00  
Capacity: 20.7 cu.ft.; Upright; Solid door  
**13-990-330** - Each for \$5141.00  
Capacity: 31.1 cu. ft.; Upright; Glass door

Thermo Scientific Stir Light and Aluminum-Top Magnetic Stirrers



**14-511-100Q** - Each for \$605.00  
Stirrer, Magnetic; Thermo Scientific; Stir Light; 7 x 7 in. plate; 100 to 1200rpm; Load cap. 15 lb.; Alnico drive; 5-1/4 in. sq. light-diffusing Plexiglas window; Includes: 9.5 x 50mm PTFE-coated stir bar; 120V 60Hz, 0.6A

Thermo Scientific Super-Nuova Digital Stirrers



**11-675-924Q** - Each for \$780.00  
Stirrer, Magnetic; Thermo Scientific; Super-Nuova Digital; Speed 50 to 1200rpm; Digital rpm display; Knob control; 12-hr. timer; 7.25 x 7.25 in. ceramic top plate with one stirring position; RS-232 port; 120V 60Hz, CSA  
**09-050-288Q** - Each for \$973.93  
Single-position stirrer; Dimensions: 10 x 10; 120V  
**11-475-32Q** - Each for \$1557.00  
Four-position stirrer; Dimensions: 10.25 x 10.25 in. 120V

# Manganese

EM Science Quant Test Strips - For Manganese Testing



**M100801** - Pack of 100 for \$79.73  
Test: Manganese Kit; Pack of: 100; Range: 2-5-20-50-100ppm

Orbeco-Hellige Powder Pack and Tube Test Reagents - For Manganese Testing



**09-053-260** - Each for \$28.25  
Reagent, Colorimeter, Tube Test; Reactive Phosphorus; Orthophosphate; 10mL; 50 Tests

Orbeco-Hellige Powder Packs for Metals - For Manganese Testing



**09-053-230** - Each for \$25.25  
Reagent, Colorimeter, Powder Pack; Manganese; High Range; Manganese Citrate buffer; 10mL; Pack of 100  
**09-053-259** - Each for \$37.90  
Manganese set; High Range  
**09-053-258** - Each for \$34.00  
Manganese set; Low Range

Orbeco-Hellige SC400 Series Colorimeters - For Manganese Testing



**09-053-297** - Each for \$320.00  
Colorimeter; Orbeco-Hellige SC400; Manganese, High-Range; Range, 0.01-0.70mg/L  
**09-053-282** - Each for \$320.00  
Manganese, Low-Range

# Microbiological

Fisher Scientific Isotemp Digital-Control Water Baths



**15-462-3Q** - Each for \$795.00  
Bath; General Purpose; Fisher; Isotemp Digital Model 202; 2L capacity; PID control; ambient to 100 deg. C; +/-0.24 deg. C uniformity; +/-0.5 deg. C accuracy/stability at 37 deg. C  
**15-462-S3Q** - Each for \$906.00  
Reservoir Capac.: 2L; 230V 60Hz; Model 202; Hinged Stainless-steel Cover  
**15-462-3SQ** - Each for \$922.00  
Reservoir Capac.: 2L; 230V 60Hz; Model 202S; Hinged Acrylic Cover  
**15-462-S3SQ** - Each for \$980.00  
Reservoir Capac.: 2L; 230V 60Hz; Model: 202S; Hinged Stainless-steel Cover  
**15-462-6Q** - Each for \$974.00  
Reservoir Capac.: 5L; 230V 60Hz; Model 205; Hinged Acrylic Cover  
**15-462-S6Q** - Each for \$943.00  
Reservoir Capac.: 5L; 230V 60Hz; Model 205; Hinged Stainless-steel Cover  
**15-462-S15Q** - Each for \$1907.00  
Reservoir Capac.: Dual 5L/10L; 120V 50/60Hz; Model 215; Hinged Stainless-steel Cover  
**15-462-S16Q** - Each for \$2008.00  
Reservoir Capac.: Dual 5L/10L; 230V 60Hz; Model 215; Hinged stainless-steel cover  
**15-462-S10Q** - Each for \$1276.00  
Reservoir Capac.: 10L; 120V 50/60Hz; Model: 210, Hinged Stainless-steel Cover  
**15-462-S11Q** - Each for \$1127.00  
Reservoir Capac.: 10L; 230V 60Hz; Model 210; Hinged Stainless-steel Cover  
**15-462-S20Q** - Each for \$1434.00  
Reservoir Capac.: 20L; 120V 50/60Hz, 8.3A; Model: 220, Stainless-steel Gable Cover  
**15-462-S21Q** - Each for \$1274.00  
Reservoir Capac.: 20L; 230V 60Hz; Model 220; Hinged Stainless-steel Cover  
**15-462-S28Q** - Each for \$1838.00  
Reservoir Capac.: 28L; 120V 50/60Hz, 8.3A; Model: 228, Stainless-steel Gable Cover



**15-462-S29Q** - Each for \$1494.00  
Reservoir Capac.: 28L; 230V 60Hz; Model 228; Hinged  
Stainless-steel Cover

### Fisher Scientific Isotemp Economy Analog Control Water Baths



**15-460-2Q** - Each for \$581.00  
Bath; General Purpose; Fisher; Isotemp Analog-Control  
Water Bath Model 102; 2L capacity; ambient +5 deg. C to  
85 deg. C; to 100 deg. C with cover; Uniformity/Stability;  
+/-0.2 deg. C at 37 deg. C  
**15-460-2SQ** - Each for \$577.00  
2L capacity; acrylic cover  
**15-460-S2SQ** - Each for \$710.00  
2L capacity; shallow form; stainless-steel cover  
**15-460-S2Q** - Each for \$717.00  
2L capacity; stainless-steel cover  
**15-460-15Q** - Each for \$1628.00  
5/10L capacity  
**15-460-S15Q** - Each for \$1799.00  
5/10L capacity; stainless-steel cover  
**15-460-5Q** - Each for \$706.00  
5L capacity  
**15-460-S5Q** - Each for \$849.00  
5L capacity; stainless-steel cover  
**15-460-S10Q** - Each for \$1021.00  
10L capacity; stainless-steel cover  
**15-460-20Q** - Each for \$1006.00  
20L capacity  
**15-460-S20Q** - Each for \$1022.00  
20L capacity; stainless-steel cover  
**15-460-28Q** - Each for \$1224.00  
28L capacity; acrylic cover  
**15-460-S28Q** - Each for \$1226.00  
28L capacity; stainless-steel cover

### Fisherbrand Compartmentalized Disposable Petri Dishes



**08-757-150** - Case of 500 for \$265.45  
Petri Dish, Disposable; Sectioned plates; W/numbered  
sections; Radiation sterilized; Polystyrene; 25/  
polyethylene sleeve; Size: 100 dia. x 15mm H; Type: I (2  
sections)  
**08-758-3** - Case of 500 for \$280.25  
Size: 100 dia. x 15mm H; Type: Y (3 sections)  
**08-758-2** - Case of 500 for \$278.25  
Size: 100 dia. x 15mm H; Type: X (4 sections)

### Fisherbrand Disposable Contact Plate



**08-757-11C** - Case of 500 for \$234.65  
Plates, Contact; Disposable; Fisherbrand; 65 x 15mm  
Sterile; Sixteen 10 x 10mm square grid; Marked  
numerically and alphabetically

### Fisherbrand Disposable Petri Dishes and Pad Dishes



**09-720-500** - Pack of 150 for \$47.14  
Dish, Petri; Fisherbrand; Disposable; Petri Dishes; Pack  
of 150  
**09-720-502** - Pack of 600 for \$144.00  
Petri Dishes; Pack of 600  
**09-720-501** - Pack of 150 for \$59.04  
Petri Dishes, with pads; Pack of 150  
**09-720-503** - Pack of 600 for \$190.00  
Petri Dishes, with pads; Pack of 600

### Fisherbrand Extra-Deep Disposable Petri Dishes



**08-757-11Z** - Case of 500 for \$207.58  
Petri Dish, Disposable; Polystyrene; Stackable; Extra-  
deep for deeper media fills; Ideal for fungal cultures, plant  
propagation; radiation sterilized; 20 per polyethylene  
sleeve; Dia. x H: 100 x 20mm  
**08-757-11** - Case of 500 for \$251.09  
Vented; Dia. x H: 100 x 25mm

### Fisherbrand Media-Miser Disposable Petri Dishes



**08-757-13A** - Case of 500 for \$174.65  
Petri Dish, Disposable; Media-Miser; Fisherbrand;  
Polystyrene; Smaller size saves media; Clear tops; Snug  
fit lids; Venting ribs; Raised, straight ridge for stacking;  
Radiation-sterilized; Dia. x H (approx): 60 x 15mm  
**08-757-14G** - Case of 500 for \$174.35  
Dia. x H (approx): 85 x 15mm

### Fisherbrand Polyethylene Biohazard Autoclave Bags



**01-832A** - Case of 100 for \$181.09  
Bag, Biohazard Autoclave; Fisherbrand; Polyethylene;  
Plain; Clear; Max. temp: 127 deg. C; Pass Dart Impact  
Resistance Test of 165g (using ASTM D1709-85);  
Thickness: 4.0mil; Size: 24 x 36 in.  
**01-827A** - Pack of 200 for \$88.72  
Clear polyethylene; Printed; Size: 8 x 12 in.; 1.5mil  
**01-827B** - Pack of 200 for \$96.42  
Clear polyethylene; Printed; Size: 12 x 24 in.; 1.5mil  
**01-827C** - Pack of 200 for \$271.63  
Clear polyethylene; Printed; Size: 24 x 30 in.; 1.5mil  
**01-827D** - Pack of 200 for \$297.87  
Clear polyethylene; Printed; Size: 24 x 36 in.; 1.5mil  
**01-814-1** - Pack of 200 for \$77.71  
Clear; Plain; Polyethylene; Thickness: 1.5mil; Size: 12 W  
x 24 in. L  
**01-814-2** - Pack of 200 for \$203.41  
Clear; Plain; Polyethylene; Thickness: 1.5mil; Size: 24 W  
x 30 in. L  
**01-814-3** - Pack of 200 for \$244.62  
Clear; Plain; Polyethylene; Thickness: 1.5mil; Size: 24 W  
x 36 in. L  
**01-829A** - Pack of 200 for \$90.78  
Red polyethylene; Printed; Size: 8 x 12 in.; 1.5mil  
**01-829B** - Pack of 200 for \$217.56  
Red polyethylene; Printed; Size: 14 x 19 in.; 1.5mil  
**01-829C** - Pack of 200 for \$308.69  
Red polyethylene; Printed; Size: 19 x 23 in.; 1.5mil  
**01-831A** - Case of 100 for \$195.19  
Red polyethylene; Printed; Size: 24 x 36 in.; 4mil  
**01-829D** - Pack of 200 for \$435.07  
Red polyethylene; Printed; Size: 25 x 35 in.; 1.5mil  
**01-829F** - Pack of 200 for \$344.05  
Red polyethylene; Printed; Size: 33 x 30 in.; 1.5mil  
**01-829E** - Pack of 100 for \$243.66  
Red polyethylene; Printed; Size: 38 x 48 in.; 1.5mil  
**01-831B** - Case of 50 for \$224.71  
Red polyethylene; Printed; Size: 38 x 48 in.; 4mil


### Fisherbrand Polypropylene Biohazard Autoclave Bags



**01-826-1** - Pack of 200 for \$74.07  
Bag, Biohazard Autoclave; Fisherbrand; Polypropylene;  
Plain; Clear; Max. temp: 140 deg. C; Pass Dart Impact  
Resistance Test of 165g (using ASTM D1709-85); With  
elastic closure; Thickness: 2.0mil; Size: 8 x 12 in.  
**01-826-3** - Pack of 200 for \$71.65  
Clear polypropylene; Plain; Size: 10 x 12 in.; 2mil  
**01-826-4** - Pack of 200 for \$85.99  
Clear polypropylene; Plain; Size: 10 x 15 in.; 2mil  
**01-826-5** - Pack of 200 for \$123.81  
Clear polypropylene; Plain; Size: 12 x 24 in.; 2mil  
**01-826-6** - Pack of 200 for \$282.68  
Clear polypropylene; Plain; Size: 24 x 30 in.; 2mil  
**01-826-7** - Pack of 200 for \$302.11  
Clear polypropylene; Plain; Size: 24 x 36 in.; 2mil  
**01-826-2** - Pack of 200 for \$71.03  
Clear polypropylene; Plain; Size: 10 x 10 in.; 2mil  
**01-826A** - Pack of 200 for \$161.44  
Clear polypropylene; Printed; Size: 12 x 24 in.; 2mil  
**01-826B** - Pack of 200 for \$300.94  
Clear polypropylene; Printed; Size: 24 x 30 in.; 2mil  
**01-826C** - Pack of 200 for \$350.72  
Clear polypropylene; Printed; Size: 24 x 36 in.; 2mil  
**01-826D** - Pack of 200 for \$467.20  
Clear polypropylene; Printed; Size: 31 x 38 in.; 2mil  
**01-826E** - Pack of 100 for \$339.86  
Clear polypropylene; Printed; Size: 37 x 48 in.; 2mil  
**01-830A** - Pack of 200 for \$78.59  
Red polypropylene; Plain; Size: 8 x 12 in.; 2mil

- 01-830B** - Pack of 200 for \$144.07  
Red polypropylene; Plain; Size: 14 x 19 in.; 2mil
- 01-830C** - Pack of 200 for \$188.27  
Red polypropylene; Plain; Size: 19 x 23 in.; 2mil
- 01-830D** - Pack of 200 for \$294.48  
Red polypropylene; Plain; Size: 25 x 35 in.; 2mil
- 01-830E** - Pack of 100 for \$252.15  
Red polypropylene; Plain; Size: 37 x 48 in.; 2mil
- 01-828A** - Pack of 200 for \$94.95  
Red polypropylene; Printed; Size: 8 x 12 in.; 2mil
- 01-828B** - Pack of 200 for \$158.24  
Red polypropylene; Printed; Size: 14 x 19 in.; 2mil
- 01-828C** - Pack of 200 for \$207.94  
Red polypropylene; Printed; Size: 19 x 23 in.; 2mil
- 01-828D** - Pack of 200 for \$335.40  
Red polypropylene; Printed; Size: 25 x 35 in.; 2mil
- 01-828E** - Pack of 100 for \$324.77  
Red polypropylene; Printed; Size: 37 x 48 in.; 2mil

### Fisherbrand Square Disposable Petri Dish with Grid



- 08-757-11A** - Case of 500 for \$298.68  
Petri Dish, Square; Disposable; W/Grid of thirty-six 13 x 13mm squares; Polystyrene; Radiation Sterilized; L x W x H: 100 x 100 x 15mm; 10 per polyethylene sleeve

### Fisherbrand Water-Testing Membrane Filters



- 09-719-1C** - Pack of 100 for \$73.00  
Filter, Membrane; Water-Testing; Fisherbrand; Designed for determining bacterial levels, including coliforms, in water, sewage, foods, and filterable beverages; Pore Size: 0.45um; Bulk Packed; Nonsterile
- 09-719-555** - Pack of 600 for \$257.00  
Individually Wrapped; Sterile

### Brinkmann/Tuttnauer Tabletop Autoclaves



- 02-964-40** - Each for \$6670.00  
Autoclave; Tabletop; Tuttnauer; Model 3545M; Self-contained design with refillable reservoir controls water purity for sterilization; 220V 50/60Hz; 2200w. With analog controls
- 02-964-1** - Each for \$3770.00  
1050w; Analog Controls; Trays: 3; 120V
- 02-964-3** - Each for \$4310.00  
1400w; Analog Controls; Trays: 3; 120V
- 02-964-4** - Each for \$4310.00  
1400w; Analog Controls; Trays: 3; 220V
- 02-964-19** - Each for \$4990.00  
1400w; Analog Controls; Trays: 4; 120V
- 02-964-7** - Each for \$5760.00  
1400w; Electronic Controls and Printer; Trays: 3; 120V
- 02-964-20** - Each for \$5770.00  
1400w; Electronic Controls and Printer; Trays: 3; 220V
- 02-964-10** - Each for \$6370.00  
1400w; Electronic Controls and Printer; Trays: 4; 120V
- 02-964-5** - Each for \$5340.00  
1400w; Electronic Controls; Trays: 3; 120V
- 02-964-9** - Each for \$5930.00  
1400w; Electronic Controls; Trays: 4; 120V
- 02-964-11** - Each for \$5940.00  
1400w; Electronic Controls; Trays: 4; 220V
- 02-964-25** - Each for \$7060.00  
2100w; Electronic Controls and Printer; Trays: 4; 220V
- 02-964-42** - Each for \$7620.00  
2200w; Electronic Controls and Printer; Trays: 2; 220V
- 02-964-41** - Each for \$7140.00  
2200w; Electronic Controls; Trays: 2; 220V
- 02-964-26** - Each for \$10700.00  
2400w; Analog Controls; Trays: 2; 220V
- 02-964-28** - Each for \$12800.00  
2400w; Electronic Controls and Printer; Trays: 2; 220V
- 02-964-27** - Each for \$12700.00  
2400w; Electronic Controls; Trays: 2; 220V
- 02-964-13** - Each for \$14300.00  
2700w; Analog Controls; Trays: 2; 220V

### Brinkmann/Tuttnauer Vertical Top-Loading Autoclaves



- 13-880-100** - Each for \$8995.00  
Autoclave, Vertical top-loading; Brinkmann/Tuttnauer; Model 2540 ELV; 220V 50/60Hz
- 13-880-101** - Each for \$8620.00  
Model 2540 ELVC, 220V 50/60Hz
- 13-880-102** - Each for \$13765.00  
Model 3850 ELV, 400V 50/60Hz
- 13-880-103** - Each for \$15600.00  
Model 3850 ELVC, 400V 50/60Hz
- 13-880-104** - Each for \$17335.00  
Model 3870 ELV, 400V 50/60Hz
- 13-880-105** - Each for \$18660.00  
Model 3870 ELVC, 400V 50/60Hz

### CPI International Colitag Test Kit



- 46000013** - Pack of 100 for \$530.45  
Water Testing Kits; Presence/Absence; Colitag P/A Test Kit; Ready-to-use dehydrated media packet for use with 100mL water sample
- 46000040** - Each for \$6.27  
Color Comparator

### Decon OdorGone Autoclave Deodorizer



- 22-032079** - Pack of 25 for \$29.70 and Case of 8 Packs for \$203.08  
Deodorizer, Autoclave; OdorGone; Removes unpleasant smells as heat and moisture from the autoclave; Scent: Apple; Pack Size: 25 Caps
- 22-032080** - Pack of 100 for \$93.96 and Case of 6 Packs for \$487.15  
Scent: Apple; Pack size: 100 caps
- 22-032084** - Pack of 100 for \$93.96 and Case of 6 Packs for \$487.15  
Scent: Heather; Pack size: 100 Caps
- 22-032085** - Pack of 25 for \$28.29 and Case of 8 Packs for \$193.41  
Scent: Lemon; Pack size: 25 caps
- 22-032087** - Pack of 100 for \$93.96 and Case of 6 Packs for \$487.15  
Scent: Lemon; Pack size: 100 caps

### Market Forge Sterilmatic Steam Pressure Sterilizers



- 14-460** - Each for \$10662.29  
Sterilizers; Sterilmatic; Model: Fixed Temperature; Temperature: 121 deg. C; Chamber: 16 dia. x 26 in.D; Exhaust speed dial; 0-60 timer; Front-mounted controls; Adjustable feet; 208/240V 60Hz
- 14-460-10** - Each for \$10972.73  
Model: Variable Temperature

### Market Forge Sterilmatic Sterilizer Stand

- 14-460-12** - Each for \$845.08  
Accessory, Sterilizer; Sterilmatic; Market Forge; Sterilizer Stand; Stainless steel with adjustable feet; L x W x H: 31 x 18-3/4 x 29 in.

### Market Forge Sterilmatic Sterilizer Tray

- 14-460-14** - Each for \$215.42  
Accessory, Sterilizer; Sterilmatic; Market Forge; Sterilizer Tray; Stainless steel with rounded corners; L x W x H: 20 x 12 x 12-1/2 in.

### Millipore EZ-Pak Membranes and Dispenser



- EZGSWG474** - Pack of 600 for \$330.00  
Filter, Membrane; EZ-Pak; with Dispenser; Black/Gridded; Individually Sealed, Sterile 47mm 0.22 MH
- MSP000814** - Pack of 600 for \$288.00  
Pore Size: 0.45um; Black gridded
- EZHAGG474** - Pack of 600 for \$330.00  
Pore Size: 0.45um; Green; Gridded
- EZHAWG474** - Pack of 600 for \$275.00  
Pore Size: 0.45um; White gridded

- EZHCWG474** - Pack of 600 for \$313.00  
Pore Size: 0.7um; White; Gridded
- EZAABG474** - Pack of 600 for \$326.00  
Pore Size: 0.8um; Black
- EZAAWG474** - Pack of 600 for \$326.00  
Pore Size: 0.8um; White; Gridded

### Millipore Microbial Count Samplers

- MHPC10025** - Pack of 25 for \$108.00  
Sampler, Total Count; HPC; pH at 25 deg. C: 7.1 +/-0.2; Red; Gridded filter surface; Polyethylene paddle, SAN chambers; Mixed Cellulose Esters; 0.45microm
- MT0010025** - Pack of 25 for \$121.00  
Total Count Sampler, White

### Millipore Microbiological Analysis Membrane Filters



- GSWP025S0** - Pack of 100 for \$107.00  
Filter, Sterile Membrane; S-Pak; Millipore; Packaging: Individually sealed; Pore size: 0.22um; Diameter: 25mm; White/Plain
- GSWP047S0** - Pack of 100 for \$98.00  
Pore size: 0.22um; Diameter: 47mm; White/Plain
- HABG047S6** - Pack of 600 for \$295.00  
Pore size: 0.45um; Diameter: 47mm; Black/Gridded
- HABG047S0** - Pack of 100 for \$111.00  
Pore size: 0.45um; Diameter: 47mm; Black/Gridded; With absorbant pad
- HAWG047S6** - Pack of 600 for \$234.00  
Pore size: 0.45um; Diameter: 47mm; White/Gridded
- HAWG047S0** - Pack of 100 for \$96.00  
Pore size: 0.45um; Diameter: 47mm; White/Gridded; With absorbant pad
- HAWP047S0** - Pack of 100 for \$98.00  
Pore size: 0.45um; Diameter: 47mm; White/Plain
- HAWP047A0** - Pack of 100 for \$92.00  
Pore size: 0.45um; Diameter: 47mm; White/Plain; Nonsterile
- HCWG047S6** - Pack of 600 for \$267.00  
Pore size: 0.7um; Diameter: 47mm; Black/Gridded
- AABG047S6** - Pack of 600 for \$289.00  
Pore size: 0.8um; Diameter: 47mm; Black/Gridded
- AAWG047S6** - Pack of 600 for \$289.00  
Pore size: 0.8um; Diameter: 47mm; White/Gridded
- AAWG047S0** - Pack of 100 for \$101.00  
Pore size: 0.8um; Diameter: 47mm; White/Gridded; With absorbant pad
- AAWP047S0** - Pack of 100 for \$111.00  
Pore size: 0.8um; Diameter: 47mm; White/Plain

### Millipore Nutrient Media



- MHA00BSM2** - Pack of 50 for \$52.00  
Media; Microbiology; Nutrient Media; Millipore; Brettanomyces Selective Broth; 2mL plastic ampule; For detection of Brettanomyces; 50/pack
- MHA00P2S** - Pack of 50 for \$64.00  
HPC and Total Count Broth; 2mL ampule; 50 per pack
- MHA00FCR2** - Pack of 50 for \$57.00  
m-Fc Broth w/o Rosolic Acid; 2mL ampule
- MHA00P2F** - Pack of 50 for \$64.00  
m-FC Fecal Broth; 2mL ampule
- MHA00P2M** - Pack of 50 for \$64.00  
m-Green (Yeast/Mold) Selective Broth; 2mL ampules
- MHA00P2P** - Pack of 50 for \$64.00  
Pseudomonas Selective Broth; 2mL ampule
- MHA00P2T** - Pack of 50 for \$64.00  
Standard Plate Broth (TGE); 2mL ampule
- MHA00P2D** - Pack of 50 for \$64.00  
Wallerstein Differential; 2mL ampule

### Nalge Lab-Tek Extra-depth Polystyrene, Disposable Petri Dishes



- 08-757-28** - Case of 300 for \$245.50  
Dish, Petri; Lab-tek; Deep Petri 100 x 25mm Internal Dim 86mm Nunc
- 08-757-10E** - Case of 72 for \$165.25  
150 x 25mm

### Precision Bath Accessories




- 15-459-2** - Each for \$220.70  
Rack, 96-Dish; For Thermo Scientific Precision Coliform Incubator Bath; Stainless Steel; With wwo rack-retaining clips

### Propper Blue Autoclavable Tapes



- 11-889-5** - Each for \$7.91 and Case of 36 for \$227.58  
Tape, Autoclave; Propper; Strong adhesive backing sticks securely to disposable wraps; High-contrast white, steam-sensitive stripes turn dark when subjected to steam autoclaving temperature; Blue; 1 in. x 60 yd.
- 11-889-4** - Each for \$5.93 and Case of 48 for \$227.37  
3/4 in. x 60 yd.

### Propper White Autoclave Indicator Tape



- 11-889-14** - Each for \$5.61 and Case of 16 for \$67.62  
Tape, Autoclave Indicator; For steam sterilization; White stripes turn dark to indicate complete processing, Color: White; Size: 1 in. x 14 yd.

### Remel WaterBugs



- R4757090** - Pack of 10 for \$259.06  
Water Bugs E. cloacae ATCC 1304; Water/wastewater quality control testing microorganisms in Quanti-Cult format; deliver less than 50 CFUs in a single inoculum to mimic water samples; 1 Test/Reconstituted Vial
- R4751985** - Pack of 10 for \$264.88  
E.coli Strain C1
- R4753935** - Pack of 10 for \$264.88  
K. pneumoniae Strain C6
- R4757060** - Pack of 10 for \$260.18  
P. aeruginosa
- R4757059** - Pack of 10 for \$298.22  
P. mirabilis

### Sciencware Odo-Clave Deodorant Pads



- 14-488-30** - Pack of 100 for \$69.35 and Case of 10 Packs for \$603.00  
Pad, Deodorant; Odo-Clave; Sciencware; Clove-scented; Heat-release deodorant works automatically at autoclave temperatures; 1-1/2 x 1-1/2 in. pads
- 14-488-31** - Pack of 100 for \$110.06 and Case of 10 Packs for \$957.00  
2-1/4 x 2-1/4 in. pads

### Thermo Scientific Indicators, Incubator and Pouches



- 14-490-24** - Pack of 100 for \$383.00  
Indicators, Incubator and Pouches; Thermo Scientific; For methods to monitor steam sterilizer effectiveness; BT/ Sure Biological Indicator for instruments, glassware and other apparatus; Pack of 100
- 14-490-25** - Pack of 5 for \$26.10  
BT/Sure Biological Indicator for instruments, glassware and other apparatus; Pack of 5
- 14-490-33** - Pack of 200 for \$19.01  
Chemitest Self-Sealing Pouch; 2-1/4 x 5 in.
- 14-490-34** - Pack of 200 for \$19.84  
Chemitest Self-Sealing Pouch; 2-3/4 x 10 in.
- 14-490-36** - Pack of 200 for \$21.49  
Chemitest Self-Sealing Pouch; 3-1/2 x 10 in.
- 14-490-37** - Pack of 200 for \$33.07  
Chemitest Self-Sealing See-Thru Indicator Pouches

- 11-715-140A** - Pack of 100 for \$399.00  
Sterilamp II Biological Indicator for media and additives;  
Pack of 100
- 11-715-140** - Pack of 25 for \$125.00  
Sterilamp II Biological Indicator for media and additives;  
Pack of 25
- 14-490-31** - Pack of 250 for \$34.11  
Strips; For Chemiclave Sterilizers only
- 14-490-27** - Pack of 250 for \$36.30  
Strips; For Steam Sterilizers only
- 14-490-32** - Pack of 250 for \$33.80  
Tabs; self-adhering; 1-1/4 x 1-1/4 in.
- 14-490-30** - Each for \$38.80  
Tape-Closure system for packs, bags or other containers;  
11/2W x 360 in.L roll

# Nitrogen (including Ammonia, Nitrate and Nitrite)

## CHEMetrics Chemets Self-Filling Ampules - For Nitrogen Testing



- 13-299-209** - Each for \$60.62  
Kit, Test; Chemets; CHEMetrics; Provide results in two minutes or less; Analyte: Ammonia; Testing Range: 0-1 and 1-10ppm; Analytical Method: Nesslerization; Complete Test Kit
- 13-299-209A** - Pack of 30 for \$28.00  
Ammonia; Testing Range: 0-1 and 1-10ppm; Analytical Method: Nesslerization; Refil Ampule
- 13-299-508F** - Pack of 30 for \$33.70  
Nitrate; Testing Range: 0-1 and 1-5ppm; Analytical Method: Cadmium Reduction/Azo Dye Formation; Refil Ampule
- 13-299-242** - Each for \$24.81  
Nitrite; Testing Range: 0-0.4 and 0.40-2.0ppm; Analytical Method: Azo Dye Formation; Refil Ampule

## EM Science Quant Test Strips - For Nitrogen Testing



- M100241** - Pack of 50 for \$69.68  
Test: Ammonium Kit; Pack of: 100; Range: 10-30-60-100-200-400ppm
- M100071** - Pack of 100 for \$53.95  
Test: Nitrate; Range: 1-5-10-20-40-80ppm
- M100201** - Pack of 100 for \$54.19  
Test: Nitrate; Range: 10-25-50-100-250-500ppm
- M100501** - Pack of 25 for \$35.75  
Test: Nitrate; Range: 10 to 500ppm; 25/Pk.
- M100221** - Pack of 100 for \$54.19  
Test: Nitrite; Range: 0.1 to 3.0g/L

## LaMotte Series 1200 Colorimeter Single-Test Kits - For Nitrogen Testing



- 22-307-840** - Each for \$67.20  
Colorimeter; Series 1200; LaMotte; Single-parameter; Water-resistant, handheld single-parameter meters; Analyte: Ammonia Nitrogen; Range (ppm): 0-2.0; Method: Salicylate Octa-Slide
- 22-278-565** - Each for \$450.00  
Analyte: Ammonia Nitrogen; Range (ppm): 0-5.0; Method: Nessler
- 22-278-575** - Each for \$469.58  
Analyte: Nitrate Nitrogen; Range (ppm): 0-3.0; Method: Cadmium Reduction

## Orbeco Model 942 Mini Analysts Ordering Information - With Reagent Tablets - For Nitrogen Testing

- 15-405-125** - Each for \$294.73  
Spectrophotometer; Model 942; Orbeco; With reagent tablets; 50 tests; Test: Nitrate; Range: 0-1.0mg/L

## Orbeco Model 942: Test Kits for 975MP Analyst and 942 Mini Analysts - With Liquid Reagents - For Nitrogen Testing

- 15-410-E** - Each for \$18.36  
Reagent; Test Kit for 975MP Analyst; Orbeco; Liquid Reagents; Test: Ammonia Nitrogen, high; Range: 0-6.8mg/L
- 23-023-999** - Each for \$44.03  
Test: Nitrate; Range: 0-1.0mg/L

## Thermo Scientific Napco Model 8000DSE Sterilizer



- 14-487-2** - Each for \$5168.36  
Sterilizer; Napco; Benchtop; Stainless steel; Slow cooldown cycle; Builtin drying element; Chamber: 9 dia. x 18 in. D; Operating range: 121-132 deg. C; Reservoir capacity: 1 qt.; 0-70 min. timer; Includes 1 tray; 120V, 60Hz, 14.6A
- 14-487-1** - Each for \$5630.27  
220V, 50Hz, 8A

## Thermo Scientific Napco Model 9000D Autoclave/Dryer



- 14-486** - Each for \$4816.64  
Dryer, Autoclave; Napco; Stainless steel; 21 L x 18 W x 14 in. H; 1 qt. cap.; 90 lb.; For sterilizing instruments and solids; one tray; Uses tap water; 115V 60Hz, 12A
- 14-486A** - Each for \$5297.99  
230V 50/60Hz, 6A

## Thermo Scientific Precision Coliform Incubator Baths



- 15-459-12** - Each for \$2200.00  
Bath, Coliform; Thermo Scientific Precision; Stainless steel bath chamber; Centrifugal water pump; Microprocessor controlled; Small-Capacity Model; Dimensions: 15-1/2 x 18-1/2 x 9-1/2 in.; 115V, 50/60Hz
- 15-459-13** - Each for \$2300.00  
Small-Capacity Model; Dimensions: 15-1/2 x 18-1/2 x 9-1/2 in.; 230V, 50/60Hz
- 15-459-15** - Each for \$2445.00  
Large-Capacity Model; Dimensions: 14 x 36 x 9-1/2 in.; 115V, 50/60Hz

## Thermo Scientific SterileMax Tabletop Sterilizers



- 14-488-24** - Each for \$8693.00  
Sterilizer; SterileMax; Tabletop; Holds three 2L flasks; 4 preset cycles; Builtin water pump; Insulated chamber; 3 chamber locks; Integral access port; Includes 1 rack, 1 lg and 1sm. tray, line cord, plug; With printer; 120V 50/60Hz
- 14-490-3** - Each for \$7824.00  
Without Printer 230v
- 14-490-1** - Each for \$8000.00  
Without printer; 120V 50/60Hz

## Wisconsin Aluminum Portable Tabletop Sterilizer



- 14-461-5** - Each for \$939.15  
Sterilizer, Portable; Wisconsin Aluminum; Aluminum construction; With heater; Operating range: 240 deg. F/10psi to 259 deg. F/20psi; Capacity: 14-1/2 qt.

### Orbeco-Hellige Powder Pack and Tube Test Reagents - For Nitrogen Testing



- 09-053-264** - Each for \$71.25  
Reagent, Colorimeter; Powder Pack; Ammonia; 10mL; 100 Tests
- 09-053-268** - Each for \$63.75  
Ammonia set; Low Range
- 09-054-103** - Each for \$58.75  
Ammonia set; High Range
- 09-053-237** - Each for \$26.50  
Molybdate HR3; 25mL
- 09-053-229** - Each for \$18.25  
Nitra X Reagent B
- 09-053-267** - Each for \$49.25  
Nitrate set
- 09-053-239** - Each for \$23.45  
Nitrite 3; 10mL
- 09-053-238** - Each for \$26.50  
Nitrite 3; 25mL
- 09-053-265** - Each for \$83.75  
Total Nitrogen set; Low Range
- 09-053-266** - Each for \$88.75  
Total Nitrogen set; High Range

### Orbeco-Hellige SC400 Series Colorimeters - For Nitrogen Testing



- 09-053-275** - Each for \$320.00  
Colorimeter; Orbeco-Hellige SC400; Ammonia; Range, 0.01-0.80mg/L

### Thermo Scientific Orion AQUAfast II Colorimeters Single Parameter Kits - For Nitrogen Testing



- 13-642-026** - Each for \$340.43  
Colorimeter; AQUAfast II; Thermo Scientific Orion; Single parameter; Ideal for fast, accurate water quality testing in the laboratory and the field; Analyte: Nitrate Nitrogen; Range: 0.05 to 0.5mg/L
- 13-642-025** - Each for \$340.43  
Analyte: Nitrate Nitrogen; Range: 1.0 to 40mg/L

## Ozone and Phenol

### CHEMetrics Chemets Self-Filling Ampoules - For Ozone and Phenol Testing



- 13-299-205** - Each for \$60.62  
Kit, Test; Chemets; CHEMetrics; Provide results in two minutes or less; Analyte: Phenols; Testing Range: 0-1 and 0-12ppm; Analytical Method: 4-Aminoantipyrine; Complete Test Kit
- 13-299-205A** - Pack of 30 for \$28.00  
Phenols; Testing Range: 0-1 and 0-12ppm; Analytical Method: 4-Aminoantipyrine; Refil Ampule

### Orbeco Model 942 Mini Analysts Ordering Information - With Reagent Tablets - For Ozone and Phenol Testing

- 15-405-127** - Each for \$294.73  
Spectrophotometer; Model 942; Orbeco; With reagent tablets; 50 tests; Test: Ozone; Range: 0-3.5mg/L

### Orbeco Model 942: Test Kits for 975MP Analyst and 942 Mini Analysts - With Reagent Tablets - For Ozone and Phenol Testing

- 15-410-K** - Each for \$9.34  
Reagent, Test Kit; For use with 975MP and 942 Mini Analysts; 50 tests; Test: Ozone; Range: 0-3.5mg/L

## Phosphates, Phosphorus and Silica

### CHEMetrics Chemets Self-Filling Ampoules - For Phosphate and Silica Testing



- 13-299-216N** - Each for \$57.84  
Kit, Test; Chemets; CHEMetrics; Provide results in two minutes or less; Analyte: Phosphate; Testing Range: 0-1.0 and 1-10ppm; Analytical Method: Molybdenum Blue/Stannous Chloride; Complete Test Kit
- 13-299-216P** - Each for \$24.13  
Phosphate; Testing Range: 0-1.0 and 1-10ppm; Analytical Method: Molybdenum Blue/Stannous Chloride; Refil Ampule
- 13-299-257** - Pack of 1 for \$57.84  
Silica; Testing Range: 0-1 and 1-10ppm; Analytical Method: Heteropoly Blue; Complete Test Kit
- 13-299-508L** - Pack of 30 for \$24.13  
Silica; Testing Range: 0-1 and 1-10ppm; Analytical Method: Heteropoly Blue; Refil Ampule

### LaMotte Series 1200 Colorimeter Single-Test Kits - For Phosphate and Silica Testing



- 22-278-577** - Each for \$425.53  
Colorimeter; Series 1200; LaMotte; Single-parameter; Water-resistant, handheld single-parameter meters; Analyte: Phosphate; Range (ppm): 0-3.0; Method: Ascorbic Acid
- 22-307-851** - Each for \$77.65  
Analyte: Phosphate; Range (ppm): 0-15; Method: Stanous Chloride Octa-Slide

### Orbeco Model 942 Mini Analysts Ordering Information - With Reagent Tablets - For Phosphate and Silica Testing

- 15-405-128** - Each for \$302.10  
Spectrophotometer; Model 942; Orbeco; With reagent tablets; 50 tests; Test: Phosphate, high range; Range: 0-100mg/L

### Orbeco Model 942: Test Kits for 975MP Analyst and 942 Mini Analysts - With Liquid Reagents - For Phosphate and Silica Testing

- 15-410-L** - Each for \$39.30  
Reagent; Test Kit for 975MP Analyst; Orbeco; Liquid Reagents; Test: Silica, high; Range: 0-80mg/L

### Orbeco Model 942: Test Kits for 975MP Analyst and 942 Mini Analysts - With Reagent Tablets - For Phosphate and Silica Testing

- 15-410-A** - Each for \$21.23  
Reagent, Test Kit; For use with 975MP and 942 Mini Analysts; 50 tests; Test: Phosphate, low range; Range: 0-4mg/L

### Orbeco-Hellige Powder Pack and Tube Test Reagents - For Phosphate and Silica Testing



- 09-054-100** - Each for \$13.25  
Reagent, Colorimeter; Powder Pack; Silica; Citric Acid; 10mL; Pack of 100
- 09-053-250** - Each for \$18.50  
HR Acid Reagent; 10mL
- 09-053-252** - Each for \$26.75  
HR Acid Reagent; 25mL
- 09-053-253** - Each for \$17.40  
HR Citric Acid; 25mL
- 09-053-245** - Each for \$10.90  
Phosphate 3 (Orthophosphate)

- 09-054-101** - Each for \$21.25  
Phosphate 3 (Orthophosphate) set
- 09-053-269** - Each for \$46.50  
Silica set; High Range
- 09-054-104** - Each for \$40.00  
Silica set; Low Range
- 09-053-270** - Each for \$58.75  
Silica set; Ultra High Range
- 09-054-102** - Each for \$39.25  
Total Phosphate set

**Orbeco-Hellige SC400 Series Colorimeters - For Phosphate and Silica Testing**



- 09-053-283** - Each for \$320.00  
Colorimeter; Orbeco-Hellige SC400; Phosphate; Range, 0.02-3.00mg/L
- 09-053-284** - Each for \$320.00  
Silica

**Solids**

**Fisher Scientific Isotemp 500 Economy Lab Ovens**



- 13-246-506GAQ** - Each for \$897.00  
Oven, Gravity; Fisher Scientific Isotemp; Gravity convection; Economy model; Electronic controls; Capacity: 0.7 cu. ft. (19.8L); 120V 50/60Hz, 3.5A
- 13-246-507GAQ** - Each for \$921.00  
Capacity: 0.7 cu. ft. (19.8L); 230V 50/60Hz, 1.75A
- 13-246-516GAQ** - Each for \$1115.00  
Capacity: 1.7 cu. ft. (19.8L); 120V 50/60Hz, 3.5A
- 13-246-517GAQ** - Each for \$1126.00  
Capacity: 1.7 cu. ft. (19.8L); 230V 50/60Hz, 3.25A

**Fisher Scientific Isotemp Economy Vacuum Ovens**



- 13-262-280A** - Each for \$1622.00  
Oven, Vacuum; Fiser Isotemp Economy Model 280A; Capacity: 0.67 cu. ft.; Temp. range: ambient plus 10 to 200deg C; Vacuum: 0 to 30 in.Hg; Model: 280A; 120V 50/60Hz 1000w, 8.4A
- 13-262-285A** - Each for \$3505.00  
120V 50/60Hz 1700w, 14.2A

**Fisher Scientific Isotemp Model 281A Vacuum Oven**



- 13-262-50** - Each for \$3245.00  
Oven, Vacuum; Fisher Scientific Isotemp Model 281A; Capacity: 0.65 cu.ft.; Full-view window; Auto temp backup control; 120V 50/60Hz
- SPN-50430** - Each for \$169.95  
Seal Replacement Kit

**Fisher Scientific Isotemp Model 282A Vacuum Oven**



- 13-262-52** - Each for \$5907.00  
Oven, Vacuum; Fisher Scientific Isotemp; Capacity: 1.5 cu.ft.; Full-view chamber door; Self-diagnostics; 7-day programmable timer; Auto time/temp controls; 2 shelves; 115V 50/60Hz

**Fisher Scientific Isotemp Premium Lab Ovens**



- 13-247-725F** - Each for \$2415.00  
Oven; Premium Lab; Fisher Scientific Isotemp; Forced Air; 120V 60Hz, 15A, 1800w; Capacity (Chamber Volume): 2.5 cu. ft.; Model: Small; 23-1/2 L x 25-3/4 W x 26 in. H
- 13-247-737F** - Each for \$2723.00  
Forced Air; 3.75 cu. ft.
- 13-247-750F** - Each for \$3282.00  
Forced Air; 5.0 cu. ft.
- 13-247-725G** - Each for \$1958.00  
Gravity Flow; 2.5 cu. ft.
- 13-247-737G** - Each for \$2391.00  
Gravity Flow; 3.75 cu. ft.
- 13-247-750G** - Each for \$2815.00  
Gravity Flow; 5.0 cu. ft.

**Fisher Scientific Isotemp Programmable Ovens**



- 13-247-825F** - Each for \$3496.00  
Oven; Fisher Scientific Isotemp; Programmable; Chamber capacity: 2.5 cu. ft.; Model: Small; Air changes/hr.: 61; Temp. range: 50-325degC; BTU per hr.: 2650; 18L x 18W x 13-1/2 in. H; 120V 60Hz, 15A4, 1800w
- 13-247-838F** - Each for \$3937.00  
Chamber capacity: 3.75 cu. ft.
- 13-247-851F** - Each for \$4375.00  
Chamber capacity: 5.0 cu. ft.

**Fisher Scientific Isotemp Standard Lab Ovens**



- 13-247-625G** - Each for \$1486.00  
Oven, General Purpose; Fisher Scientific Isotemp; Capacity 2.5 cu. ft.; Model: Small; Temp. range 50 deg. to 225 deg. C; 1325 BTU/hr. at 200 deg. C; 24 air exchanges/hr.; 120V 60Hz, 11A, 1300w
- 13-247-637G** - Each for \$1804.00  
Model: Medium
- 13-247-650G** - Each for \$2022.00  
Model: Large

**Fisherbrand Aluminum Dishes with Fluted Sides**



- 08-732-105** - Pack of 100 for \$30.27 and Case of 10 Packs for \$258.66  
Dish, Aluminum; Fisherbrand; with Fluted Sides; Capac. 20mL
- 08-732-106** - Pack of 100 for \$38.02 and Case of 12 Packs for \$389.93  
Capacity: 60mL
- 08-732-107** - Pack of 100 for \$32.98 and Case of 10 Packs for \$281.86  
Capacity: 75mL
- 08-732-108** - Pack of 50 for \$26.35  
Capacity: 200mL
- 08-732-109** - Pack of 50 for \$40.18  
Capacity: 500mL

**Fisherbrand Aluminum Weighing Dishes**



- 08-732-100** - Pack of 100 for \$28.91 and Case of 10 Packs for \$247.11  
Dishes, Weighing; Fisherbrand; Aluminum; Capacity: 11/16 fl. oz.
- 08-732-101** - Pack of 144 for \$32.10 and Case of 56 Packs for \$1403.41  
With Fluted Sides; Capacity: 1-3/8 fl. oz.
- 08-732-102** - Pack of 100 for \$58.51 and Case of 10 Packs for \$500.02  
With Fluted Sides; Capacity: 2-7/8 fl. oz.
- 08-732-103** - Pack of 100 for \$51.05 and Case of 10 Packs for \$436.36  
With Smooth Sides; Capacity: 2-3/8 fl. oz.
- 08-732-104** - Pack of 100 for \$75.14 and Case of 10 Packs for \$664.95  
With Smooth Sides; Capacity: 5 fl. oz.

### Fisherbrand Disposable Aluminum Weighing/Drying Pans



**08-732-111** - Pack of 50 for \$28.77 and Case of 10 Packs for \$245.94

Pan, Weighing/Drying; Fisherbrand; Disposable; Aluminum; 4-1/4 in. (10.9cm) dishes with slightly fluted sides and beaded rim

**08-732-110** - Pack of 100 for \$31.96 and Case of 10 Packs for \$273.10

4-3/4 in. (12.2cm) dishes with flat tops

### Fisherbrand Hexagonal Polystyrene Weighing Dishes



**02-202-100** - Pack of 500 for \$81.25 and Case of 8 Packs for \$573.25

Dishes, Weighing; Fisherbrand; Hexagonal; Flat bottom with sloping sides; Polystyrene; For solids or liquids; I.D. Top/Base: 1-1/2 in./1 in.; Appx. Weight: 0.02 oz.

**02-202B** - Pack of 500 for \$98.00 and Case of 6 Packs for \$507.00

2-1/2 in. Top Opening; 2 in. Base

**02-202C** - Pack of 500 for \$215.00 and Case of 4 Packs for \$740.00

4 in. Top Opening; 3 in. Base

**02-202-103** - Pack of 500 for \$273.33 and Case of 4 Packs for \$934.44

5 in. Top Opening; 3-1/2 in. Base

### Fisherbrand Low Nitrogen Weighing Paper



**09-898-12A** - Pack of 500 for \$24.72 and Case of 12 Packs for \$253.49

Paper, Weighing; Fisherbrand; Low nitrogen; Sufficient body to support sample; Does not absorb moisture; 3 x 3 in. (76 x 76mm); 500 sheets per pack

**09-898-12B** - Pack of 500 for \$24.03 and Case of 12 Packs for \$246.46

4 x 4 in.

**09-898-12C** - Pack of 500 for \$25.50 and Case of 12 Packs for \$236.34

6 x 6 in.

### Fisherbrand Polystyrene Antistatic Weighing Dishes



**08-732-116** - Pack of 250 for \$73.67 and Case of 8 Packs for \$521.57

Dish; Weighing; Fisherbrand; Anti-Static; 12mil thick Polystyrene; Pour Boat; 1-5/8 L x 1-1/4 W x 5/16 in. H; Natural; disposable; flat bottom

**08-732-117** - Case of 250 for \$107.05

Pour Boat; 3-1/2 L x 5-1/4 W x 1 in. H; Natural

**08-732-118** - Case of 250 for \$150.30

Pour Boat; 4-3/4 L x 7-3/4 W x 1 in. H; Natural

**08-732-112** - Pack of 500 for \$75.95 and Case of 8 Packs for \$537.20

Standard Style; 1-5/8 L x 1-5/8 W x 5/16 in. H; Natural

**08-732-114** - Case of 500 for \$94.66

Standard style; 3-1/2 L x 3-1/2 W x 1 in. H; Blue

**08-732-113** - Case of 500 for \$83.37

Standard style; 3-1/2 L x 3-1/2 W x 1 in. H; Natural

**08-732-115** - Case of 500 for \$164.23

Standard style; 5-1/2 L x 5-1/2 W x 1 in. H; Blue

### Fisherbrand Polystyrene Beakers



**08-732-119** - Pack of 1000 for \$81.20 and Case of 20 Packs for \$1437.25

Beaker, Polystyrene; Fisherbrand; Disposable; Can be used in atomic absorption spectroscopy and flame photometry; 100 per cardboard sleeve; Capacity: 5mL

**08-732-121** - Pack of 1000 for \$128.60 and Case of 16 Packs for \$1758.59

Capacity: 10mL

**08-732-120** - Pack of 500 for \$117.86 and Case of 18 Packs for \$1813.28

Capacity: 20mL

**08-732-122** - Pack of 500 for \$158.84 and Case of 12 Packs for \$1629.14

Capacity: 50mL

### Fisherbrand Weighing Funnels



**14-353B** - Pack of 5 for \$62.74

Funnel, Weighing; Fisherbrand; Borosilicate glass; Tapered pouring necks; Flat Bottom; Diameter x L: 15 x 40mm

**14-353D** - Pack of 5 for \$74.14

Tapered pouring necks; Flat Bottom; Diameter x L: 25 x 55mm

**14-353F** - Pack of 5 for \$82.20

Pack of 1 Each (10 x 35mm, 15 x 40mm, 20 x 45mm, 25 x 55mm and 32 x 68mm)

### CoorsTek Porcelain Casserole Evaporating Dishes



**04-695B** - Each for \$16.40 and Case of 12 for \$171.08  
Dish, Evaporating; CoorsTek; Porcelain; Casserole-shaped; Diameter: 43mm; Capacity: 20mL

**04-695D** - Each for \$20.66 and Case of 12 for \$211.94  
Diameter: 70mm; Capacity: 60mL

**04-695E** - Each for \$26.72 and Case of 12 for \$278.79  
Diameter: 89mm; Capacity: 140mL

**04-695F** - Each for \$32.18 and Case of 12 for \$330.07  
Diameter: 100mm; Capacity: 210mL

**04-695H** - Each for \$51.53 and Case of 6 for \$268.83

Diameter: 133mm; Capacity: 500mL

**04-695J** - Each for \$65.42 and Case of 4 for \$231.59

Diameter: 144mm; Capacity: 750mL

**04-695K** - Each for \$85.19 and Case of 4 for \$301.55

Diameter: 174mm; Capacity: 1200mL

### CoorsTek Porcelain Evaporating Dishes



**08-690A** - Each for \$10.45 and Case of 48 for \$401.24  
Dish, Evaporating; CoorsTek; Porcelain; Round bottoms; With pour-out spouts; Diameter: 60mm; Capacity: 35mL

**08-690B** - Each for \$10.84 and Case of 48 for \$416.40  
Diameter: 75mm; Capacity: 70mL

**08-690C** - Each for \$11.88 and Case of 24 for \$228.07  
Diameter: 80mm; Capacity: 80mL

**08-690E** - Each for \$14.85 and Case of 24 for \$285.16  
Diameter: 94mm; Capacity: 120mL

**08-690F** - Each for \$16.19 and Case of 18 for \$249.02  
Diameter: 100mm; Capacity: 150mL

**08-690G** - Each for \$19.38 and Case of 18 for \$298.11  
Diameter: 115mm; Capacity: 250mL

**08-690J** - Each for \$37.72 and Case of 12 for \$386.92  
Diameter: 145mm; Capacity: 385mL

**08-690K** - Each for \$53.95 and Case of 12 for \$553.34  
Diameter: 162mm; Capacity: 525mL

**08-690L** - Each for \$73.81 and Case of 8 for \$522.52  
Diameter: 185mm; Capacity: 765mL

**08-690M** - Each for \$105.28 and Case of 6 for \$559.00  
Diameter: 215mm; Capacity: 1285mL

**08-690P** - Each for \$143.72 and Case of 4 for \$491.35  
Diameter: 265mm; Capacity: 2100mL

**08-690Q** - Each for \$165.71 and Case of 3 for \$424.89  
Diameter: 305mm; Capacity: 3250mL

### CoorsTek Shallow-Form Porcelain Evaporating Dishes



**08-693A** - Each for \$12.72 and Case of 24 for \$244.16  
Dish, Evaporating; CoorsTek; Porcelain; Shallow-Form; Diameter: 70mm; Capacity: 30mL

**08-693B** - Each for \$13.04 and Case of 24 for \$250.46  
Diameter: 80mm; Capacity: 50mL

**08-693C** - Each for \$14.92 and Case of 18 for \$229.56  
Diameter: 90mm; Capacity: 75mL

**08-693H** - Each for \$16.01 and Case of 18 for \$246.30  
Diameter: 105mm; Capacity: 100mL

**08-693D** - Each for \$19.37 and Case of 12 for \$198.70  
Diameter: 120mm; Capacity: 195mL

**08-693F** - Each for \$34.88 and Case of 8 for \$238.50  
Diameter: 160mm; Capacity: 290mL

### Corning Vycor Evaporating Dishes



**08-708A** - Each for \$104.92 and Case of 12 for \$879.64  
Dish, Evaporating; Vycor; Glass; High thermal and chemical resistance; Comprised of 96% silica; Flat bottom; Pour-out spout; Withstand temperatures to 900 deg. C (1652 deg. F); Diameter: 70mm; Capacity: 45mL

**08-708B** - Each for \$163.92 and Case of 8 for \$927.52  
Diameter: 90mm; Capacity: 100mL

**Denver Instrument Infrared Moisture Analyzer Disposable Foil Sample Dishes**

**01-913-356** - Pack of 50 for \$42.44  
Sample Dishes; Disposable Foil; for Denver Instrument Infrared Moisture Analyzer

**Denver Instrument Infrared Moisture Analyzer Glass Fiber Sample Pads**

**01-913-358** - Pack of 200 for \$40.94  
Pad, Sample, Glass Fiber, Use With High Moisture Content Samples, For Denver Ir-200 Infrared Moisture Analyzer 3-1/2 In. (90Mm) Dia

**Denver Instrument IR-120 Moisture Analyzer**



**01-913-440** - Each for \$5227.50  
Analyzer, Moisture; Denver Instrument IR-120; Quartz coil infrared heating element; Single-block weighing w/0.001g resolution; Range: 0.1-99.9%; Temp: 30-210 deg. C/1 deg. C increment; Weigh/Tare: 0-120g; 18x13-13/16x6 in.; 115/230V 50/60Hz

**Denver Instrument IR-35 Moisture Analyzer**



**01-915-00** - Each for \$2728.50  
Moisture Analyzer; Denver Instrument; Fast; Easy to operate; IR-35; 115V

**Denver Instrument IR-60 Moisture Analyzer**



**01-914-270** - Each for \$3391.50  
Analyzer, Moisture; Denver Instrument IR-60; Quartz coil infrared heating element; Single-block weighing w/0.001g resolution; Temp Steps: 1; Temp: 40-210 deg. C/1 deg. C increment; Weigh/Tare: 0-60g; 12-5/8x8-3/8x7-1/8 in.; 115/230V 50/60Hz

**Mettler Toledo Halogen Moisture Analyzer Built-in Printer**



**01-909-382** - Each for \$585.00  
Printer; Halogen; Mettler Toledo; For Mettler HR83 and HG63 Moisture Analyzers; Provides documentation of measured values to meet GLP and GMP guidelines

**Mettler Toledo Halogen Moisture Analyzer Glass Fiber Discs**

**01-909-422** - Each for \$75.00  
Glass Fiber Discs; For use with Mettler Toledo Halogen Moisture Analyzer; 3-1/2 in. dia.

**Mettler Toledo Halogen Moisture Analyzer Sample Pan Handlers**

**01-914-15** - Each for \$34.34  
Handler, Sample Pan; Halogen; Mettler Toledo; Stainless steel; Set of 3

**Mettler Toledo Halogen Moisture Analyzer Temperature Calibration Kits**

**01-909-385A** - Each for \$563.00  
Kits; Calibration; Halogen Moisture Analyzer Temperature; Mettler Toledo; With NIST certificate  
**01-909-385** - Each for \$278.00  
Without Certificate

**Mettler Toledo HB43-S Compact Halogen Moisture Analyzer**



**01-910-100** - Each for \$3379.00  
Balance; Moisture Analyzer; HB43-S; Analytical; Compact; Uniform heating; Large keys; Rugged; Easy to clean; Switchable drying methods; Methods library for over 100 substances; Max Sample Weight: 54g; Readability: 1mg

**Mettler Toledo HR83 and HG63 Halogen Moisture Analyzers**



**01910330** - Each for \$4839.00  
Analyzer, Halogen Moisture; Mettler Toledo HR83; 81g capacity x 1mg; Measurement Values: 0.01%; Balance: 1mg; Temp Range: 40-200 deg. C; 2 drying programs; Increments: 1 deg. C; Memory: 10 samples; 110V 50/60Hz  
**01910331** - Each for \$5306.00  
2 drying programs; with Printer; Memory: 10 samples  
**01-910-328** - Each for \$6065.00  
4 drying programs; Memory: 40 samples  
**01910329** - Each for \$6547.00  
4 drying programs; with printer; Memory: 40 samples

**Mettler Toledo LabX Software for Moisture Analyzers**

**01-919-700** - Each for \$510.00  
Software; LabX; Direct Moisture; Automatically transfers measurement data into Excel; For Use With: Mettler Toledo moisture analyzers; Reads IDs with barcode reader; Visualizes drying curves

**Mettler Toledo Moisture Analyzer Sample Pans**

**01-909-427** - Each for \$69.00  
Sample Pans; for halogen moisture analyzers; Stainless chrome-nickel steel; Diameter: 3-1/2 in.  
**01-913-97B** - Each for \$21.00  
For LJ16 Infrared Moisture Analyzer; Stainless Steel  
**01-913-97A** - Pack of 50 for \$52.00  
Sample Pans; for Mettler LJ16 Moisture Analyzer; Aluminum


**Nalgene Plastic Settrometer Kit**



**15-443-35** - Each for \$197.99 and Case of 4 for \$528.00  
Kit, Plastic Settrometer; Nalgene; Includes: polycarbonate jar w/cover, polypropylene paddle, ten 15mL polycarbonate conical centrifuge tubes w/friction-fit polypropylene closures, an instruction booklet and data sheet



### Nalgene Polycarbonate Imhoff Settling Cone and Rack



**15-438** - Each for \$42.85 and Case of 4 for \$114.25  
Settling Cone; Imhoff; Nalgene; Molded acrylic; For wastewater testing; Graduated from 0 to 1L; Increments; Closure: 13mm Leakproof screw cap; Top Dia.: 4-3/16 in.  
**15-443-60** - Each for \$183.00 and Case of 4 for \$488.00  
Dimensions: 7-3/4L x 16W x 14-1/2 in.H

### Ohaus MB Series Moisture Analyzers



**01-920-115** - Each for \$2750.00  
BBalances, Moisture Analyzer; Ohaus; Model MB35; Weighing range: 0-35g; Moisture range: 0.05-100%; Temp. range: 50-160 deg. C; Timer: 1-120 min.; Halogen heat source w/reflective housing; GLP compliant format; RS 232 port  
**01-920-62** - Each for \$3350.00  
Weighing range: 0-45g

### Pyrex Direct-Reading Mallory Settler



**15-443-30** - Case of 1 for \$196.63  
Settler, Mallory; Pyrex; Direct-Reading; Measures 51/8 I.D. x 71/2 in.H (13 x 19cm); Graduated in cc per liter and hundredths of a foot; Heavy-wall cylinder; 2000mL

### Pyrex Evaporating Dishes



**08-710A** - Case of 6 for \$64.63  
Dish, Evaporating; Pyrex; Glass; Withstand temperatures to 230 deg. C (446 deg. F); Beaded rim; Flat bottom; Medium depth; With pouring spout; Diameter: 80mm; Capacity: 140mL  
**08-710B** - Case of 6 for \$73.39  
Diameter: 90mm; Capacity: 170mL  
**08-710C** - Case of 6 for \$206.00  
Diameter: 105mm; Capacity: 290mL

### Pyrex Glass Imhoff Cone



**15-441** - Case of 4 for \$1134.15  
Cone, Imhoff; Pyrex; 439mm; Blunt Tip  
**15-439** - Case of 2 for \$985.76  
Cone 454mm

### Thermo Scientific Lindberg/Blue M Economy Gravity Convection Ovens




**13-258-30A** - Each for \$1450.00  
Oven, Gravity Convection; Thermo Scientific Lindberg/Blue M; 1 cu. ft. capacity; Temp. range 40 to 220 deg. C; Digital control; w/2 shelves; 17-1/2L x 21W x 23-1/2 in.H; 120V 50/60Hz, 550w; Not for use w/ hazardous vapors  
**13-258-30C** - Each for \$1650.00  
2 cu. ft.; 120V 50/60Hz, 550w

### Thermo Scientific Lindberg/Blue M Gravity Convection Ovens



**13-258-14** - Each for \$1979.00  
Oven, Gravity Convection; Thermo Scientific Lindberg/Blue M; 1.0 cu. ft.; Painted Steel; Deluxe series; 120V, 50/60Hz, 5.4A, 900w  
**13-258-14B** - Each for \$2403.00  
2.1 cu. ft.; Painted Steel; Deluxe series; 120V, 50/60Hz, 10.8A, 1000w  
**13-258-14D** - Each for \$2827.00  
3.0 cu. ft.; Painted Steel; Deluxe series; 120V, 50/60Hz, 15.8A, 1300w  
**13-258-34** - Each for \$2047.00  
3.0 cu. ft.; Painted Steel; General Purpose series; 120V, 50/60Hz, 14A, 1600w  
**13-258-33** - Each for \$2047.00  
3.0 cu. ft.; Painted Steel; General Purpose series; 208/240V, 50/60Hz, 7A, 1600w  
**13-258-14H** - Each for \$3141.00  
4.5 cu. ft.; Painted Steel; Deluxe series; 120V, 50/60Hz, 10.8A, 1900w  
**13-258-14J** - Each for \$3141.00  
4.5 cu. ft.; Painted Steel; Deluxe series; 208/240V, 50/60Hz, 8.75A, 1900w  
**13-258-14M** - Each for \$3390.00  
7.0 cu. ft.; Painted Steel; Deluxe series; 120V, 50/60Hz, 10.8A, 2100w  
**13-258-14N** - Each for \$3390.00  
7.0 cu. ft.; Painted Steel; Deluxe series; 208/240V, 50/60Hz, 8.75A, 2100w

### Thermo Scientific Lindberg/Blue M Mechanical Convection Ovens



**13-258-15A** - Each for \$3299.00  
Oven, Mechanical Convection; Thermo Scientific Lindberg/Blue M; 1.2 cu. ft.; Deluxe series; 5 shelf positions; Stainless steel exterior; 120V 50/60Hz; 7A, 1600w  
**13-258-15B** - Each for \$3081.00  
1.2 cu. ft.; Deluxe series; 7 shelf positions; Painted steel exterior; 120V, 50/60Hz, 20A, 1600w  
**13-258-15D** - Each for \$3280.00  
3.0 cu. ft.; Deluxe Series; 7 shelf positions; Painted steel exterior; 120V, 50/60Hz, 10.3A, 1300w  
**13-258-15F** - Each for \$3280.00  
3.0 cu. ft.; Deluxe Series; 7 shelf positions; Painted steel exterior; 208/240V, 50/60Hz, 7.9A, 1900w  
**13-258-15E** - Each for \$4039.00  
3.0 cu. ft.; Deluxe Series; 7 shelf positions; Stainless steel exterior; 120V, 50/60Hz, 10.3A, 1300w  
**10-549-212** - Each for \$2704.00  
3.0 cu. ft.; General purpose; 16 shelf positions; Painted steel exterior; 120V 50/60Hz; 20A, 1600w  
**10-549-213** - Each for \$3403.00  
3.0 cu. ft.; General purpose; 16 shelf positions; Stainless steel exterior; 120V, 50/60Hz, 20A, 1600w  
**10-549-215** - Each for \$3403.00  
3.0 cu. ft.; General purpose; 16 shelf positions; Stainless steel exterior; 208/240V, 50/60Hz, 20A, 1600w  
**13-258-15H** - Each for \$3484.00  
4.9 cu. ft.; Deluxe series; 12 shelf positions; Painted steel exterior; 120V, 50/60Hz, 17.5A, 2100w  
**13-258-15K** - Each for \$3484.00  
4.9 cu. ft.; Deluxe series; 12 shelf positions; Painted steel exterior; 208/240V, 50/60Hz, 8.75A, 2100w  
**13-258-15J** - Each for \$4306.00  
4.9 cu. ft.; Deluxe series; 12 shelf positions; Stainless steel exterior; 120V, 50/60Hz, 17.5A, 2100w

Thermo Scientific Lindberg/Blue M Vacuum Ovens



- 13-258-13** - Each for \$3090.00  
Oven, Vacuum; Thermo Scientific Lindberg/Blue M; Max temp: 260 deg. C; Digital microprocessor control; LED of setpoint/actual temperature; overtemperature safety feature; 0.65 cu. ft.; Painted Steel; 120V 50/60Hz, 750w
- 10-549-223** - Each for \$3090.00  
0.65 cu. ft.; Painted Steel; 208/240V 50/60Hz, 750w
- 13-258-13B** - Each for \$5480.00  
1.5 cu. ft.; Painted Steel; 120V 50/60Hz, 1250w
- 10-549-224** - Each for \$5480.00  
1.5 cu. ft.; Painted Steel; 208/240V 50/60Hz, 1250w
- 10-549-227** - Each for \$12176.00  
4.5 cu. ft.; Painted Steel; 120V 50/60Hz, 1500w
- 10-549-225** - Each for \$12176.00  
4.5 cu. ft.; Painted Steel; 208/240V 50/60Hz, 7100w

Thermo Scientific Napco Vacuum Ovens



- 13-262-1** - Each for \$1569.00  
Oven, Lab; Thermo Scientific Napco; Capacity: 0.45 cu. ft.; Chamber Dimensions: 12 x 8 x 8 in.; 120V 50/60Hz, 4.2A, 500w
- 13-262-2** - Each for \$2135.00  
0.45 cu. ft.; 230V 50/60Hz, 2.1A, 500w
- 13-262-12** - Each for \$3862.00  
1.6 cu. ft.; 120V 50/60Hz, 8.3A, 1000w
- 13-262-25A** - Each for \$7732.00  
4.5 cu. ft.; 120V 50/60Hz, 12.5A, 1500w

Thermo Scientific Oven/Incubator



- 13-261-40** - Each for \$1087.00  
Oven/Incubator; Thermo Scientific; Capacity: 1 cu. ft.; Heats to 56 deg. C in 9 minutes; Uniformity: +/-1.25 deg. at 37 deg. C; Bimetallic thermostat controls temperature, from ambient to 140 deg. C +/-1 deg. C

Thermo Scientific Precision All-Purpose Laboratory Ovens



- 13-254-1** - Each for \$1491.00  
Oven, Laboratory; Thermo Scientific Precision; All-Purpose; Temperature control to 250 deg. C; Built-in timer; Electronic Temperature Control; 2.5 cu. ft.; 115V 50/60Hz, 10.4A, 1200w
- 13-254-2** - Each for \$1995.00  
Electronic Control; 2.5 cu. ft.; 230V 50/60Hz, 5.2A, 1300w
- 13-254-3** - Each for \$1811.00  
Electronic Control; 4.5 cu. ft.; 115V 50/60Hz, 14.8A, 1700w
- 13-254-4** - Each for \$2113.48  
Electronic Control; 4.5 cu. ft.; 230V 50/60Hz, 7.4A, 1700w
- 13-254-5** - Each for \$2670.00  
Electronic Control; 5.5 cu. ft.; 230V 50/60Hz, 8.7A, 2000w
- 13-254-6** - Each for \$1871.00  
Microprocessor Control; 2.5 cu. ft.; 115V 50/60Hz, 10.4A, 1200w
- 13-254-8** - Each for \$2322.01  
Microprocessor Control; 4.5 cu. ft.; 115V 50/60Hz, 14.8A, 1700w
- 13-254-10** - Each for \$2970.00  
Microprocessor Control; 5.5 cu. ft.; 230V 50/60Hz, 8.7A, 2000w

Thermo Scientific Precision All-Purpose Mechanical Convection Ovens



- 13-254-11** - Each for \$1916.30  
Oven, Mechanical Convection; Thermo Scientific Precision; Electronic temperature control to 250 deg. C; Capacity: 2.5 cu. ft.; 115V 50/60Hz, 11.3A, 1300w
- 13-254-16** - Each for \$2308.00  
2.5 cu. ft.; 115V 50/60Hz, 11.3A, 1300w; Microprocessor Control
- 13-254-13** - Each for \$2370.21  
4.5 cu. ft.; 115V 50/60Hz, 15.6A, 1800w; Electronic Control
- 13-254-18** - Each for \$2696.00  
4.5 cu. ft.; 115V 50/60Hz, 15.6A, 1800w; Microprocessor Control
- 13-254-19** - Each for \$2970.00  
4.5 cu. ft.; 230V 50/60Hz, 7.8A, 1800w; Microprocessor Control
- 13-254-20** - Each for \$3418.00  
5.5 cu. ft.; 230V 50/60Hz, 9.1A, 2100w; Microprocessor Control

Thermo Scientific Precision Economy Lab Ovens



- 13-264F** - Each for \$1216.00  
Oven, Convection; Precision; Thermo Scientific; Includes: Two corrosion-resistant, nontip, nickel-plated shelves, vent cap, thermometer, line cord, and plug; Capacity: 1.4 cu. ft.; Type: Gravity Convection; 230V 115V 50/60Hz, 7.1A, 800w
- 13-264G** - Each for \$1287.00  
Capacity: 1.4 cu. ft.; Type: Gravity Convection; 230V 50/60Hz, 3.5A, 800w
- 13-254-25** - Each for \$1296.00  
Capacity: 2.5 cu. ft.; Type: Gravity Convection; 115V 50/60Hz, 10.4A, 1200w
- 13-254-24** - Each for \$1333.00  
Capacity: 2.5 cu. ft.; Type: Gravity Convection; 230V 50/60Hz, 5.6A, 1300w
- 13-254-21** - Each for \$1783.00  
Capacity: 2.5 cu. ft.; Type: Mechanical Convection; 115V 50/60Hz, 11.3A, 1300w
- 13-254-26** - Each for \$1927.00  
Capacity: 2.5 cu. ft.; Type: Mechanical Convection; 230V 50/60Hz, 5.6A, 1300w
- 13-254-22** - Each for \$1699.00  
Capacity: 4.5 cu. ft.; Type: Gravity Convection; 115V 50/60Hz, 15.6A, 1800w
- 13-254-23** - Each for \$1836.00  
Capacity: 4.5 cu. ft.; Type: Gravity Convection; 230V 50/60Hz, 7.8A, 1800w
- 13-254-27** - Each for \$2047.00  
Capacity: 4.5 cu. ft., Type: Mechanical Convection; 115V 50/60Hz, 15.6A, 1800w
- 13-254-28** - Each for \$2132.00  
Capacity: 4.5 cu. ft.; Type: Mechanical Convection; 230V 50/60Hz, 7.8A, 1800w

Thermo Scientific Precision Heavy-Duty Deluxe Ovens



- 13-248A** - Each for \$6062.39  
Ovens, Deluxe, Heavy-Duty; Thermo Scientific Precision; Electrical Requirements: 120V 60Hz; Chamber Volume: 1.4 cu. ft.; Precision Scientific No.: 0.03m3; Model: 605; Includes: Two nickel-plated nontip shelves
- 13-248B** - Each for \$7747.00  
4.0 cubic ft.
- 13-248C** - Each for \$9784.00  
10.2 Cubicft.

Thermo Scientific Precision Lab Oven



- 13-254-29** - Each for \$1081.00  
Oven, General Purpose; Precision Econotherm; Capacity 2.5 cu. ft.; Analog temp. control to 200 deg. C; Exterior 21-1/2L x 24W x 40 in.H; Chamber 15-1/2L x 18-1/2W x 27 in.H; 115V 50/60Hz, 15.6A, 1800w; NEMA 5-20P plug

## Thermo Scientific Precision Vacuum Ovens



**13-264A** - Each for \$1569.00  
Oven, Vacuum; Precision; Thermo Scientific;  
Temperature range: 35 to 200 deg. C; 600w; Capacity:  
0.45 cu. ft.; 120V, 50/60Hz, 5.0A  
**13-264B** - Each for \$3670.01  
1600w; Capacity: 1.6 cu. ft.; 120V, 50/60Hz, 13.3A  
**13-264C** - Each for \$3996.00  
1600w; Capacity: 1.6 cu. ft.; 240V, 50/60Hz, 6.9A

## Wheaton Plastic Imhoff Cone



**02-927-011** - Each for \$34.87 and Case of 4 for \$119.20  
Cone, Imhoff; Borosilicate glass, Conical interior, 5.0mL,  
20mm dia. 65mm H, 20-400 screw top, With -lined solid  
top caps, Clear

## Sulfide

### CHEMetrics Chemets Self-Filling Ampules - For Sulfide Testing



**13-299-258** - Pack of 1 for \$57.84  
Kit, Test; Chemets; CHEMetrics; Provide results in two  
minutes or less; Analyte: Sulfide; Testing Range: 0-1 and  
1-10ppm; Analytical Method: Methylene Blue; Complete  
Test Kit  
**13-299-508M** - Pack of 30 for \$24.60  
Sulfide; Testing Range: 0-1 and 1-10ppm; Analytical  
Method: Methylene Blue; Refil Ampule

### EM Science Quant Test Strips - For Sulfide Testing



**M100191** - Pack of 100 for \$54.20  
Testing Supplies; Water Quality; Strips; Test; EM Quant;  
Test: Sulfate; Range: 200 to 1600ppm; Ready-to-use;  
Detection chemicals, buffers, masking agents, stabilizers  
are incorporated; Supplied in sturdy aluminum cylinders  
**M100131** - Pack of 100 for \$53.95  
Test: Sulfite; Range: 10 to 400ppm

### LaMotte Series 1200 Colorimeter Single-Test Kits - For Sulfide Testing



**22-307-862** - Each for \$125.00  
Colorimeter; Series 1200; LaMotte; Single-parameter;  
Water-resistant, handheld single-parameter meters;  
Analyte: Sulfide; Range (ppm): 1 drop = 1.0 or 0.1;  
Method: Total, Dissolved Hydrogen Sulfide Dropper Pipet

### Orbeco Model 942: Test Kits for 975MP Analyst and 942 Mini Analysts - With Reagent Tablets - For Sulfide Testing

**15-399-F** - Each for \$26.65  
Reagent, Test Kit; For use with 975MP and 942 Mini Analysts; 50 tests; Test:  
Sulfite; Range: 0-500mg/L

### Orbeco-Hellige Powder Pack and Tube Test Reagents - For Sulfide Testing



**09-053-254** - Each for \$21.25  
Reagent, Colorimeter; Powder Pack; Silica; Ultra High  
Range; HR Molybdate; 25mL; Pack of 100  
**09-053-256** - Each for \$20.25  
Sulfate 4; 10mL  
**09-053-255** - Each for \$21.25  
Sulfate 4; 25mL


## Temperature

### Fisherbrand Blue-Spirit Ever-Safe 8-inch Thermometers



**15-160-34** - Each for \$18.25  
Thermometer; Fisherbrand; Ever-Safe; 8-inch; 50mm  
Immersion; -10 to +110 deg. C  
**15-160-36** - Each for \$18.25  
50mm Immersion; -10 to +150 deg. C  
**15-160-33** - Each for \$18.63  
Total Immersion; -10 to +110 deg. C  
**15-160-35** - Each for \$18.48  
Total Immersion; -10 to +150 deg. C

### Fisherbrand Blue-Spirit Ever-Safe Laboratory Thermometers



**15-171-10** - Each for \$47.42  
Thermometer; Ever-Safe; Fisherbrand; Blue-Spirit;  
Permanently fused markings for long-term use; Fractional  
Degree/Partial Immersion; Range: -10 to +50 deg. C  
**15-160-14** - Each for \$82.76  
Fractional Degree/Partial Immersion; Range: -1 to +51  
deg. C  
**15-160-16** - Each for \$103.30  
Fractional Degree/Partial Immersion; Range: -1 to +101  
deg. C  
**15-160-18** - Each for \$111.40  
Fractional Degree/Partial Immersion; Range: -1 to +201  
deg. C  
**15-171-11** - Each for \$43.40  
Fractional Degree/Total Immersion; Range: -10 to +50  
deg. C  
**15-160-13** - Each for \$82.93  
Fractional Degree/Total Immersion; Range: -1 to +51 deg.  
C  
**15-160-15** - Each for \$104.32  
Fractional Degree/Total Immersion; Range: -1 to +101  
deg. C  
**15-160-17** - Each for \$111.08  
Fractional Degree/Total Immersion; Range: -1 to +201  
deg. C  
**15-160-30** - Each for \$19.41  
Partial Immersion; Range: -35 to +50 deg. C  
**15-160-20** - Each for \$16.62  
Partial Immersion; Range: -20 to +110 deg. C  
**15-160-22** - Each for \$18.95  
Partial Immersion; Range: -20 to +150 deg. C  
**15-160-26** - Each for \$31.55  
Partial Immersion; Range: -10 to +260 deg. C  
**15-160-25** - Each for \$17.11  
Partial Immersion; Range: 0 to 230 deg. F  
**15-160-28** - Each for \$19.41  
Partial Immersion; Range: 0 to 300 deg. F  
**15-160-32** - Each for \$33.50  
Partial Immersion; Range: 20 to +500 deg. F  
**15-160-29** - Each for \$19.63  
Total Immersion; Range: -35 to +50 deg. C  
**15-160-19** - Each for \$16.82  
Total Immersion; Range: -20 to +110 deg. C  
**15-160-21** - Each for \$19.17  
Total Immersion; Range: -20 to +150 deg. C  
**15-160-23** - Each for \$27.63  
Total Immersion; Range: -10 to +210 deg. C  
**15-160-24** - Each for \$17.32  
Total Immersion; Range: 0 to 230 deg. F  
**15-160-27** - Each for \$19.63  
Total Immersion; Range: 0 to 300 deg. F

### Fisherbrand Petri Dishes with Clear Lids



**08-757-13** - Case of 500 for \$150.05  
Dish, Petri; Fisherbrand; Clear Lid; Radiation-sterilized;  
Polystyrene; Beveled Ridge; 100 O.D. x 15mm H;  
Edges are square; Three venting ribs in lid; Stackable;  
Disposable  
**08-757-14** - Case of 100 for \$152.35  
Beveled Ridge; 150 Dia. x 15mmH  
**08-757-12** - Case of 500 for \$150.05  
Raised Ridge; 100 O.D. x 15mm H

### Fisherbrand Red-Spirit Deep-Immersion Thermometers



- 15-041-6A** - Each for \$57.99  
Thermometer, Deep-Immersion; Fisherbrand; Red-Spirit; Graduated in 1 deg. C divisions; Range: -100 to +50 deg. C; Length: 380mm; Immersion: 152mm
- 15-041-7A** - Each for \$59.02  
Range: -100 to +50 deg. C; Length: 457mm; Immersion: 225mm
- 15-041-8A** - Each for \$58.00  
Range: -100 to +50 deg. C; Length: 533mm; Immersion: 305mm
- 15-041-6B** - Each for \$44.99  
Range: -50 to +50 deg. C; Length: 380mm; Immersion: 152mm
- 15-041-7B** - Each for \$51.01  
Range: -50 to +50 deg. C; Length: 457mm; Immersion: 225mm
- 15-041-8B** - Each for \$56.00  
Range: -50 to +50 deg. C; Length: 533mm; Immersion: 305mm
- 15-041-6C** - Each for \$47.01  
Range: -20 to +150 deg. C; Length: 380mm; Immersion: 152mm
- 15-041-7C** - Each for \$47.00  
Range: -20 to +150 deg. C; Length: 457mm; Immersion: 225mm
- 15-041-8C** - Each for \$50.00  
Range: -20 to +150 deg. C; Length: 533mm; Immersion: 305mm
- 15-041-9A** - Each for \$90.99  
Range: -20 to +150 deg. C; Length: 685mm; Immersion: 457mm
- 15-041-6D** - Each for \$49.99  
Range: -10 to +250 deg. C; Length: 457mm; Immersion: 152mm
- 15-041-7D** - Each for \$51.00  
Range: -10 to +250 deg. C; Length: 533mm; Immersion: 225mm
- 15-041-8D** - Each for \$54.00  
Range: -10 to +250 deg. C; Length: 610mm; Immersion: 305mm
- 15-041-9B** - Each for \$93.01  
Range: -10 to +250 deg. C; Length: 762mm; Immersion: 457mm

### Fisherbrand Red-Spirit Fluoropolymer-Coated Laboratory Thermometers



- 14-983-19A** - Each for \$34.00  
Thermometer, Red-Spirit; Fisherbrand; Fluoropolymer-Coated; Range: -20 to +110 deg. C
- 14-983-19B** - Each for \$34.02  
Range: -20 to +150 deg. C
- 14-983-25A** - Each for \$34.00  
Range: 0 to +230 deg. F
- 14-983-25B** - Each for \$34.02  
Range: 0 to +300 deg. F

### Fisherbrand Red-Spirit General-Purpose Laboratory Thermometers



- 15-035** - Each for \$59.02  
Thermometer, Red-Spirit; Fisherbrand; General-Purpose; High Range: +50 deg. C; Length: 305mm; Low Range: -100 deg. C; Partial Immersion
- 15-041-4B** - Each for \$31.99  
Partial Immersion; Range: +50 deg. C to -50 deg. C
- 15-041-4D** - Each for \$24.03  
Partial Immersion; Range: +150 deg. C to -20 deg. C
- 15-041-4E** - Each for \$36.96  
Partial Immersion; Range: +200 deg. C to -10 deg. C
- 15-041-4F** - Each for \$45.98  
Partial Immersion; Range: +260 deg. C to -10 deg. C
- 15-038** - Each for \$104.01  
Total Immersion; Range: +30 deg. C to -200 deg. C
- 15-041-5A** - Each for \$48.99  
Total Immersion; Range: +50 deg. C to -100 deg. C
- 15-041-5C** - Each for \$24.98  
Total Immersion; Range: +110 deg. C to -20 deg. C
- 15-041-5D** - Each for \$24.03  
Total Immersion; Range: +150 deg. C to -20 deg. C
- 15-041-5E** - Each for \$36.04  
Total Immersion; Range: +200 deg. C to -10 deg. C

- 15-169-201** - Each for \$36.70  
Total Immersion; Range: -55 deg. C to +50 deg. C

### Fisherbrand Red-Spirit No-Roll Laboratory Thermometers



- 14-998** - Each for \$11.02  
Thermometers; Fisherbrand Red-Spirit No-Roll; Length: 305mm; High Range: +230 deg. F; Low Range: 0 deg. F
- 14-997** - Each for \$11.02  
Range: -20 deg. C to +110 deg. C; 305mm L; Immersion: 76mm; Subdiv.: 1 deg. C

### Fisherbrand Red-Spirit Variable-Immersion Thermometers



- 15-041-10A** - Each for \$84.99  
Thermometer, Red-Spirit; Fisherbrand; Variable-Immersion; Range: -100 to +50 deg. C; Length: 482mm; Immersion: 76 - 178mm
- 15-041-10G** - Each for \$142.98  
Range: -100 to +50 deg. C; Length: 774mm; Immersion: 305 - 457mm
- 15-041-10B** - Each for \$68.02  
Range: -20 to +150 deg. C; Length: 482mm; Immersion: 76 - 178mm; Contains mercury
- 15-041-10E** - Each for \$75.00  
Range: -20 to +150 deg. C; Length: 635mm; Immersion: 178 - 305mm
- 15-041-10C** - Each for \$72.00  
Range: -10 to +250 deg. C; Length: 482mm; Immersion: 76 - 178mm; Contains mercury
- 15-041-10F** - Each for \$79.99  
Range: -10 to +250 deg. C; Length: 635mm; Immersion: 178 - 305mm
- 15-041-10J** - Each for \$107.00  
Range: -10 to +250 deg. C; Length: 774mm; Immersion: 305 - 457mm

## Turbidity

### GFS Chemicals Amco Clear Individual Primary Turbidity Standards

- 15-426-64** - Each for \$98.74  
Turbidity Standard; Primary; Amco Clear; 0.1 NTU; Specific Gravity 1.000; 1L Bottle
- 15-426-1** - Each for \$102.98  
0.2 NTU, 1L
- 15-426-2** - Each for \$104.19  
0.5 NTU, 1L
- 15-426-3** - Each for \$97.53  
1.0 NTU Value
- 15-426-41** - Each for \$124.90  
1.8 NTU, 1L
- 15-426-4** - Each for \$132.90  
5.0 NTU, 1L
- 15-426-5** - Each for \$130.03  
10.0 NTU
- 15-426-42** - Each for \$196.28  
18.0 NTU, 1L
- 15-426-6** - Each for \$212.68  
20.0 NTU
- 15-426-7** - Each for \$206.53  
40.0 NTU, 1L

### GFS Chemicals Amco Clear Primary Turbidity Standards Linear Calibration Sets

- 15-426-10** - Pack of 5 for \$200.03  
Standard, Turbidity; Primary; Linear Calibration Sets; Amco Clear; NTU Range: 0 to 1; NTU Values/Set: 0.2/0.4/0.6/0.8/1.0
- 15-426-11** - Pack of 5 for \$230.72  
0 to 10 NTU Range
- 15-426-12** - Pack of 5 for \$270.44  
0 to 100 NTU Range

### HF Scientific Micro 100 Laboratory Turbidimeter



**15-393-80** - Each for \$1095.54  
 Turbidimeter; Micro 100; Auto range: 0-1000 NTU;  
 Resolution: 0.01 NTU; Response time: 6 sec; Min. sample  
 size: 270mL; Light: Tungsten filament; Auto calibration  
 alert; EPA; CE approved; Includes: 3 cuvetts, cal. std.,  
 power adapter; 120V  
**15-393-81** - Each for \$1196.86  
 Micro 100; 240V

### HF Scientific Micro 100 Laboratory Turbidimeter Calibration Kit

**15-393-84** - Each for \$215.15  
 Calibration Kit, 'Primary'; For Micro 100 Lab Turbidimeter; 0-100 NTU; Includes  
 0.02, 10 and 1000 calibration NTU

### HF Scientific Micro 1000 Ratio Turbidimeters



**15-393-97** - Each for \$1941.71  
 Turbidimeter, Ratio, Micro 1000, IR, 100-240VAC,  
 Bidirect RS-232 Output, Multiple Measurement Modes,  
 Color Correction  
**15-393-95** - Each for \$1909.78  
 Micro 1000, WL, 100-240VAC

### Orbeco Model 965-10A Digital Turbidimeter Replacement Set of 0 and 40 NTU Standards

**15-387** - Each for \$53.80  
 Standard, Turbidity; Replacement standards for Orbeco Model 965-10A; 0 and  
 40 NTU

### Orbeco-Hellige Model 965-10A, 966, and 966-IR Digital Turbidimeters



**15-375A** - Each for \$1087.71  
 Digital Turbidimeter, Model 965-10A; Portable;  
 Measurements 0-20, 0-200, 0-1000 NTU; Flow rate 1-2L/  
 min; 0-5 psi  
**15-398-181** - Each for \$660.21  
 Model 966-IR Portable Infrared Turbidimeter  
**15-386** - Each for \$759.75  
 Portable Turbidimeter W/case

### Phipps and Bird Six-Paddle Stirrer



**15-443-56** - Each for \$2795.00  
 Stirrer; Phillips and Bird; Six-Paddle; Comes complete  
 with six standard 1L round glass beakers and dust cover;  
 Stainless-steel paddles stir water samples simultaneously  
 at same speed; L x W x H: 8 x 40 x 18 in.

### Thermo Scientific Orion AQ4500 Turbidimeter



**13-650-100** - Each for \$1399.00  
 Meter, Turbidity, Model AQ4500, Dual Source, Thermo  
 Scientific, Portable, 0 to 1000 NTU

### Thermo Scientific Orion AQUAfast II Colorimeters Single Parameter Kits - For Turbidity Testing



**13-642-027** - Each for \$562.00  
 Colorimeter; AQUAfast II; Thermo Scientific Orion; Single  
 parameter; Ideal for fast, accurate water quality testing in  
 the laboratory and the field; Analyte: Turbidity Range: 0.1  
 to 2000 NTU

## Zinc

### EM Science Quant Test Strips - For Zinc Testing



**M100381** - Pack of 100 for \$73.26  
 Test: Zinc Kit; Pack of: 100; Range: 10-40-100-250ppm

### Orbeco Model 942: Test Kits for 975MP Analyst and 942 Mini Analysts - With Reagent Tablets - For Zinc Testing

**15-398-469** - Each for \$35.11  
 Reagent, Test Kit; For use with 975MP and 942 Mini Analysts; 50 tests; Test:  
 Zinc; Range: 0-4mg/L







**Fisher Scientific**

Part of Thermo Fisher Scientific



**Fisher Scientific**

For customer service, call 1-800-766-7000.  
To fax an order, use 1-800-926-1166.  
To order online: [www.fishersci.com](http://www.fishersci.com)