



Buy 1 Case of WHEATON Sample Vials in Lab File® and Receive 1 Free Coordinating Rack

Choose from a variety of sizes and Type I clear or amber glass. WHEATON Sample Vials in Lab File® are packaged in partitioned trays that provide an easy way to inventory samples or store empty vials. Vials are packaged with screw caps attached to maintain cleanliness.

Sample Vials in Lab File®

- Sample vials with caps attached to vial help maintain cleanliness
- Lab File® with partitioned trays provides an easy way to inventory samples or to store empty vials
- Clear vials made from low extractable borosilicate glass to provide superior chemical resistance
- Clear vials conform to USP Type I and ASTM E 438 Type I, Class A requirements
- Amber vials made from borosilicate glass that conforms to USP Type I requirements for light transmission to protect light-sensitive products
- Shorty Vials® feature a low profile for greater stability and less dead volume
- 14B rubber lined black phenolic screw cap for aqueous samples
- PTFE / 14B rubber lined black phenolic screw cap for organic samples
- Replacement caps can be purchased separately
- Vials and caps are autoclavable
- All caps are solid top / black phenolic

Cat. No.	Color	Size (mL)	Size (dr)	Liner Material	Cap Size	Dia. x H (mm)	Qty / Case	Fits Vial Rack
Shorty Vials with Caps Attached								
02-912-506	Clear	2	.5	14B Rubber	13-425	15 x 31	200	66022-523
02-912-514	Clear	2	.5	PTFE / 14B Rubber	13-425	15 x 31	200	66022-523
02-912-507	Clear	4	1	14B Rubber	15-425	17 x 41	200	66022-569
02-912-515	Clear	4	1	PTFE / 14B Rubber	15-425	17 x 41	200	66022-569
Standard Vials with Caps Attached								
06-408A	Clear	2	.5	14B Rubber	8-425	12 x 38	288	66022-478
02-911-648	Clear	2	.5	PTFE / 14B Rubber	8-425	12 x 38	288	66022-478
06-412-19	Amber	2	.5	14B Rubber	8-425	12 x 38	288	66022-478
02-911-654	Amber	2	.5	PTFE / 14B Rubber	8-425	12 x 38	288	66022-478
06-408B	Clear	4	1	14B Rubber	13-425	15 x 48	144	66022-523
02-911-649	Clear	4	1	PTFE / 14B Rubber	13-425	15 x 48	144	66022-523
06-412-20	Amber	4	1	14B Rubber	13-425	15 x 48	144	66022-523
02-911-655	Amber	4	1	PTFE / 14B Rubber	13-425	15 x 48	144	66022-523
06-408C	Clear	8	2	14B Rubber	15-425	17 x 63	144	66022-569
02-911-650	Clear	8	2	PTFE / 14B Rubber	15-425	17 x 63	144	66022-569
06-412-21	Amber	8	2	14B Rubber	15-425	17 x 63	144	66022-569
02-911-656	Amber	8	2	PTFE / 14B Rubber	15-425	17 x 63	144	66022-569

Continued on next page...

Offer good on Purchases
Now through 12/31/2013

How to redeem your FREE product: Purchase your product by calling 1.800.926.1166, visiting www.fishersci.com promo page or by contacting your Fisher Scientific sales representative before 12/31/13.

Restrictions

Orders must be placed by 12/31/2013. Redemption forms and proof of purchase must be received by 12/31/2013. Proof of purchase consists of either order confirmation, delivery ticket, packing list, invoice or acknowledgement. Redemptions must be completed in full to be a valid entry.

Offer valid in North America. Limited to two redemptions per customer. Free case must be of equal or lesser value. Not for resale. Offer valid while supplies last.

Buy 1 Case of WHEATON Sample Vials in Lab File® and Receive 1 Free Coordinating Rack

Sample Vials in Lab File®

Cat. No.	Color	Size (mL)	Size (dr)	Liner Material	Cap Size	Dia. x H (mm)	Qty / Case	Fits Vial Rack
Standard Vials with Caps Attached								
06-412-29	Clear	20	5	14B Rubber	24-400	28 x 60	72	66022-525
02-911-665	Clear	20	5	PTFE / 14B Rubber	24-400	28 x 60	72	66022-525
02-912-504	Amber	20	5	14B Rubber	24-400	28 x 60	72	66022-525
02-912-700	Amber	20	5	PTFE / 14B Rubber	24-400	28 x 60	72	66022-525
06-412-13	Clear	24	6	14B Rubber	20-400	23 x 88	144	66022-556
02-911-653	Clear	24	6	PTFE / 14B Rubber	20-400	23 x 88	144	66022-556
06-412-30	Clear	25	6.76	14B Rubber	24-400	28 x 73	72	66022-525
02-911-666	Clear	25	6.76	PTFE / 14B Rubber	24-400	28 x 73	72	66022-525
06-412-31	Clear	40	10.8	14B Rubber	24-400	28 x 98	72	66022-525
02-911-667	Clear	40	10.8	PTFE / 14B Rubber	24-400	28 x 98	72	66022-525
02-912-505	Amber	40	10.8	14B Rubber	24-400	28 x 98	72	66022-525
02-912-573	Amber	40	10.8	PTFE / 14B Rubber	24-400	28 x 98	72	66022-525
Standard Vials with Writing Patch and Caps Attached								
03-337-21A	Clear	4	1	14B Rubber	13-425	15 x 48	144	66022-523

Vial Racks

- Manufactured from polypropylene
- Size of rack depends on vial OD
- Easy to clean and autoclavable
- Alphanumeric indexing indicated on rack
- Racks are sturdy and stackable, even when the vials are in place
- Each well has an opening in the bottom to facilitate drainage



When selecting the proper rack, the vial OD can not exceed the well ID dimension.

Cat. No.	Well ID (mm)	Description	No. of Wells	Dimensions (L x W x H)	Qty / Case
06-408-10	12.5	50-Position Rack	5 deep x 10 wide	19 x 10 x 2.2cm	5
06-408-7	15.5	48-Position Rack	4 deep x 12 wide	26.6 x 9.4 x 2.8cm	5
22-262-955	17.1	90-Position Rack	6 deep x 15 wide	33 x 17 x 3cm	5
06-408-8	23.1	36-Position Rack	3 deep x 12 wide	32.2 x 9.1 x 2.8cm	5
06-408-6	28.1	50-Position Rack	5 deep x 10 wide	33 x 17 x 3cm	5