

Disposable Borosilicate Glass Tubes—with polypropylene screw cap.

The chemical stability and biological inertness of hard, borosilicate glass—at the price of disposable tubes. Ideal for tissue culture, bacteriology, clinical chemistry, blood typing, and cross matching procedures.

- Start clean—no lost samples due to contaminated, cloudy or scratched tubes
- Avoid pH problems caused by soft glass
- Round bottom
- With natural linerless polypropylene screw cap and marking spot
- Packed in trays of 500 or 250

O.D. x L	No. Per Tray	Catalog. No.	Case of
13 x 100mm	500	14-962-26D	1000/274.79
16 x 100mm	250	14-962-26F	1000/290.19
16 x 125mm	250	14-962-26G	1000/305.58
16 x 150mm	250	14-962-26H	1000/335.64
20 x 125mm	250	14-962-26K	500/247.25
20 x 150mm	250	14-962-26M	500/275.51



14-962-26

Foam Culture Tube Racks—Resilient wells grip tubes securely.

- Made from chemical- and solvent-resistant polyester foam
- Float in water bath with full load of tubes and samples
- Flame retardant
- Weight: Less than 2 oz. (56.7g)
- Five rows of wells and 10 columns per rack

For Tube Size	Catalog. No.	Pack of 6	Case of
10 x 75, 12 x 75, 13 x 100mm	05-664-15A	54.31	5 Pk./240.32
15 x 85, 16 x 100, 16 x 125 and 16 x 150mm	05-664-15B	82.93	3 Pk./220.18



05-664-15A

Fisherbrand is a registered trademark of Fisher Scientific.