



Isotemp Flammable Material Storage Refrigerator/Freezer Specifications

Model 13-986-425D

- Total storage capacity: 25 cu. ft. (707.9 l) (refrigerator), 4.5 cu. ft. (127.4 l) (freezer)
- Temperature range: Refrigerator compartment 3 to 13°C (37.4 to 55.4°F); freezer -15°C (5.0°F) at refrigerator temperature of 4°C (39.2°F)
- Average temperature stability: Refrigerator compartment $\pm 4^{\circ}\text{C}$ ($\pm 7.2^{\circ}\text{F}$)
- Defrost: Manual with built-in defrost drain
- Door: One solid, opens from left (hinged on right), non-reversible, lift-off for ease of installation, standard door lock, positive seal closure
- Insulation: Polyurethane foam
- Exterior dimensions: 80" H (203.2 cm), 35-1/2" W (90.2 cm), 35" D (88.9 cm) (depth includes handle)
- Interior useable dimensions: 49" H (124.5 cm), 32" W (81.3 cm), 22-1/2" D (57.2 cm)
- Shelves: 5 adjustable and 1 half-depth bottom rack
- Shelf capacity: 38.75 sq. ft. (3.6 cu.m.)
- Refrigerant: R404A, CFC-free
- Top-mounted: Hydraulic thermostat, solar powered LCD digital temperature display; user selects degrees C or F, reads in tenths of degree, keyed power switch
- Exterior: White heavy, baked-on polyester enamel finish
- Interior: White, epoxy-coated steel; door liner, ABS plastic
- Freezer compartment: Made from stainless steel, internal door
- Air clearances: Top 4" (10.2 cm), sides and back 4" (10.2 cm)
- Compressor: 1/3 hp, hot wall condenser
- Power requirements: 120 volts, $\pm 10\%$, 60 Hz, 3.5 amps, single phase
- Power cord: Three-prong (grounding) plug NEMA 5-15P which mates with a standard three-prong (grounding) wall receptacle (NEMA 5-15R)
- Approvals: UL listed, CSA approved; complies with NFPA code 99
- Provided with four leveling legs, two in front, two in rear
- Shipping weight: 350 lbs. (158.8 kg)
- Warranty: Two year parts and labor warranty, plus an additional three years parts-only warranty on the compressor
- Optional temperature recorder/alarm (changes exterior height to 81" [205.7 cm])