


## Worry-free Weighing

### Thanks to Balance Intelligence



#### StaticDetect™ – Sample OK

When static charges are detected, the weighing error is measured. If the user-defined limit is exceeded, a warning is given. For the highest process security, the user can employ anti-static measures to neutralize the charge and ensure the most accurate results.



#### StatusLight™ – Balance Ready

The StatusLight uses color to indicate the status of the balance at a glance. Green means ready, yellow is a warning and errors are shown with red. The clearly visible light communicates if the balance is ready for you to start your weighing task.



#### Operation – Ergonomic

The enhanced touchscreen user interface offers tireless, intuitive balance operation. SmartSens sensors allow you to operate your balance with the wave of a hand (e.g. open/close draft shield door). Tasks are easier and safer, and cross-contamination is avoided.



### Excellence XPE Analytical Balances Outstanding Performance

XPE Analytical Balances provide outstanding performance in analytical weighing and support the highest requirements for safety, efficiency and ease of compliance. Thanks to low repeatability, XPE Analytical Balances offer you the smallest minimum weight.

Quality management features, such as the innovative StatusLight and patented StaticDetect technology, take the worry out of weighing and provide you with a high level of trust in your results.

With a wide range of accessories available and multiple connectivity options, XPE Balances grow with your needs. You can enjoy a wealth of weighing possibilities for years to come.

LabX Standard Preparation Joanne

Net **0.26845 g**

Substance	Vanillin	<input type="checkbox"/>
Standard ID	A2536	<input type="checkbox"/>
Concentration	35.00 mmol/l	<input type="checkbox"/>
Flask Size	50 ml	<input type="checkbox"/>
Mol Mass	152.150 g/mol	<input type="checkbox"/>

Dose 0.26626 g of Vanillin  
Observe SmartTrac while dosing

Ctrl OK

#### LabX – Processes Under Control

LabX laboratory software provides flexible SOP user guidance on the balance touchscreen. Automatic data handling, calculations and report generation eliminate transcription errors and assure full traceability.

# Excellence XPE Analytical Balances

## Technical Specifications

Model	Item	Catalog No.
XPE105	30087635	01911000
XPE205	30087653	01911001
XPE205DR	30087700	01911002

Model	Item	Catalog No.
XPE204	30087643	01911003
XPE504	30087770	01911004

Limit values	XPE105	XPE205	XPE205DR	XPE204	XPE504
Maximum capacity	120 g	220 g	220 g	220 g	520 g
Readability	0.01 mg	0.01 mg	0.1 mg	0.1 mg	0.1 mg
Readability, fine range	–	–	0.01 mg	–	–
Tare range (from ... to)	0 ... 120 g	0 ... 220 g	0 ... 220 g	0 ... 220 g	0 ... 520 g
Maximum capacity, fine range	–	–	81 g	–	–
Repeatability (nominal) (sd)	0.03 mg (100 g)	0.03 mg (200 g)	0.06 mg (200 g)	0.07 mg (200 g)	0.12 mg (500 g)
Repeatability (5% load) (sd)	0.015 mg	0.015 mg	0.015 mg	0.05 mg	0.08 mg (20 g)
Linearity deviation	0.10 mg	0.10 mg	0.15 mg	0.2 mg	0.4 mg
Eccentricity (test load) <sup>1</sup>	0.12 mg (50 g)	0.2 mg (100 g)	0.25 mg (100 g)	0.25 mg (100 g)	0.4 mg (200 g)
Sensitivity offset (test weight)	0.3 mg (100 g)	0.4 mg (200 g)	0.5 mg (200 g)	0.6 mg (200 g)	1.5 mg (500 g)
Sensitivity temperature drift <sup>2</sup>	0.0001%/°C	0.0001%/°C	0.0001%/°C	0.0001%/°C	0.0001%/°C
Sensitivity stability <sup>3</sup>	0.0001%/a	0.0001%/a	0.0001%/a	0.0001%/a	0.0001%/a

### Typical values

Repeatability (5% load) (sd)	0.007 mg	0.007 mg	0.007 mg	0.04 mg	0.04 mg (20 g)
Linearity deviation	0.065 mg	0.065 mg	0.1 mg	0.13 mg	0.32 mg
Eccentricity (test load) <sup>1</sup>	0.1 mg (50 g)	0.1 mg (100 g)	0.1 mg (100 g)	0.12 mg (100 g)	0.2 mg (200 g)
Sensitivity offset (test weight)	0.15 mg (100 g)	0.2 mg (200 g)	0.32 mg (200 g)	0.4 mg (200 g)	0.6 mg (500 g)
USP minimum sample weight (5% load, k=2, U=0.10%)	14 mg	14 mg	14 mg	80 mg	80 mg
Minimum sample weight (5% load, k=2, U=1%)	1.4 mg	1.4 mg	1.4 mg	8 mg	8 mg
Settling time	1.5 s	2.5 s	1.5 s	1.5 s	1.5 s
Settling time, fine range	–	–	2.5 s	–	–

<sup>1</sup> according to OIML R76; <sup>2</sup> in the temperature range 10 to 30°C; <sup>3</sup> Stability of sensitivity with proFACT self-adjustment switched on; s: seconds; a: year (annum); sd: standard deviation

## Features

<b>Accurate Results</b>	High Resolution Technology Internal Adjustment with Sensitivity Test Internal Temperature Control StaticDetect™
<b>Efficient Operation</b>	Color Touchscreen User Interface in 11 Languages ErgoClips for Direct Dosing Easy Cleaning SmartGrid Hanging Weighing Pan SmartTrac Guided Dosing to Target Automatic Draft Shield SmartSens for Hands-free Operation
<b>Quality Assurance</b>	Graphical Leveling & Level Warning MinWeigh Protection Test Manager FACT, GWP & Admin History 8 Users & Password Protection StatusLight
<b>Seamless Process</b>	Quantos Upgrade Ready LabX Ready RFID Communication Ready Compact Antistatic Kit Ready Built-in RS232 & Optional 2nd Interface

## Accessories



### Quantos Upgrade Kit

Automated solid and solvent dispensing modules eliminate variability and errors, and offer the highest level of accuracy and safety.



### SmartSample™ RFID Tags

Transfer titration sample information securely from your balance to your titrator via the titration beaker.




### EasyScan

Check testing and calibration dates on RFID tagged pipettes. Record new test dates when you test using the balance application.



### AntiStatic Kits

The compact ionizer fixes onto your balance to gently remove charge from the weighing chamber. Free-standing units also available.



### Printers

The robust P-50 series lab printers produce archival-quality printouts on paper as well as continuous and peel-off labels.

For further information on accessories, please visit [www.mt.com/lab-accessories](http://www.mt.com/lab-accessories)

[www.fishersci.com/mettlertoledo](http://www.fishersci.com/mettlertoledo)

For more information



**In the United States:**  
For customer service, call 1-800-766-7000.  
To fax an order, use 1-800-926-1166.  
To order online: [www.fishersci.com](http://www.fishersci.com)

**In Canada:**  
For customer service, call 1-800-234-7437.  
To fax an order, use 1-800-463-2996.  
To order online: [www.fishersci.ca](http://www.fishersci.ca)