

US&R RAPID DEPLOYMENT STRIKE FORCE PACKAGE

Want to cut to the chase? What appears below is a standard equipment cache for a US&R team, as determined by our industry experts. To request a quote covering any segment of this list, merely fill in the quantity beside each item and fax the completed form to our toll free number: **1-866-209-3627**. If you are uncertain of the appropriate stocking levels for the size of your team, contact one of our product specialists at **1-800-226-4732** and they can help you clarify your needs.

PERSONAL GEAR

- Elbow Pads
- Flashlight
- Half-Facepiece Respirators
- APR Cartridges
- US&R Helmets
- Helmet Light
- Knee Pads
- US&R Gloves
- US&R Boots
- Saw Chaps
- Eye Protection
- Hearing Protection
- Welder's Gloves
- Welder's Jacket
- Welder's Goggles
- Welder's Helmet

BUILDING MARKING

- Spray Paint
- Lumber Chalk
- Lumber Crayon

CARPENTRY

- Carpenter Belt
- Carpenter's Pencils
- Level, 4'
- Duct Tape
- Framing Hammer
- Speed Square
- Tape Measure, 3'
- Nails, 8D, Per Case
- Nails, 16D, Per Case
- Hacksaw, Heavy Duty
- Hacksaw Blade, Carbide Grit

ROPE & HARDWARE

- Kernmantle Rope, 20' x 1/2"
- Kernmantle Rope, 150' x 1/2"
- Kernmantle Rope, 300' x 1/2"
- Webbing, 1" tubular
- Rope, Prussik Cord, 7mm
- Anchor Strap
- Pulley, 4"
- Carabiner, Steel-locking
- Steel Pickets
- Brake Bar Rack
- Edge Protection

ELECTRICAL

- String Lights, 50'
- Junction Box, 4 Outlet
- Extension Cord, 50' (14 Gauge) GFCI
- Generator, 5Kw (w/Lights)

US&R TECHNICIAN TRAINING

- Structural Collapse Awareness, 8 hr.
- Structural Collapse Operations, 50 hr.
- Structural Collapse Technician, 80 hr.

MISCELLANEOUS

- Come Along
- Haul Bucket
- Pipe Cutter
- Pipe
- Water Can
- General-Purpose Tool Kit
- Gas Can
- Web Sling
- Shackles, 24,000 lb.
- Wedge Anchor, 1/2"
- Wedge Anchor, 3/4"
- Hoist Ring, 1/2"
- Hoist Ring, 3/4"
- Four-Gas Monitor (O₂/CO/H₂S/LEL)
- Laser Range Meter

SPECIALIZED RESCUE TOOLS

- Air Bag Kit
 - Small
 - Medium
 - Large
- Mechanical Structural Shoring
 - Basic
 - Medium Duty
 - Heavy Duty
- Hydraulic/Pneumatic Tools
 - Hydraulic Power Unit
 - Hydraulic Chain Saw, 13" w/Chain
 - Hydraulic Chain Saw, 18" w/Chain
 - Hydraulic Cutoff Saw, 14"
 - Hydraulic Breaker, Medium Duty
 - Hydraulic Breaker, Heavy Duty
 - Pneumatic Impact Tools
 - Supplied-Air Cart

HAND TOOLS

- Axe, Flat Head
- Axe, Pick Head
- Bolt Cutter, 30"
- Bolt Cutter, 42", Heavy Duty
- Shovel, Long Handle, Round
- Shovel, Long Handle, Square
- Shovel, Scoop "D" Handle
- Pinch Point Bar
- Sledge Hammer, Short, 3-4 lb.
- Sledge Hammer, 8-10 lb.
- Claw Wrecking Bar, 3'
- Percussive Rescue Tool

SEARCH EQUIPMENT

- Search Camera, Non-listening
- Search Camera, Listening
- Listening Device (1 Sensor)
- Listening Device (4 Sensor)
- Electrical Cable Detector

ELECTRIC TOOLS

- Cordless Framing Nail Gun, Fuel Cells, and Nail Strips
- Demolition Hammer and Bits
- Rotary Hammer and Bits
- Metal Cutting Saw, 7" w/Blades
- Circular Saw, 10 1/4" w/Blades
- Ventilation Fan w/Ducting
- Rescue Tool Kit (Cutter, Spreader, Combo, and Rams)
- Reciprocating Saw w/Blades
- Compound Miter Saw w/Blades
- Drill, 1/2" Variable Speed w/Bits
- Rebar Cutter
- Steel-Reinforcement Detection System

FUEL-DRIVEN TOOLS

- Core Drill
- Core Drill Wet Kit
- Diamond Drill Bit, 2"
- Chain Saw, 16"
- Chain Saw w/Carbide-tip Chain
- Circular Cutoff Saw, 14"
- Circular Cutoff Saw, 16"
- Circular Saw Blade, 14"
- Circular Saw Blade, 16"
- Masonry Chain Saw w/Water Kit
- Diamond Chain Saw Replacement, 14"
- Water Tank
- Water Hose

WELDING EQUIPMENT

- Oxy-Gasoline Cutting Torch System
- Exothermic Cutting Torch and Rods
- Portable Oxy-Acetylene Cutter

LOGISTICS

- Storage Cases
- Trauma Kit w/O₂
- US&R Structures Field Guide

OTHER CUSTOMER NEEDS

NAME

DEPARTMENT

PHONE

FAX

EMAIL

US&R TRAILER QUOTATION/INFORMATION REQUEST FORM

Check those specs! At Fisher, we're all about giving you options. Review the features listed below, checking off those options that you would like to see in a trailer for your application. If you are unsure of how some of these features fit together, or if you would like to inquire about options not listed below, contact one of our product specialists at **1-800-226-4732** for more information. Fax the completed form to our toll-free number, **1-866-209-3627**.

STANDARD FEATURES

- Extended three-piece A-frame to accommodate generator (*Generator sold separately*)
- 2 $\frac{5}{16}$ " adjustable-height coupler with 25,000 lb. Gross Vehicle Weight Rating (GVWR) capacity
- Stationary drop leg 7,000 lb. jack
- High wind-rated air/sea lashing rings
- Tandem 6000 lb. Torflex® axles w/ Nev-R-Lube® hubs
- ST235/80R16 load range "D" radial tires with 8-bolt E-coated silver spoke wheels
- 7'6" interior height
- **Cargo Control System** including: Sidewall- (*multi-level*) and floor-mounted E-Track; 5000 lb. nonswivel D-rings; four-level adjustable steel shelving for housing the US&R Rapid Deployment Strike Force Package of your choice; organized storage for confined space shoring materials; and 12' tie straps with weblock assembly
- Spring-assisted rear ramp door with aluminum cam-lock and ramp extension
- Fully insulated sidewalls and ceiling
- **Interior/exterior battery-supported 12VDC lighting array** including: Interior dome lights; exterior porch light; wall switch; recessed 100 Ah deep cycle battery assembly with vented box, fuse panel, and PC 30 power source; and LED exterior wall-mounted emergency strobe light system
- **Extended time operations 120/240VAC lighting system** including: 4' fluorescent lighting; duplex wall receptacles; wall switch; 50 Amp (120/240V) service panel with 25' shoreline, cable hatch, and manual transfer switch; 500w 120V exterior surface-mounted quartz/halogen lighting
- Flow-thru sidewall vents
- Aluminum tread plate stone guard
- **LED Safety Package** consisting of: LED clearance lights; clearance lights on rear roof cap used as high profile brake light and side-mounted center clearance light used as turn indicator

ADDITIONAL OPTIONS (Check those specs you want added to your quote)

___ **Logistics Center Package†**, including:

- Exterior side-entry door with 22 x 15" radius tinted window
- Recessed step well at side door, providing a 15" step height from the ground
- Partition wall with door providing access to cargo area
- White Kemlite®-lined sidewalls and ceiling for easy cleanup
- R-5 insulation in sidewalls and ceiling
- One-piece, Lavent® rubber floor covering
- 71L x 36W x 24"H seated work station across front wall with undercounter drawer system
- Executive task chair with 5-point roller system
- 72L x 36W x 24"H workbench with laminated aluminum top, undercounter cabinets, and center knee-hole
- Overhead storage cabinets with positive locking doors
- 12V task lighting
- Cat #5 data and voice outlets (2 each)
- 120VAC duplex outlets (3 each) and multi-outlet battery charging center (1-5 ft.)
- 12VDC and 120VAC general interior lighting with wall switches
- 13,500 BTU roof-mounted air conditioner with 5600 BTU heat strip
- 1000w baseboard electric heater
- 48"H interior wall-mounted wet/dry marker board

___ **Custom Exterior Graphics Package**, including: 2 lines of text with 5" two-color nonreflective vinyl letters and NAPA reflective 1-3-1" stripping

- ___ 2 $\frac{1}{2}$ " adjustable pintle eye coupler exchanged from standard
- ___ Aluminum wheels exchanged from standard
- ___ Additional 15 Amp, 120VAC duplex outlet
- ___ Recessed 500w exterior quartz/halogen flood light
- ___ Exterior telescoping 500w quartz/halogen flood light
- ___ 15 Amp, 120VAC weatherproof exterior duplex outlet
- ___ 18' A & E Roll Up Exterior Awning
- ___ Honda ES6500, 6000w portable generator
- ___ A-frame mounted vented aluminum generator housing
- ___ Exterior removable message center board with overhead light

† Because of the space necessary to accommodate cargo section, Logistic Center Package can only be added to a 32' trailer.

NAME _____

DEPARTMENT _____

PHONE _____

FAX _____

EMAIL _____



BN128041B GCS-5M-1/04